



Ferrites and accessories

Index of part numbers

Date: May 2017

© EPCOS AG 2017. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

Index of part numbers

(In numerical order)

Part number	Page	Type
B62152	668	Double-aperture cores
B64290	621	Toroids (ring cores)
B65491	350	P 3.3 × 2.6 core
B65495	351	P 4.6 × 4.1 core
B65501	352	P 5.8 × 3.3 core
B65511	354	P 7 × 4 core
B65512	355, 356, 404	P 7 × 4 coil former, mounting assembly, PS 7.35 × 3.6 core, coil former
B65513	550	ER 14.5/6 core
B65517	358	P 9 × 5 core
B65518	361	P 9 × 5 mounting assembly
B65522	359	P 9 × 5 coil former, insulating washer
B65523	546	ER 9.5 core
B65524	360	P 9 × 5 coil former (SMD)
B65525	548	ER 11/5 core
B65526	549	ER 11/5 coil former (SMD), yoke
B65527	547	ER 9.5 coil former (SMD), yoke
B65531	363	P 11 × 7 core
B65532	364	P 11 × 7 coil former
B65535	365	P 11 × 7 mounting assembly
B65539	220, 232, 366	Adjusting screw for RM 4, RM 5, P 11 × 7
B65541	368	P 14 × 8 core
B65542	369, 406	P 14 × 8 coil former, insulating washer, P core half 14 × 7.5 coil former
B65545	370	P 14 × 8 mounting assembly
B65549	371	P 14 × 8 adjusting screw
B65611	394	P 36 × 22 core
B65612	395	P 36 × 22 coil former, insulating washer
B65615	396	P 36 × 22 mounting assembly
B65621	399	P 41 × 25 core
B65623	400	P 41 × 25 mounting assembly
B65646	302	PM 50/39 core
B65647	303, 304	PM 50/39 coil former, mounting assembly
B65651	373	P 18 × 11 core
B65652	374	P 18 × 11 coil former, insulating washer
B65655	375	P 18 × 11 mounting assembly
B65659	242, 249, 376	Adjusting screw for RM 6, RM 7, P 18 × 11
B65661	378	P 22 × 13 core
B65662	379	P 22 × 13 coil former, insulating washer

Index of part numbers

Part number	Page	Type
B65671	383	P 26 × 16 core
B65672	385	P 26 × 16 coil former, insulating washer
B65675	386	P 26 × 16 mounting assembly
B65679	267, 387, 392, 397	Adjusting screw for RM 10, P 26 × 16, P 30 × 19, P 36 × 22
B65684	305	PM 62/49 core
B65685	306, 307	PM 62/49 coil former, mounting assembly
B65686	308	PM 74/59 core
B65687	309, 310	PM 74/59 coil former, mounting assembly
B65701	389	P 30 × 19 core
B65702	390	P 30 × 19 coil former, insulating washer
B65705	391	P 30 × 19 mounting assembly
B65713	311	PM 87/70 core
B65714	312	PM 87/70 coil former
B65733	313	PM 114/93 core
B65734	314	PM 114/93 coil former
B65803	216, 221	RM 4 core, RM 4 low-profile core
B65804	218, 222 223, 224 504, 512	RM 4 coil former, insulating washer, RM 4 low-profile clamp, insulating washer, coil former (SMD) ELP 18, ELP 22 clamp
B65805	226, 233	RM 5 core, RM 5 low-profile core
B65806	219, 220 228, 229 230, 231, 232 366	RM 4 clamp, adjusting screw RM 5 coil former, clamp, insulating washer RM 5 clamp, adjusting screw, coil former (SMD) Adjusting screw for P 11 × 7
B65807	235, 243	RM 6 core, RM 6 low-profile core
B65808	237 ... 242 516	RM 6 coil former, clamp, insulating washer, adjusting screw ELP 32 clamp
B65811	252, 259	RM 8 core, RM 8 low-profile core
B65812	254 ... 258 260, 381	RM 8 coil former, clamp, insulating washer, adjusting screw RM 8 low-profile clamp, insulating washer, P 22 × 13 adjusting screw
B65813	262, 268	RM 10 core, RM 10 low-profile core
B65814	264, 265, 266	RM 10 coil former, clamp, insulating washer
B65815	270, 274	RM 12 core, RM 12 low-profile core
B65816	271, 272	RM 12 coil former
B65819	245, 250	RM 7 core, RM 7 low-profile core
B65820	247, 248	RM 7 coil former, clamp, insulating washer
B65821	241	RM 6 coil former (SMD)
B65822	230, 231	RM 5 coil former (SMD)

Index of part numbers

Part number	Page	Type
B65839	319	EP 7 core
B65840	321, 322	EP 7 coil former, cap yoke, EP 7 coil former (SMD)
B65841	328	EP 10 core
B65842	330, 331	EP 10 coil former, mounting assembly
B65843	333, 338	EP 13 core, EPO 13 core
B65844	335 ... 337 340, 341	EP 13 coil former, mounting assembly EPO 13 coil former
B65845	342	EP 17 core
B65846	343, 344	EP 17 coil former, mounting assembly
B65847	345	EP 20 core
B65848	346, 347	EP 20 coil former, mounting assembly
B65855A	317	EP 5 core
B65855B	318	EP 6 core
B65857A	324	EPX 7/9 core
B65857C	326	EPX 9/9 core
B65859	332	EPX 10 core
B65875A	284	PQ 20/20 core
B65875B	283	PQ 20/16 core
B65877A	287	PQ 26/25 core
B65877B	285	PQ 26/20 core
B65878E	288, 286	PQ 26/25 coil former, PQ 26/20 coil former
B65879A	289	PQ 32/20 core
B65879B	291	PQ 32/30 core
B65880E	290, 292	PQ 32/20 coil former, PQ 32/30 coil former
B65881A	293	PQ 35/35 core
B65883A	295	PQ 40/40 core
B65883B	294	PQ 40/30 core
B65884E	296	PQ 40/40 coil former
B65885A	282	PQ 16/11.6 core
B65887	276, 280	RM 14 core, RM 14 low-profile core
B65888	277, 278, 279	RM 14 coil former, clamp, insulating washer
B65928	411	PS core 68 × 14.5
B65933	404	PS core 7.35 × 3.6
B65935	405	PS core 9 × 3.5
B65936	405	PS core 9 × 3.5 coil former
B65937	406	P core half 14 × 7.5
B65939	407	PS core 25 × 8.9

Index of part numbers

Part number	Page	Type
B65940	407	PS core 25 × 8.9 coil former
B65941	408	PS core 30.5 × 10.2
B65942	408	PS core 30.5 × 10.2 coil former
B65943	410	PS core 47 × 14.9
B65945	412	P core half 70 × 14.5
B65946	411, 412	P core half 68 × 14.5 coil former, P core half 70 × 14.5 coil former
B65947	409	PS core 35 × 10.8
B65949	413	P core half 150 × 30
B65981A	298	PQ 50/50 core
B65981B	297	PQ 50/40 core
B65982E	299	PQ 50/50 coil former
B66202	429	E 13/7 coil former, yoke
B66206	447 ... 450	E 20/10 coil former, yoke
B66208	456 ... 457	E 25/13 coil former, yoke
B66219	435	E 14/8 core
B66229	466	E 32/16 core
B66230	467	E 32/16 coil former, yoke
B66232	464	E 30/15 coil former, yoke
B66233	468	E 32/16 core
B66243	477	E 42/21 coil former
B66281	502, 503	ELP14/3.5 core, I 14/1.5 core
B66283	504, 505	ELP18/4 core, I 18/2 core
B66284	506	EILP 18 clamp
B66285	509, 511	ELP 22/6 core, I 22/2.5 core
B66287	515, 517	ELP 32/6 core, I 32/3 core
B66289	521, 522	ELP 38/8 core, I 38/4 core
B66291	525, 526	ELP 43/10 core, I 43/4 core
B66293	529, 530	ELP 58/11 core, I 58/4 core
B66295	531, 532	ELP 64/10 core, I 64/5 core
B66297	533, 534	ELP 102/20 core, I 102/7 core
B66300	421	E 6.3 core
B66301	422	E 6.3 coil former (SMD), cover cap
B66302	423, 424	E 8.8 core, coil former (SMD), cover cap
B66303	420	E 5 core
B66305	427	E 13/7 core
B66306	431	E 13/7 coil former (SMD)
B66307	438	E 16/8 core
B66308	440, 441	E 16/8 coil former, yoke

Index of part numbers

Part number	Page	Type
B66310	451	E 20/10/11 core
B66311	445	E 20/10 core
B66314	452	E 21/9 core
B66315	459	E 25.4/10 core
B66317	454	E 25/13 core
B66319	462	E 30/15 core
B66322	425	E 10/5.5 core
B66325	473	E 42/21 core
B66325DG	492	E 42/21 core
B66329	475	E 42/21 core
B66329DG	493	E 42/21 core
B66335	480	E 55/28 core
B66335DG	495	E 55/28 core
B66344	482	E 55/28 core
B66347	560	ER 42/22 core
B66350	559	ER 35/20 core
B66357	563	ER 54/18 core
B66358	566	ETD 29/16 core
B66359	568, 569	ETD 29/16 coil former, yoke
B66361	570	ETD 34/17 core
B66362	572, 573	ETD 34/17 coil former, yoke
B66363	574	ETD 39/20 core
B66364	576	ETD 39/20 coil former, yoke
B66365	577	ETD 44/22 core
B66366	579	ETD 44/22 coil former, yoke
B66367	580	ETD 49/25 core
B66368	582	ETD 49/25 coil former, yoke
B66370	469	E 34/14 core
B66371	487	E 70/33 core
B66371DG	498	E 70/33 core
B66372	489	E 70/33/32 coil former
B66375	490	E 80/38 core
B66375DG	499	E 80/38 core
B66377	561	ER 46/17 core
B66379	443	E 19/8 core
B66381	472	E 40/16 core
B66383	479	E 47/20 core
B66383DG	494	E 47/20 core

Index of part numbers

Part number	Page	Type
B66385	484	E 56/24 core
B66387	485	E 65/32 core
B66387DG	497	E 65/32 core
B66388	486	E 65/32/27 coil former
B66389	470	E 36/18 core
B66390	471	E 36/18 coil former
B66391	562	ER 49/27 core
B66393	436	E 16/6 core
B66395	583	ETD 54/28 core
B66396	585	ETD 54/28 coil former, yoke
B66397	586	ETD 59/31 core
B66398	588	ETD 59/31 coil former, yoke
B66408	603	EV 25/13 core
B66411	591	EFD 10/5 core
B66413	592	EFD 15/8 core
B66414	432, 593, 594	E 13/7 cover plate, EFD 15/8 coil former, yoke, cover plate
B66417	595	EFD 20/10 core
B66418	597	EFD 20/10 coil former, yoke
B66421	598	EFD 25/13 core
B66422	599	EFD 25/13 coil former, yoke
B66423	600	EFD 30/15 core
B66424	601	EFD 30/15 coil former, yoke
B66432	604	EV 30/16 core
B66433	558	ER 28/17 core
B66434	602	EV 15/9 core
B66453	507, 508	ELP 18/4 core, I 18/2 core
B66455	513, 514	ELP 22/6 core, I 22/2.5 core
B66457	519, 520	ELP 32/6 core, I 32/3 core
B66459	523, 524	ELP 38/8 core, I 38/4 core
B66461	527, 528	ELP 43/10 core, I 43/4 core
B66479	536, 537	EQ 13/2.8 core, I 13/1 core
B66480	551	ER 18/3 core
B66481	540, 541	EQ 25/5.6 core, I 25/2.3 core
B66482	552, 553	ER 23/5 core, I 23/2 core
B66483	538, 539	EQ 20/6.3 core, I 20/2.3 core
B66484	554, 555	ER 25/6 core, I 25/3 core
B66486	453	E 22/15 core
B66489	461	E 28/10 core

Index of part numbers

Part number	Page	Type
B66492	426	E 12.7/6 core
B66500	437	E 16/7 core
B66501	556	ER 32/5 core
B66506	542, 543	EQ 30/8 core, I 30/2.7 core
B66536	434	E 13/6 core
B66543	433	E 13/6.5 core
B66567	605	EV 36/16/9 core
B66894	491	E 100/60 core
B67345	609	U 93/76 core, I 93/28 core
	610	U 93/76 core, I 93/28 core
	611	U 93/76 core, I 93/28 core
B67355	607	U 26/22 core
B67362	608	U 30/26 core
B67370	612	U 101/76 core
B67374	614	U 141/78 core
B67385	613	U 126/91 core, I 126/28 core
B68450	671	FPC film C350, C351 material
B68451	671	FPC film C350, C351 material

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.