



Sample Kit SMD Common-mode Chokes

Series B82721S0





www.tdk-electronics.tdk.com


SMD Common-mode Chokes – Series B82721S0

I _R	A	2.7	2.8	3.2	3.2	5.6	5.7	5.7
L _N	mH	3.000	1.470	1.320	0.220	0.768	1.180	0.590
L _{stray, typ}	μH	12	11	11	10	5	5	5
R _{typ}	mΩ	65	59	50	49	18	17	17
T _R	°C	+40	+40	+40	+40	+40	+40	+40
Version		2	1	1	1	1	1	1
Ordering code	B82721S0	272T040	282A030	322A020	322A010	562A030	572A040	572A020

Features

- All values measured at +20 °C
- Approx. 0.8 ... 0.9% stray inductance for differential-mode interference suppression (B82721S0322A010: 4.6%)
- Suitable for reflow soldering
- RoHS-compatible
- Storage conditions (packaged): -25 °C to +40 °C, ≤75% RH
- Tape and reel packing: 32 mm blister tape, 330 mm reel
- Packing unit: 200 pcs/reel

Dimensional drawing and pin configuration



Important information: It is incumbent on the customer to check and decide whether a product is suitable for use in a particular application. Our products are described in detail in our data sheets. Our Important notes and the product-specific Cautions and warnings must be observed. All relevant information is available through our sales offices.

© TDK Electronics AG · Edition 2023 · Ordering No. B82721X2 · SO 0623