



Aluminum Electrolytic Capacitors

Selection chart

Date: December 2019

© TDK Electronics AG 2019. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.

Selection chart

Automotive – Axial-lead and soldering star capacitors

Low-voltage series

125 ... 140 °C

Ultra compact

<p>B41690/B41790 25 ... 40 V 125 °C / > 5000 h 140 °C / > 2000 h</p>
Page

125 ... 150 °C

Very high ripple current

<p>B41689/B41789 25 ... 63 V 125 °C / > 10000 h 150 °C / > 2000 h</p>
Page

Extremely high ripple current

<p>B41687/B41787 63 V 125 °C / > 4000 h 150 °C / > 1000 h</p>
Page

Compact

<p>B41692/B41792 25 ... 75 V 125 °C / > 5000 h 140 °C / > 2000 h</p>
Page

High reliability

<p>B41693/B41793 75 ... 100 V 125 °C / > 5000 h 150 °C / > 1000 h</p>
Page

High-voltage series

125 ... 140 °C

High voltage

<p>B43693/B43793 140 ... 250 V 125 °C / > 2500 h 140 °C / > 1000 h</p>
Page