

Aluminum Electrolytic Capacitors

4-/5-pin snap-in terminals and solder pins – Selection chart

Date: December 2019

Selection chart

High voltage series

85 °C

105 °C

*4-/5-pin snap-in,
very compact*

<p>B43512 385 ... 500 V 85 °C / > 5000 h 105 °C at $V_{OP} \leq 0.90 \cdot V_R$</p>
Page

4-pin snap-in

<p>B43516 400 ... 450 V 105 °C / > 3000 h</p>
Page

Solder pins, very compact

<p>B43522 385 ... 500 V 85 °C / > 5000 h 105 °C at $V_{OP} \leq 0.90 \cdot V_R$</p>
Page

Solder pins

<p>B43526 400 ... 450 V 105 °C / > 3000 h</p>
Page

*4-pin snap-in,
long useful life*

<p>B43513 350 ... 450 V 85 °C / > 10000 h 105 °C at $V_{OP} \leq 0.95 \cdot V_R$</p>
Page

Solder pins, long useful life

<p>B43523 350 ... 450 V 85 °C / > 10000 h 105 °C at $V_{OP} \leq 0.95 \cdot V_R$</p>
Page