



Film Capacitors

Weights

Date: June 2018

© EPCOS AG 2018. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

Weights

Radial-lead capacitors

The following table contains the weights for all radial-lead capacitors with plastic casings. Deviations of up to approximately $\pm 30\%$ are possible.

Lead spacing/ Type number	Dimensions w × h × l mm (max.)	Weight g	Lead spacing/ Type number	Dimensions w × h × l mm (max.)	Weight g
Lead spacing 5 mm			Lead spacing 22.5 mm		
B32529, B32559	2.5 × 6.5 × 7.3	0.20	B32023, B32033, B32523, B32643, B32683, B32913, B32913, B32923, B32923, B32933, B81123	6.0 × 15.0 × 26.5	4.0
	3.0 × 6.5 × 7.3	0.25		7.0 × 16.0 × 26.5	4.8
	3.5 × 8.0 × 7.3	0.32		7.5 × 14.0 × 26.5	4.7
	4.5 × 9.5 × 7.3	0.46		8.5 × 16.5 × 26.5	5.5
	5.0 × 10.0 × 7.5	0.54		9.0 × 14.0 × 26.5	5.6
	6.0 × 10.5 × 7.5	0.68		10.5 × 16.5 × 26.5	7.5
	7.8 × 13.0 × 7.8	0.90		10.5 × 18.5 × 26.5	8.0
Lead spacing 7.5 mm				10.5 × 20.5 × 26.5	8.5
B32520, B32620	2.5 × 7.0 × 10.0	0.30		11.0 × 20.5 × 26.5	9.0
	3.0 × 8.0 × 10.0	0.40		12.0 × 22.0 × 26.5	10.5
	4.0 × 8.5 × 10.0	0.52		14.5 × 29.5 × 26.5	18.9
	5.0 × 10.5 × 10.0	0.80		15.5 × 33.5 × 26.5	20.5
	6.0 × 12.0 × 10.3	0.98		17.0 × 22.0 × 26.5	12.5
Lead spacing 10 mm			Lead spacing 27.5 mm		
B32021, B32521, B32621, B32641, B32651, B32671, B32911, B32921	4.0 × 7.0 × 13.0	0.52	B32024, B32034, B32524, B32654, B32674, B32684, B32754, B32774, B32914, B32924, B32934	11.0 × 19.0 × 31.5	9.5
	4.0 × 9.0 × 13.0	0.70		11.0 × 21.0 × 31.5	10
	5.0 × 11.0 × 13.0	1.1		12.5 × 21.5 × 31.5	13
	6.0 × 12.0 × 13.0	1.4		13.5 × 23.0 × 31.5	15
	6.0 × 14.0 × 13.0	1.6		14.0 × 24.5 × 31.5	16
	7.0 × 16.0 × 13.0	1.8		15.0 × 24.5 × 31.5	16
8.0 × 17.5 × 13.0	2.5	16.0 × 32.0 × 31.5		21	
Lead spacing 15 mm				18.0 × 27.5 × 31.5	20
B32022, B32032, B32522, B32642, B32652, B32672, B32682, B32912, B32922, B32932, B81123	5.0 × 10.5 × 18.0	1.5		18.0 × 33.0 × 31.5	24.5
	5.5 × 8.5 × 18.0	1.4		19.0 × 30.0 × 31.5	23
	5.5 × 11.0 × 18.0	1.8		21.0 × 31.0 × 31.5	26.3
	6.0 × 11.0 × 18.0	1.9	22.0 × 36.5 × 31.5	33	
	6.0 × 12.0 × 18.0	2.1	22.0 × 48.0 × 31.5	36	
	7.0 × 12.5 × 18.0	2.5			
	8.0 × 14.0 × 18.0	3.2			
	8.5 × 14.5 × 18.0	3.3			
	9.0 × 13.5 × 18.0	3.0			
	9.0 × 17.5 × 18.0	4.5			
	11.0 × 18.5 × 18.0	5.6			
13.0 × 14.0 × 18.0	4.1				

Weights

Lead spacing/ Type number	Dimensions w × h × l mm (max.)	Weight g
Lead spacing 37.5 mm		
B32026, B32036,	12.0 × 22.0 × 42.0	18
B32526, B32656,	14.0 × 25.0 × 42.0	20
B32676,	16.0 × 28.5 × 42.0	25
B32686A	18.0 × 32.5 × 42.0	32
B32776, B32756,	20.0 × 39.5 × 42.0	40
B32916, B32926,	22.0 × 45.0 × 42.0	60
B32936	24.0 × 15.0 × 42.0	16
	24.0 × 19.0 × 42.0	20
	28.0 × 37.0 × 42.0	46
	28.0 × 42.5 × 42.0	60
	33.0 × 48.0 × 42.0	72
	43.0 × 22.0 × 42.0	44

Lead spacing/ Type number	Dimensions w × h × l mm (max.)	Weight g
Lead spacing 52.5 mm		
B32658, B32678,	22.0 × 33.0 × 57.5	52
B32758, B32778,	27.0 × 39.5 × 57.6	78
B32918, B32928	30.0 × 45.0 × 57.5	90
	35.0 × 50.0 × 57.5	120
	38.0 × 57.5 × 57.5	125
	43.0 × 24.0 × 57.5	61
	45.0 × 57.0 × 57.5	151
	60.0 × 45.0 × 57.5	164
	130.0 × 24.0 × 57.5	182
	130.0 × 58.0 × 57.5	495