

Aluminum Electrolytic Capacitors

Capacitors with screw terminals – Selection chart

Date: December 2019

Selection chart

Low-voltage series

85 °C

B41456 / B41458

16 ... 100 V

85 °C / > 12000 h

Page

105 °C

Very compact

B41560 / B41580

25 ... 100 V

105 °C / > 3000 h

Page

High-voltage series

85 °C

B43701 / B43721

350 ... 450 V

85 °C / > 5000 h

Page

B43712 / B43732

350 ... 450 V

85 °C / > 10000 h

Page

105 °C

B43742 / B43762

350 ... 500 V

105 °C / > 5000 h

Page

High voltage

B43700 / B43720

550 ... 600 V

85 °C / > 8000 h

Page

Very long useful life

B43713 / B43733

200 ... 500 V

85 °C / > 15000 h

Page

Very high ripple current

B43743 / B43763

350 ... 500 V

105 °C / > 6000 h

Page

Very compact

B43703 / B43723

350 ... 500 V

85 °C / > 12000 h

Page

Ultra compact

B43707 / B43727

400 ... 450 V

85 °C / > 12000 h

Page

High ripple current

B43704 / B43724

350 ... 550 V

85 °C / > 12000 h

Page

Outstanding ripple current

B43705 / B43725

350 ... 450 V

85 °C / > 12000 h

Page