

NTC Inrush Current Limiters

Taping and packing

Date: July 2019

© TDK Electronics AG 2019. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.




Taping and packing

1 Taping of radial leaded ICL NTC thermistors according to the specified lead spacing


Dimensions and tolerances

Lead spacing F = 5.0 mm (taping to IEC 60286-2)

for the following types: S153, S235 and S236



Lead spacing F = 7.5 mm (taping based on IEC 60286-2) for the following types: P11, P13, S237, S238 and S364





Taping and packing

Dimensions (mm)


	1	ı	ı		
	Lead	Tolerance of	Lead	Tolerance of	Remarks
	spacing 5 mm	lead spacing 5 mm	spacing 7.5 mm	lead spacing 7.5 mm	
	<12.0	3 111111	>12.0	7.5 111111	nlaces refer to dimensional
W	≤12.0		≥12.0		please refer to dimensional drawings
th	6.0	max.	7	max.	please refer to dimensional drawings
d	0.5/0.6	±0.05	0.8/1.0	±0.05	please refer to dimensional drawings
Po	12.7	±0.3	12.7	±0.3	± 1 mm / 20 sprocket holes
P ₁	3.85	±0.7	8.95	±0.8	
F	5.0	+0.6/-0.1	7.5	±0.8	
Δh	0	±2.0	0	Depends on th	•
					of component body
Δp	0	±1.3	0	±2.0	
W	18.0	±0.5	18.0	±0.5	
W_0	5.5	min.	11.0	min.	peel-off force ≥5 N
W ₁	9.0	+0.75/-0.5	9.0	+0.75/-0.5	
W ₂	3.0	max.	3.0	max.	
Н	18.0	+2.0/-0	18.0	+2.0/-0	applies only to uncrimped types
H _o	16.0	±0.5	16.0	±0.5	applies only to crimped types
H ₁	32.2	max.	45.0	max.	
D ₀	4.0	±0.2	4.0	±0.2	
t	0.9	max.	0.9	max.	without wires
L	11.0	max.	11.0	max.	
L ₁	4.0	max.	4.0	max.	




Taping and packing

Types of packing

Reel packing






Reel dimensions (in mm)

Reel type	Series	pcs. per reel	d	f	n	w
I	S153, S235	1500	360 max.	31 ±1	approx. 45	54 max.
I	S236	1000	360 max.	31 ±1	approx. 45	54 max.
II	P11, P13	1500	500 max.	23 ±1	approx. 59	72 max.
II	S237, S238, S364	1000	500 max.	23 ±1	approx. 59	72 max.

Ammo packing



Ammo type	Series	pcs. per package	х	у	Z
I	S153, S235, S236	1000	45	335	272
II	P11, P13, S237, S238, S364	750	55	340	340

Ammo packing dimensions (in mm)

Bulk packing

The components are packed in cardboard boxes, the size of which depends on the order quantity. Series S464 and P27 is only available as bulk.