



Sample Kit



Frame Core Chokes

B82732F*B001 for Power Lines

www.epcos.com

Frame Core Chokes for Power Lines

Series B82732F*B001

$L_R +30/-50\%$	mH	10	15	27	39	47	68	100
$I_{R \text{ typ}}$	A	1.6	1.3	0.9	0.8	0.7	0.6	0.45
$L_{\text{stray typ}}$	μH	200	290	520	760	920	1340	1930
R_{typ}	m Ω	290	430	770	1100	1260	1970	2930
Ordering code		B82732 F2162B001	B82732 F2132B001	B82732 F2901B001	B82732 F2801B001	B82732 F2701B001	B82732 F2601B001	B82732 F2451B001

Rated inductance L_R : measured at 10 kHz, 0.1 mA, 20 °C

- Rated current: I_R at 50 Hz and $T_A = 40$ °C
- Rated voltage: 250 V AC
- Clearance and creepage distances: > 3 mm
- Lead spacing: 18.75 x 10.0 ±0.2 mm
- Climatic category 40/125/56 (to IEC 60068-1)
- Excellent differential-mode suppression

Contact at product marketing: uwe.ernst@epcos.com

