

Sample Kit

SMD Common-mode Chokes

Series B82722S0



www.tdk-electronics.tdk.com




SMD Common-mode Chokes – Series B82722S0

I _R	А	3.25	8.60	10.40	13.00	19.00	19.00
L _N	mH	5.60	0.81	0.63	0.47	0.38	0.16
L _{stray, typ}	μH	21.0	10.0	6.6	4.3	2.5	0.8
R _{typ}	mΩ	69.0	12.0	8.8	6.7	3.0	2.5
T _R	°C	+40	+40	+40	+40	+40	+40
Ordering code	B82722S0	322A040	862A020	103A020	133A020	193A040	193A041


Features

- All values measured at +20 °C
- Approx. 0.4 ... 1.2% stray inductance for differential-mode
- · Suitable for reflow soldering
- RoHS-compatible
- Storage conditions (packaged): -25 °C to +40 °C. <75% BH
- Tape and reel packing: 44 mm blister tape, 330 mm reel
- Packing unit: 100 pcs/reel

Dimensional drawing and pin configuration




Layout recommendation



IND1276-LE

Important information: It is incumbent on the customer to check and decide whether a product is suitable for use in a particular application. Our products are described in detail in our data sheets. Our Important notes and the product-specific Cautions and warnings must be observed. All relevant information is available through our sales offices.



Important information: It is incumbent on the customer to check and decide whether a product is suitable for use in a particular application. Our products are described in detail in our data sheets. Our Important notes and the product-specific Cautions and warnings must be observed. All relevant information is available through our sales offices.