



Film Capacitors

Marking and ordering code system

Date: June 2018

© EPCOS AG 2018. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

Marking and ordering code system






1 Capacitor markings

Depending on the capacitor size, the markings are positioned either on the side and/or the top of the component. The coded forms specified in IEC 60062:2004 are used to indicate the rated capacitance, capacitance tolerance and date of manufacture.

The lot number (production batch number) ensures unique identification of a particular capacitor and allows, together with the date of manufacture, exact assignment to the process data of the entire production run (traceability).

Marking examples

Boxed capacitors (without EMI suppression capacitors)

Style	Lead spacing	Marking example	Marking
MKT	5 mm	Version 1  KMK17394	Side stamping: Manufacturer's logo, C_R , tolerance, V_R
		Version 2  KMK0994-V-E	Side stamping: C_R , tolerance, V_R , manufacturer's logo, coded type "1", date of manufacture (year and month coded)
		Version 3  KMK0995-4-E	Top stamping: Manufacturer's logo, C_R , tolerance, V_R
	7.5 mm	Version 1  KMK0995-4-E	Top stamping: Manufacturer's logo, C_R , tolerance, V_R
		Version 2  KMK0994-V-E	Side stamping: C_R , tolerance, V_R , Manufacturer's logo, coded type "1", date of manufacture (year and month coded).

Marking and ordering code system

Style	Lead spacing	Marking example	Marking
MKT MKP	10 mm		Manufacturer's logo <i>1st line:</i> Lot number (1 character, 9 digits), series number (film material is coded in the series number) <i>2nd line:</i> C _R , tolerance, V _R (DC or AC), date of manufacture (year and month coded)
MKT MKP MFP	15 ... 37.5 mm	Version 1 	Manufacturer's logo <i>1st line:</i> Lot number (1 character, 9 digits), series number (film material is coded in the series number) <i>2nd line:</i> C _R , tolerance, V _R (DC or AC), date of manufacture (year and month coded)
		Version 2 	Manufacturer's logo <i>1st line:</i> Series number, film material (MKP or MFP) <i>2nd line:</i> C _R , tolerance, V _R (DC or AC) <i>Vertical:</i> Date of manufacture (year and month coded)
		Version 3 	Manufacturer's logo <i>1st line:</i> Lot number, series number <i>2nd line:</i> C _R , tolerance, V _R (DC or AC), date of manufacture (year and month coded)
MKP	52.5 mm	Version 1 	Manufacturer's logo <i>1st line:</i> Series number, film material (MKP or MFP) <i>2nd line:</i> C _R , tolerance, V _R (DC or AC) <i>Vertical:</i> Date of manufacture (year and month coded)
		Version 2 	Manufacturer's logo <i>1st line:</i> Lot number, series number <i>2nd line:</i> C _R , tolerance, V _R (DC), date of manufacture


SilverCap™ capacitors

Style	Lead spacing	Marking example	Marking
MKT	7.5 ... 27.5 mm		<i>1st line:</i> C _R <i>2nd line:</i> V _R

Marking and ordering code system

EMI suppression capacitors

X1-330 V AC:




KMK1736-1

X1-530 VAC:




KMK1737-2

Y1-500 V AC:



KMK1557-M

Y2-300 V AC:



KMK1738-3


X2-305 V AC (B3292 C/D): For X2 EMI capacitors we distinguish between two different types of marking, depending on the capacitance.

$C \leq 10 \mu\text{F}$




KMK1541-3

$C > 10 \mu\text{F}$



KMK1542-2

X2-305 V AC (B3293 A/B):



KMK1318-E

X2-305 V AC (B3293 H/J):



KMK1582-Y

X2-350 V AC:



KMK1872-T

Marking and ordering code system

For all EMI capacitors:

If the capacitor is wide enough, the entire marking will be on the top. In this case, the stamping will contain the following information:

1st line: Manufacturer's logo, lot number, revision status


2nd line: Date code, capacitance, cap. tolerance, rated voltage

3rd line: Type number, interference suppression, sub class, style/self-healing

4th line: Climatic category

5th line: Marks of conformity

If the capacitor is not wide enough for the entire marking, the information in the marking will be split between the top and side. In this case, the following partial information will be found on the top:

Manufacturer's logo  Lot number, Revision status
Date code, Capacitance,
Cap. tolerance, Rated voltage

KMK1740-5

Codes for rated capacitance

Rated capacitance	To IEC 60062	Short code
100 pF	100p	n1
150 pF	150p	n15
1.0 nF	1n0	1n
1.5 nF	1n5	
10 nF	10n	
100 nF	100n	μ1
150 nF	150n	μ15
1.0 μF	1μ0	1μ
1.5 μF	1μ5	
10 μF	10μ	
15 μF	15μ	

Codes for capacitance tolerance

Cap. tolerance	Code letter	Remark
–	A	Capacitance tolerances for which no code letter is defined can be indicated by an A. The meaning of code A must then be mutually specified in other documentation.
±2.5%	H	
±5%	J	
±10%	K	
±20%	M	

Marking and ordering code system

Codes for date of manufacture (to IEC 60062:2004)

Code for year				Code for month			
Year	Code letter	Year	Code letter	Month	Code numeral	Month	Code numeral/letter
2012	C	2018	K	January	1	July	7
2013	D	2019	L	February	2	August	8
2014	E	2020	M	March	3	September	9
2015	F	2021	N	April	4	October	O
2016	H	2022	P	May	5	November	N
2017	J	2023	R	June	6	December	D

E.g.: J5 \triangle 2017 May

Marking types

The capacitors may have either an ink-jet marking or a laser marking. The main advantage of laser marking is that it cannot be removed by solvents, which ensures the reliable identification of the capacitor. Moreover, because the laser marking process reduces the amount of chemicals used, it is an environmentally friendly marking solution.


Marking and ordering code system

2 Ordering code system

A component and the packing in which it is to be delivered are defined by the ordering code, which has 15 digits (plus 3 additional digits for internal use). For all capacitors the ordering codes are explicitly stated (together with the corresponding tolerance and/or packing variants) in the data sheets.

Should there be any doubt about the coding system, however, then it is better to order the capacitor using a plain text description (i.e. without a code).

Basic structure of the ordering code:



Digit	Meaning			
1	B = Passive components			
2, 3	32 = Metallized film capacitors, EMI suppression capacitors 81 = EMI suppression capacitors			
4 ... 6	Type (block 1 is termed the "type number")			
7	Revision status S = Special type A = Automotive type (not for EMI suppression capacitors)			
8	Rated DC voltage, coded (not for EMI suppression capacitors)			
9 ... 11	Rated capacitance (coding method for value in pF) Examples: Digit 9 10 11 B 3 2 6 5 2 A 3 <table border="1" style="display: inline-table; vertical-align: middle;"><tr><td>1</td><td>5</td><td>4</td></tr></table> K = $15 \cdot 10^4$ pF = 150 nF	1	5	4
1	5	4		
12	Code letter for capacitance tolerance			
13 ... 15	Codes for lead and taping parameters (refer to respective data sheet). Special code for capacitors with "S" in digit 7.			
16 ... 18	Internal use			

Display of ordering codes for EPCOS products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications and the website of EPCOS, or in order-related documents such as shipping notes, order confirmations and product labels. **The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.** Detailed information can be found on the Internet under www.epcos.com/orderingcodes.