

# **EMC filters**

3-line active filter LeaXield for leakage current compensation

 Series/Type:
 B84233A1500R000

 Date:
 March 2019

© TDK Electronics AG 2019. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



B84233A1500R000

# 3-line active filter LeaXield

## for leakage current compensation

Rated voltage  $V_R$ : 305/530 V AC Rated current  $I_R$ : 50 A Peak load side leakage current  $I_{LK-LOAD}$ : 1 A

U.S. Patent No. 10,069,480

# Construction

- 3-line filters
- Metal case
- Book size

## Features

- High leakage current compensation
- Optimization of the RCD<sup>1</sup> compatibility
- Easy to install
- No external power supply needed
- Degree of protection: IP 20<sup>2)</sup>

## **Typical applications**

- Drives
- Machine tools
- Pumps
- Compressors
- Transport systems
- Pluggable machines

# Terminals

Finger-safe terminal blocks

#### Marking

Marking on component:

Manufacturer's logo, ordering code, rated voltage, rated current, rated temperature, climatic category, date code

Minimum data on packaging: Manufacturer's logo, ordering code, quantity, date code

1) RCD = Residual current device


2) According to IEC 60529





for leakage current compensation

# Typical circuit diagram



# Technical data and measuring conditions

Rated voltage V <sub>R</sub>	305/530 V AC (50 Hz)
Minimum operating voltage V <sub>min</sub>	208/360 V AC (50 Hz)
Rated current I <sub>R</sub>	Referred to 50 °C rated temperature
Test voltage V <sub>test</sub>	1770 V DC, 2 s (line/line)
	1500 V DC, 2 s (lines/case)
Overload capability (thermal)	$1.5 \cdot I_{R}$ for 3 min per hour or
	$2.5 \cdot I_{R}$ for 30 s per hour
Peak load side leakage current ILK-LOAD	1 A
Contactor connection:	
<ul> <li>Maximum voltage V<sub>max</sub></li> </ul>	24 V DC / 250 V AC
<ul> <li>Maximum current I<sub>max</sub></li> </ul>	2 A
Climatic category (IEC 60068-1)	25/100/21 (-25 °C/+100 °C/21 days damp heat test)

# Characteristics and ordering codes

I <sub>R</sub>	Terminal cross section		<b>R</b> <sub>typ</sub>	Approx. weight	Ordering code
	Line/Load	Contactor connection			
А	mm <sup>2</sup>	mm <sup>2</sup>	mΩ	kg	
50	16	4	1.0	1.63	B84233A1500R000



#### for leakage current compensation

#### Functional description

LeaXield<sup>™</sup> was developed to significantly reduce the earth leakage currents that are produced in variable-speed drive systems. It enables the operation of systems with high earth leakage currents together with the use of residual current devices (RCDs). LeaXield thus plays a valuable role in industrial applications with variable-speed drives such as those in machine tools, pumps, compressors, conveyance systems, and other pluggable devices.

LeaXield is inserted in the power line and requires no additional power supply. In order for LeaXield to be ready for operation before leakage currents flow, there must be a contactor in the power line. The contactor must be on the load side of the LeaXield and have a minimum time delay of 2 s. If this is not possible, the built-in contactor connection on the LeaXield can be used. This ensures that the contactor is switched with a delay when the mains is switched on. Refer to the diagram below for installation.


LeaXield is an active leakage current filter that does not need any additional power supply. Attenuation of more than 35 dB is possible within a frequency range of 150 Hz up to 30 kHz.

LeaXield can improve EMC performance of existing systems. For example, other EMC measures within the system can be reduced.

#### Note:


According to EN 50178 / VDE 0160, only type B/B+ RCDs are allowed in variable-speed drive systems!

# **Recommended system configuration**



#### Wiring of contactor connection

Important notes at the end of this document.






B84233A1500R000

# 3-line active filter LeaXield

#### for leakage current compensation

# **Dimensional drawings**

# B84233A1500R000 (50 A)



Dimensions in mm



B84233A1500R000

**3-line active filter LeaXield** 

#### for leakage current compensation

## Cautions and warnings

Please read all warning and safety notes carefully before installing the filter and putting it into operation (see  $\underline{M}$ ). The same applies to the warning signs on the filter. Please ensure that the signs are not removed nor their legibility impaired by external influences.

Death, serious bodily injury and substantial material damage to equipment may occur if the appropriate safety measures are not carried out or the warnings in the text are not observed.

## Using according to the terms

The filters may be used only for their intended application within the specified values in lowvoltage networks in compliance with the instructions given in the data sheets and the data book. The conditions at the place of application must comply with all specifications for the filter used.

# Marning

- It shall be ensured that only qualified persons (electricity specialists) are engaged on work such as planning, assembly, installation, operation, repair and maintenance. They must be provided with the corresponding documentation.
- Danger of electric shock. Filters contain components that store an electric charge. Dangerous voltages can continue to exist at the filter terminals for longer than five minutes even after the power has been switched off.
- The protective earth connections shall be the first to be made when the filter is installed and the last to be disconnected. Depending on the magnitude of the leakage currents, the particular specifications for making the protective earth connection must be observed.
- Impermissible overloading of the filter or filter, such as with circuits able to cause resonances, impermissible voltages at higher frequencies etc. can lead to bodily injury and death as well as cause substantial material damages (e.g. destruction of the filter housing).
- Filters must be protected in the application against impermissible exceeding of the rated currents by overcurrent protective devices.
- In case of leakage currents >3.5 mA you shall mount the PE conductor stationary with the required cross section before beginning of operation and save it against disconnecting. For leakage currents I<sub>L</sub><sup>1</sup> ≤10 mA the PE conductor must have a KU value<sup>2</sup> of 4.5<sup>3</sup>; for leakage currents I<sub>L</sub> >10 mA the PE conductor must have a KU value of 6<sup>4</sup>.
- Output chokes and output filters must be protected in the application against impermissible exceeding of the component temperature.
- The converter output frequency must be within the specified range to avoid resonances and uncontrolled warming of the output chokes and output filters.
- Because the product can become very hot during operation, there is the risk of burns if touched. The product can remain hot for some time after the power is switched off!

- A value of KU = 4.5 with respect to interruptions is attained with: a) permanently connected protective earth connection ≥1.5 mm<sup>2</sup> and b) a protective earth connection ≥2.5 mm<sup>2</sup> via connectors for industrial equipment (IEC 60309-2)
- 4) KU = 6 with respect to interruptions is achieved for fixed-connection lines  $\geq 10 \text{ mm}^2$  where the type of connection and installation correspond to the requirements for PEN conductors as specified in relevant standards.

<sup>1)</sup>  $I_L$  = leakage current let-go

<sup>2)</sup> The KU value (symbol KU) is a classification parameter of safety-referred failure types designed to ensure protection against hazardous body currents and excessive heating.



# for leakage current compensation

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant chapters of the databook.

Торіс	Instructions	Reference chapter (data book), paragraph
Selecting a filter	When selecting a filter, it is mandatory to observe the rated data of the equipment (such as its rated input current, rated voltage, harmonic content etc.) as well as the derating instructions in Chapters 9 and 10.	Selection guide for converter filters
Rated voltage	When power distribution systems deviating from the symmetric TN-S system is to check the suitability of the filters and the allowed voltages including the fault cases.	Power distribution systems, 7
Protection from residual voltages Discharge resistors	Active parts must be discharged within 5 s to a voltage of less than 60 V (or 50 $\mu$ C). If this limit cannot be observed due to the operating mode, the hazardous point must be permanently marked in a clearly visible way.	
	Filters which are not permanently connected (e.g. when the test voltage is applied to the filter at the incoming goods inspection) must be discharged after the voltage has been switched off.	Safety regulations, 6.2
Installing and removing of filters Installation	When installing and removing our filters, a voltage-free state must be set up and secured with observance of the five safety rules described in EN 50110-1.	, ,
Use in IT systems	The special features of the IT system ("first fault case" and other fault cases) shall be observed.	Power distribution system (network types), 7.6
Safety notes on leakage currents	The filter leakage currents specified in the data book are intended for user information only.The maximum leakage current of the entire electrical equipment or appliance has to be limited for safety reasons. Please obtain the applicable limits for your application from the relevant regulations, provisions and standards.	8.4 Leakage current,
Voltage derating Hazards caused by overloading the filters	If the permissible limits for the higher-frequency voltages at the filter are exceeded, the filter may be damaged or destroyed.	Voltage derating, 9.8
Current derating at elevated ambient temperatures	Non-observance of the current derating may lead to overheating and consequently represents a fire hazard.	Current derating, 10.1



B84233A1500R000

#### for leakage current compensation

Торіс	Instructions	Reference chapter (data book), paragraph
Protective earth connection at operating currents >250 A	For operating currents greater than 250 A, we recommend the PE connection to be set up between the feed (filter: line) and output (filter: load) not via the PE terminal bolt in the filter housing.	instructions,
Mounting position	Note the mounting position of the filters! It must always be ensured that natural convection is not impaired.	•
Long motor cables	Long motor cables cause parasitic currents in the installation. The cable lengths indicated for the output chokes and output filters serve for orientation. The user must check the technical parameters and especially the choke temperatures for the respective application.	Mounting instructions, point 15

## **Display of ordering codes for TDK Electronics products**

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.

Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.



# for leakage current compensation

# Symbols and terms

Symbol	English	German
α	Insertion loss	Einfügungsdämpfung
C <sub>R</sub>	Rated capacitance	Bemessungskapazität
C <sub>x</sub>	Capacitance X capacitor	Kapazität X-Kondensator
C <sub>Y</sub>	Capacitance Y capacitor	Kapazität Y-Kondensator
$\Delta V$	Voltage drop (input to output)	Spannungsabfall im Filter
dv/dt	Rate of voltage rise	Spannungsanstiegsgeschwindigkeit
f	Frequency	Frequenz
f <sub>M</sub>	Converter output frequency	Motorfrequenz
f <sub>P</sub>	Pulse frequency	Pulsfrequenz
f <sub>R</sub>	Rated frequency	Bemessungsfrequenz
f <sub>res</sub>	Resonant frequency	Resonanzfrequenz
I <sub>C</sub>	Current through capacitor	Strom durch Kondensator
I <sub>LK</sub>	Filter leakage current	Filter-Ableitstrom
I <sub>max</sub>	Maximum current	Maximalstrom
I <sub>N</sub>	Nominal current	Nennstrom
I <sub>op</sub>	Operating current (design current)	Betriebsstrom
I <sub>pk</sub>	Rated peak withstand current	Bemessungs-Stoßstromfestigkeit
l <sub>q</sub>	Capacitive reactive current	Kapazitiver Blindstrom
I <sub>R</sub>	Rated current	Bemessungsstrom
ls	Interference current	Störstrom
Ľ	Inductance	Induktivität
L <sub>R</sub>	Rated inductance	Bemessungsinduktivität
L <sub>stray</sub>	Stray inductance	Streuinduktivität
PL	Power loss	Verlustleistung
R	Resistance	Widerstand
R <sub>is</sub>	Insulation resistance	Isolationswiderstand
R <sub>typ</sub>	DC resistance, typical value	Gleichstromwiderstand, Richtwert
T <sub>A</sub>	Ambient temperature	Umgebungstemperatur
T <sub>max</sub>	Upper category temperature	Obere Kategorietemperatur
T <sub>min</sub>	Lower category temperature	Untere Kategorietemperatur
T <sub>B</sub>	Rated temperature	Bemessungstemperatur
U <sub>k</sub>	Refered voltage drop in %	Bezogener Spannungsabfall in %
V <sub>eff</sub>	RMS voltage	Effektivspannung
V <sub>K</sub>	Voltage drop	Spannungsabfall
V <sub>LE</sub>	Voltage line to earth; voltage line to ground	Spannung Phase zu Erdpotential
V <sub>N</sub>	Nominal voltage	Nennspannung
V <sub>R</sub>	Rated voltage	Bemessungsspannung
V <sub>peak</sub>	Peak voltage	Spitzenspannung
V <sub>test</sub>	Test voltage	Prüfspannung
V <sub>X</sub>	Voltage over X capacitor	Spannung über X-Kondensator
V <sub>Y</sub>	Voltage over Y capacitor	Spannung über Y-Kondensator
XL	Inductive reactance	Induktiver Blindwiderstand
Z	Impedance	Scheinwidertand
Z	Impedance, absolute value	Scheinwiderstand (Betragswert)



The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.



#### Important notes

- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10