


# Chokes for Power Lines

# Material Data Sheet

<b>Product Class:</b>	<b>Ring Core Double Choke</b> <b>B82725S2***N00x</b>	
<b>Date</b>	<b>14.10.2011</b>	
IMDS ID if available		
<b>Version:</b>	<b>06</b>	

Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance	TMPS** [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
<b>Active Part</b>	Ceramic	4B	Manganese Zinc Ferrite	100	12645-49-7	43.4	
	Duromer	2C	Epoxy (EP)	100	25068-38-6	1.3	
	Heavy Metal	1C	Cu	100	7440-50-8	45.7	
	Duromer	2C	Polyurethane (PUR)	100	68400-67-9	2.4	
<b>Encapsulation and Mounting</b>	Thermoplastic	2A	Polycarbonate (PC)	90	25766-59-0	3.8	
			Glass fiber	10	65997-17-3		
	Thermoplastic	2A	Polyethylene terephthalate (PET)	100	25038-59-9	0.9	
	Duromer	2C	Phenoplast	100	9003-35-4	2.0	
<b>Termination</b>	Heavy Metal	1C	Cu	100	7440-50-8	0.3	
	Heavy Metal	1C	Sn	100	7440-31-5	0.1	
<b>Label</b>	Polymer	2C	Polyethylenterephthalate (PET)	100	25038-59-9	0.1	
	Polymer	2C	Acrylic resin	100	37325-11-4		X
<b>Sum in total:</b>						<b>100.0</b>	

Size W x L x H [max. in mm] <b>20.5 x 40.4 x 37</b>	Weight [approx. in g] <b>55</b>	Part Number <b>B82725S2xxxN00x</b>
---	---------------------------------------	---------------------------------------

**Not part of a Product Class**

<b>Contact</b>	Dr. Johann Reindl, MAG EPQM	<b>Important remarks:</b> 1) The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906) Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated. 2) This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. EPCOS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.
<b>Division</b>	EPCOS AG, Magnetics Business Group (MAG)	
<b>Address</b>	Rosenheimer Strasse 116b, 81669 Munich	
	Tel: +49 89 54020 3030 mailto: johann.reindl@epcos.com	
*) others: (not declarable or prohibited substances acc. GADSL)		
**) typical mass percentage of substance		

**The products set forth herein are "RoHS-compatible".** RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8<sup>th</sup>, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

**RoHS - Exemptions for the Product Class / Product according to Annex III: (  valid  not valid )**

- no exemptions;**
- Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;
- Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;
- Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;
- Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);
- Exemption 7 (c)-I: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;
- Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;
- Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;
- Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;
- Other Exemption than above .....