


Aluminium Electrolytic Capacitor

Material Data Sheet

Product Class	Capacitors for pulse application with snap-in terminals	Remark: This material datasheet is valid for the part numbers contained in the Data Book 2019. In case of special (B4****S****) or obsolete capacitors please contact our sales department 
Date	29.08.2019	
IMDS ID if available		
Version	04	

Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance	TMPS** [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Light Metals	1B	Aluminium	100	7429-90-5	44	
	Acids, Bases, Salts	6F	Ethylene glycol	80	107-21-1	25	
	Acids, Bases, Salts	6F	Others*)	20	-		
	Thermoplastics	2A	Polypropylene	100	9003-07-0	0,1	
	Paper, Cardboard	5C	Cellulose	100	9004-34-6	11,9	
Encapsulation	Light Metals	1B	Aluminium	100	7429-90-5	11	
	Paper, Cardboard	5C	Cellulose	56	9004-34-6	2,7	
	Duromer	2D	Phenolic plastic	44	-		
	Elastomer	2B	EPDM rubber	41,5	25038-36-2	1,3	
	Inorganic, solid	4A	Silicon dioxide	13	7631-86-9		
	Inorganic, solid	4A	Kaolinite	28,5	1318-74-7		
	Lubricant	6B	Paraffin	10,5	8012-95-1		
	-	-	Others *)	6,5	-		
	Thermoplastics	2A	Polyvinyl chloride or Polyethylene terephthalate or without insulation	90	9002-86-2 25038-59-9	3,0	
		others*)	10				
Termination	Iron and Steel	1A	Iron	100	7439-89-6	1	
	Heavy Metals	1C	Copper	100	7440-50-8	<0,1	
	Heavy Metals	1C	Tin	100	7440-31-5	<0,1	

Sum in total: 100

sizes D x L [mm]	weight range [g]	sizes D x L [mm]	weight range [g]	sizes D x L [mm]	weight range [g]	sizes D x L [mm]	weight range [g]	part numbers
22 x 45	20	30-30,5 x 50	46	35 x 55	81	40 x 40	60	B43406 / B43416
25 x 55	32			35 x 65	95	40 x 70	120	
25 x 70	50			35 x 80	110	40 x 105	190	
25 x 85	60					45 x 60	136	
						45 x 105	190	

Not Part of a Product Class

Contact	Ivett Bálint
Division	SZ LQM
Address	Csaba utca 30. H-9700 Szombathely / Hungary
	Tel: +36 94 522 226
	mailto: ivett.balint@tdk-electronics.tdk.com

Important remarks:

- The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated.
- This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.

*) others: (not declarable or prohibited substances acc. GADSL)

**) typical mass percentage of substance

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

RoHS - Exemptions for the Product Class / Product according to Annex III: (valid not valid)

- no exemptions;**
- Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;
- Exemption 6 (b): Lead as an alloying element in aluminum containing up to 0,4 % lead by weight;
- Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;
- Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);
- Exemption 7 (c)-I: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;
- Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;
- Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;
- Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;
- Other Exemption than above