


Inductor

Material Data Sheet

Product Class	ERU19 SMD B82559AxxxxA019	
Date	22.06.2018	
IMDS ID if available		
Version	02	

Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance	TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Ceramic	4B	Manganese Zinc Ferrite	100	1264549-7	70.6	
	Heavy Metal	1C	Cu	100	7440-50-8	16.1	
	Elastomer	2B	Polyurethane (PUR)	100	68400-67-9	0.9	
Encapsulation	Thermoplastic	2A	Phenoplast	35-50	9003-35-4	7.2	
			Glass fiber	50-65	65997-17-3		
	Duromer	2C	Epoxy (EP)	100	25068-38-6	0.1	
Termination	Heavy Metal	1C	Cu	100	7440-50-8	4.2	
	Heavy Metal	1C	Sn	100	7440-31-5	0.9	
Sum in total:						100	

Size W x L x H [max. in mm]	Weight [approx. in g]	Part Numbers	Size W x L x H [max. in mm]	Weight [approx. in g]	Part Numbers
20.5x19.9x8.8	9.8	B82559A2102A019	20.5x19.9x9.0	10.3	B82559A3152A019
20.5x19.9x10.2	11.1	B82559A4222A019	20.5x19.9x11.3	12.7	B82559A5332A019
20.5x19.9x8.8	9.4	B82559A6682A019	20.5x19.9x8.8	9.6	B82559A7103A019
20.5x19.9x9.6	10.7	B82559A9153A019	20.5x19.9x10.2	11.6	B82559A0203A019
20.5x19.9x10.9	12.7	B82559A5472A019	20.5x19.9x11.3	13.0	B82559A0303A019

Not Part of a Product Class	
Contact	Dr. Johann Reindl, MAG EPQM
Division	TDK Electronics AG, Magnetics Business Group (MAG)
Address	Rosenheimer Strasse 116b, 81669 Munich
	Tel: +49 89 54020 3030 mailto: johann.reindl@tdk-electronics.tdk.com
*) others: (not declarable or prohibited substances acc. GADSL)	
**) typical mass percentage of substance	
Important remarks:	
1) The declaration limit is 0.1% as defined by IEC PAS 61906. Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated.	
2) This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.	

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

RoHS - Exemptions for the Product Class / Product according to Annex III: (valid not valid)

no exemptions;

Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;

Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;

Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;

Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);

Exemption 7 (c)-I: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectric devices, or in a glass or ceramic matrix compound;

Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;

Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;

Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

Other Exemption than above