

## **Aluminium Electrolytic Capacitor**

## **Material Data Sheet**

app lug			citors for pulse eation with sold	obsolete capacitors pl	Remark: This material datasheet is valid for the part numbers contained in the Data Book 2019. In case of special (B4****S****) or obsolete capacitors please contact our sales department					
		29.08.	2019							
IMDS ID if available					~					
Version 10		10								
					1	(				
Product Part (IMDS: semi component)	Material Class (IMDS: Mat		Material (Classification) VDA 231	Substance	ubstance		CAS if applicable	typical mass o material [wt-%]	of Traces see 1)	
Active Part	Light Me	tals	1B	Alumin	ium	100	7429-90-5	44		
	Acids, Bases, Salts		6F	Ethylene	glycol	80	107-21-1	05		
	Acids, Bases, Salts		6F	Other	Others*)		-	25		
	Thermoplas tics		2A	Polypropylene		100	9003-07-0	0,1		
	Paper, Cardboard		5C	Cellulose		100	9004-34-6	11,9		
Encapsulation	Light Metals		1B	Aluminium		100	7429-90-5	11		
	Paper, Cardboard		5C	Cellulose		56	9004-34-6	2,7		
	Duromer		2D	Phenolic	plastic	44	-			
	Elastomer		2B	EPDM ru	ıbber	41,5	25038-36-2	1,3		
	Inorganic, solid		4A	Silicon di	oxide	13	7631-86-9			
	Inorganic, solid		4A	Kaolin	ite	28,5	1318-74-7			
	Lubricant		6B	Paraf	fin	10,5	8012-95-1			
	-		-	Others *)		6,5	-			
	Thermoplas tics		2A	Polyvinyl chloride or Polyethylene terephthalate or without insulation		90	9002-86-2 25038-59-9 -	3,0		
				others	5*)	10				
Termination	Heavy Metal		1C	CuZn	CuZn37		-	1		
	Heavy Metals		1C	Copper		100	7440-50-8	<0,1		
	Heavy Metals		1C	Tin		100	7440-31-5	<0,1		
							Sum in total:	100		
sizes D x L [mm] weight range [r   35 x 45 56   35-35,8 x 50 75   35-35,8 x 65-65,8 82   35-35,8 x 70 88   35-35,8 x 80 92   35-35,8 x 85 98   35-35,8 x 90 101			sizes D x L [mm] 35-35,8 x 105 35-35,8 x 110 40-40,8 x 40 40-40,8 x 55 40 x 60 40-40,8 x 65-65,8 40-40,8 x 70	$\begin{array}{cccccccccccccccccccccccccccccccccccc$		<b>ht range [g]</b> 143 150 180 190 90 136 190	sizes D x L [mm] 45 x 105 50 x 75 50 x 85 50-50,8 x 115,8	weight range [g] 260 180 240 340	part numbers B43405 / B43406 B43415	
Not Part of a Pr			40-40,8 x 75	140						
Contact	Ivett Bálin				Important rem	arks:				
	SZ LQM					Important remarks:   1) The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are				
	Sz LQM Csaba utca 30. H-9700 Szombathely / Hungary							percentage of 0.1 %		
	Tel: +36 94 522 226 mailto: ivett.balint@tdk- electronics.tdk.com					ial Data Sheet		es of the respective pro		

Umbrella Specification Rev 5.02.1a, based on ZVEI Layout, TDK Electronics AG, Dept. TQ, 03/2019



**) typical mass p	percentage of substance or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY FOR ANY PURPOSE.
The products se	et forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of
	EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.
RoHS - Exempti	ions for the Product Class / Product according to Annex III: ( ☑ valid  □ not valid )
	······································
no exemptions;	
Exemption 6 (a):	Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;
Exemption 6 (b):	Lead as an alloying element in aluminum containing up to 0,4 % lead by weight;
Exemption 6 (c):	Copper alloy containing up to 4 % lead by weight;
Exemption 7 (a):	Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);
Exemption 7 (c)-I:	Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;
Exemption 7 (c)-II:	Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;
Exemption 7 (c)-III:	Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;
<b>— — — — — — — — — —</b>	I and in colders to complete a visible electrical concertion between companying of a and conject within interpreted size/ii Flip Objectory

Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

Other Exemption than above .....