Attracting Tomorrow



CeraCharge[™]

Backup battery for real time clock



CeraCharge[™] as backup battery for real time clock (RTC)





- RTCs have to continue counting the time during energy interruption and for that need a back up source of energy
- CeraCharge™ is the ideal back up energy solution for RTC, offering many opportunities of process/product optimizations to designers

Advantages of CeraCharge™

- Longer life time (>15 years)
- Miniaturized (SMD EIA1812) and maintenance free battery
- Wide temperature range (no leak, no burn and no explode)
- Replaces Coin and Li batteries and super cap (electrolytic / ADLC)
- 100% lead free = RoHs-conform

Key questions

- RTC type?
- Backup period? <35 days
- Voltage threshold? <1.4 V
- Standby current?
 <1 μA
- No. of cycles?

Specifications

Nominal voltage 1.5 V

Operating voltage 0 to 1.6 V_{op}

Nominal capacity 100 µAh

Nominal discharge current 20 µA

Operating temperature -20 to +80 °C








CeraCharge[™] as backup battery for real time clock (RTC)





- RTCs have to continue counting the time during energy interruption and for that need a back up source of energy
- CeraCharge™ is the ideal back up energy solution for RTCs, offering many opportunities of process/product optimizations to designers



1) Voltage regulator: XC6206 (TOREX)

2) Schotky barrier diode: RB530SM-30T2R (ROHM)

CeraCharge[™] as backup battery for real time clock (RTC)





