

NTC

Material Data Sheet

Product Class	Glass encapsulated Sensor, coated B575*1G*
Date	22.08.2019
IMDS ID if available	
Version	04

Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance	TMPS** [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Ceramic	3B	Mn ₂ O ₄	64	1317-35-7	0,4	
			NiO	17	1313-99-1		
			Co ₃ O ₄	15	1308-06-1		
			Dopants*)	4			
Termination	Noble Metal	1D	Au	95	7440-57-5	0,1	
			Glass frit (Pb-B-silicate)	5			
Leads	Iron and Steel	1A	Fe	53	7439-89-6	46,5	
			Ni	47	7440-02-0		
	Heavy Metal	1C	Cu	100	7440-50-8	8	
Encapsulation	Glass	3A	SiO ₂	34	14808-60-7	12	
			K ₂ O	6	12136-45-7		
			PbO	57	1317-36-8		
			Dopants*)	3			
Coating	Thermoplast	2A	Thermoplastic fluoropolymer	100		33	
Sum in total:						100	

sizes [mm]	weight range [g]	part numbers:
Ø0,9 x 66	0,04	G541 / G1541
Ø1,4 x 73	0,06	G551 / G1551
Ø2,4 x 71	0,14	G561 / G1561

Not Part of a Product Class

Contact	Mr. Heinz Strallhofer
Division	TPS
Address	8530 Deutschlandsberg, AUSTRIA
	Tel: +43 3462 800 2589 mailto: heinz.strallhofer@tdk-electronics.tdk.com

*) others: (not declarable or prohibited substances acc. GADSL)
 **) typical mass percentage of substance

Important remarks:

- The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated.
- This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

RoHS - Exemptions for the Product Class / Product according to Annex III: (valid not valid)

- no exemptions;
- Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;
- Exemption 6 (b): Lead as an alloying element in aluminum containing up to 0,4 % lead by weight;
- Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;
- Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);
- Exemption 7 (c)-I: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;
- Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;
- Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;
- Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;
- Other Exemption than above