

Chokes for Power Lines

Material Data Sheet

Product Class:	Ring Core Double Choke
	B82724J****N***
	(Vertical Version)
Date	26.07.2021
IMDS ID if available	
Version:	11

Parts with Full Compound

Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance		TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Ceramic	4B	Manganese Zinc Ferrite		100	12645-49-7	46.6	
	Polymer	2C	Epoxy (EP)		100	25068-38-6	1.5	
	Heavy Metal	1C	Cu		100	7440-50-8	12.8	
	Polymer	2C	Polyurethane (PUR)		100	68400-67-9	0.7	
Encapsulation and Mounting	Polymer	0.4	Polycarbonate (PC)		89.8	25971-63-5	11.5	
		2A	Glass fiber		10	65997-17-3		
			PFBS		0.2	29420-49-3	1	
	Polymer	2C	Polyurethane (PUR)		100	68400-67-9	26.2	
	Heavy Metal	1C	Sn		100	7440-31-5	0.1	
Termination		1C	Cu		62	7440-50-8		
	Heavy Metal	1C	Ni		18	7440-02-0	0.5	
		1C	Zn 20 7440-66-0		7440-66-6			
	Heavy Metal	1C	Ni		100	7439-89-6		Х
	Heavy Metal	1C	Sn		100	7440-31-5	0.1	
	•	•				Sum in total:	100.0	
Size W x L x H [max. in mm] 18,5 x 31,3 x 33,2	Weight [approx. in g] 33-39	B82724J8103N040 B82724J8612N040 B82724J8302N040 B82724J2142N021 B82724J2302N021	B82724J8742N040 B82724J8672N040 B82724J8332N040 B82724J2512N020 B82724J2222N021	Part Numbers B82724J8322N040 B82724J8482N040 B82724J8252N040 B82724J2182N021 B82724J8432N040	B82724J8202N040 B82724J2222N020			



Parts with Economic Compound

Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance		TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Ceramic	4B	Manganese Zinc Ferrite		100	12645-49-7	58.4	
	Polymer	2C	Epoxy (EP)		100	25068-38-6	1.8	
	Heavy Metal	1C	Cu		100	7440-50-8	16.1	
	Polymer	2C	Polyurethane (PUR)		100	68400-67-9	0.8	
Encapsulation and Mounting	Polymer	-	Polycarbonate (PC)		89.8	25971-63-5	14.4	
		2A	Glass fiber		10	65997-17-3		
			PFBS		0.2	29420-49-3	1	
	Polymer	2C	Polyurethane (PUR)		100	68400-67-9	7.6	
	Heavy Metal	1C	Sn		100	7440-31-5	0.1	
Termination		1C	Cu		62	7440-50-8		
	Heavy Metal	1C	Ni		18	7440-02-0	0.7	
		1C	Zn		20	7440-66-6		
	Heavy Metal	1C	Ni		100	7439-89-6		Х
	Heavy Metal	1C	Sn		100	7440-31-5	0.1	
	·	•	•			Sum in total:	100.0	
Size W x L x H [max. in mm]	Weight [approx. in g]			Part Numbers				
18,5 x 31,3 x 33,2	28	B82724J2501N001 B82724J2202N001 B82724J2402N001	B82724J2102N001 B82724J2252N001 B82724J2402N020	B82724J2102N021 B82724J2252N020 B82724J2502N001	B82	724J2142N001 724J2272N020 724J2602N001	B82724J210 B82724J233 B82724J260	32N001

Contact	Dr. Johann Reindl, MAG EPQM			
Division	TDK Electronics AG, Magnetics Business Group (MAG)			
Address	Rosenheimer Strasse 116b, 81669 Munich			
	Tel: +49 89 54020 3030	mailto:		
		johann.reindl@tdk-electronics.tdk.com		
*) others: .(not declarable or prohibited substances acc. GADSL)				

Important remarks:

- The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906) Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not
- This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

RoHS - Exemptions for the Product Class / Product according to Annex III: (☑ valid □ not valid)

☑ no exemptions;

□ Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;

☐ Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;

☐ Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;

□ Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);

□ Exemption 7 (c)-1: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;

☐ Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher; ☐ Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;

☐ Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

☐ Other Exemption than above ...

^{**)} typical mass percentage of substance