

## **Chokes for Data and Signal Lines**

## **Material Data Sheet**

Product Class:		SMD Double Choke RK4 B82790C0/S0*** 03.11.2016		882790 S513 N 7383							
						-					
IMDS ID											
if available  Version:  0											
		01									
Product Part (IMDS: semi component)	Material (IMDS: I		Material (Classification) VDA 231	Substance			TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)	
Active Part	Ceramic		4B	Nickel Zinc Ferrite			100	12645-49-7	20.5		
	Duromer		2C	Parylene			100	25722-33-2	0.3		
	Heavy Metal		1C	Cu			100	7440-50-8	10.7		
	Elastomer		2B	Polyurethane (PUR)			100	9009-54-5	0.6		
Encapsulation	Thermoplastic			Phenylenesulfide (PPS)			60	25212-74-2	60.4		
and Mounting			2A	Glass fiber			40	65997-17-3			
	Thermoplastic		2A	Silicone (SI)			100	63148-62-9	3.3		
	Heavy Metal		1C	Sn			100	7440-31-5	0.1		
Termination	Heavy Metal		1C	Cu			94	7440-50-8	4.0		
			1C	Sn			6	7440-31-5			
	Heavy Metal		1C	Ni			100	7440-02-0		Х	
	Heavy Metal		1C	Sn			100	7440-31-5	0.1		
			•	<b>Sum in total</b> : 100.0						l	
Size W x L x H [max. in mm] 6.0 x 7.1 x 4.9	[appro	ight x. in g] <b>36</b>	Part Numbers  B82790C0*** B82790S0***								
Not part of a p	roduct cla	ss									
		Reindl, MA		Important remarks:							
	TDK Electronics AG, Magnetics Business Group (MAG)					The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906) Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not					
Address	Rosenheimer Strasse 116b, 81669 Munich  Tel: +49 89 54020 3030 mailto:				otherwise regulated  This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are						
*) others: .(not declarable or prohibited substances acc. GADSL)  **) typical mass percentage of substance					based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARNANTY, WHETHER EXPRESS, IMPLIED OR						

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

## RoHS - Exemptions for the Product Class / Product according to Annex III: ( ☑ valid ☐ not valid )

## ☑ no exemptions;

□ Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;

☐ Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;

☐ Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;

☐ Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);

□ Exemption 7 (c)-l: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;

☐ Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;

☐ Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;

□ Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

□ Other Exemption than above .....

STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.