

MKP Film Capacitor

Material Data Sheet

Product Class	MKP Motor run round B32335xxseries	<u> 1</u>
Date	17/04/2019	
IMDS ID if available	NA	25.005.21 No.
Version	5.02.1a (03/2019)	& P FPCOS CC

Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance	TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Thermoplastic	2A	PP	100	9003-07-0	34.4	
	Light Metal	1B	AL	6	7429-90-5	0.0	
	Heavy Metal	1C	Zn	94	7440-66-6	9.8	
Encapsulation	Light Metal	2B	Al	100	7429-90-5	14.7	
	Thermoplastic	2A	Polyamide 66 or	100 or	32131-17-2 or		
	Thermoplastic Filler Material Flame Retardant Inorganic solid	2A 5A Not available 4A	Polyamide 6 Fiber glass Brominated flame retardants Sb2O3	35 30 25 10	25038-54-4 65997-17-3 Not available 1309-64-4	12.5	
	Elastomer	2C	Silicon Silica	90 10	68083-18-1 7631-86-9	0.6	
	Duromer	2D	Polyurathan	100		22.2	
Termination	Iron & Steel	1a	Fe	94	7439-89-6		
	Heavy Metal	1c	Cu	4	7440-50-8	3.5	
	Heavy Metal	1c	Sn	2	7440-31-5		
	Heavy Metal	1c	Sn	99.3	7440-31-5	1.6	
	Heavy Metal	1c	Cu	0.7	7440-50-8	1.0	
Mounting Part	Iron & Steel	1a	Fe	92	7439-89-6	0.7	
	Heavy Metal	1c	Zn	8	7440-66-6	0.7	
					Com in totals	100	

				Gain in total.
sizes []	weight range []	sizes []	weight range []	sizes [] weight
30 x 52	62	40 x 103	154	range []
30 x 68	65	40 x 130	179	50 x 80 177
30 x 73	74	45 x 78	146	50 x 92 209
30 x 93	86	45 x 83	156	50 x 105 232
40 x 68	99	45 x 103	193	50 x 132 280
40 x 78	113	45 x 130	232	53 x 80 194
40 X 70	110	40 X 100	202	53 x 105 302

Not Part of a Product Class

Contact	Mr. M. Surendrababu		
Division	AC, R&D Film Capacitor		
Address	TDK India Pvt. Ltd.		
	E 22/25, 25/1, MIDC, Satpur, Nashik, INDIA -422007		
	Tel: +91 253 2205 210	mailto:surendrababu.m@tdk- electronics.tdk.com	

^{*)} others: .(not declarable or prohibited substances acc. GADSL)

Important remarks:

- The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are
 product parts, substances etc. that are below a percentage of 0.1 % by weight, if not
 otherwise regulated.
- This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

^{**)} typical mass percentage of substance



###