


Attracting Tomorrow




# CeraLink

Ceramic capacitors for fast-switching power electronic circuits






**TDK Electronics AG**  
Piezo & Protection Devices Business Group  
Munich, Germany  
August 2024


# Capacitor Technology Requirements Moving to Wide Bandgap



# CeraLink: Special Behavior 1/2


## Some differences to MLCC

Linear	Ferroelectric	Antiferroelectric
MLCC class I	MLCC class II	CeraLink
		



## Feature: Positive bias behavior

- Increasing capacitance with DC bias between 0 V and  $V_{op}$
- Best in class capacitance density at operating point ( $V_{op}$  &  $T_{op}$ )



# CeraLink: Special Behavior 2/2

## At high temperature

- Operating temperature up to +150 °C
- Low losses at high temperature
- Low leakage current
- No thermal runaway
- Generally low self-heating AND self-heating supports CeraLink to come to temperature for good performance

## At high frequency


- Optimal frequency in the range of 100 kHz to 1 MHz
- Minimal ESR due to low-loss copper electrodes and HF-suited mechanical construction
- Typ. ESR @ 25 °C, 1 MHz\*: 3 to 45 mΩ
- Typ. ESL\*: 2 to 4 nH
- Very high dV/dt ratios possible
- Temperature decrease with rising frequency

Due to low losses at high temperature and high frequency, CeraLink can carry more current under these conditions

Measurement condition	MKP film capacitor	MLCC class II (BTO)	CeraLink
Typical capacitance density @ DC link voltage, 20 V <sub>RMS</sub> , 25 °C	0.7 μF/cm <sup>3</sup>	2.5 μF/cm <sup>3</sup>	4.9 μF/cm <sup>3</sup>
Typical current rating per capacitance @ 100 kHz, 105 °C	< 1 A/μF	< 4.5 A/μF	11 A/μF

\* varies with series and voltage class

# CeraLink: Product Portfolio and Outlook



Series	Rated voltage		
	500 V	700 V	900 V
Low profile <b>LP (L / J-style)</b>	1 $\mu\text{F}$	0.5 $\mu\text{F}$	0.25 $\mu\text{F}$
Flex assembly <b>FA2 / FA3</b>	2 / 3 $\mu\text{F}$	1 / 1.5 $\mu\text{F}$	0.5 / 0.75 $\mu\text{F}$
Flex assembly <b>FA10</b>	10 $\mu\text{F}$	5 $\mu\text{F}$	2.5 $\mu\text{F}$
2220 series <b>2220</b> Soft termination	0.25 $\mu\text{F}$ @ h 1.4 mm *		0.056 $\mu\text{F}$ @ h 1.6 mm *

\* also available as standard termination

# CeraLink: Ideal for Demanding Applications (Examples)



**High-voltage applications in xEVs**




**Power supplies for medical equipment**



**Test and measurement**




**Drives**



**Welding**



**Traction (SiC)**



# CeraLink: Known Customer Applications

## Markets


### Automotive

- On-board chargers (OBC)
- DC-DC converters
- Auxiliary inverters for xEVs (HV compressors, HV pumps, HV heaters)
- Power modules for inverters

### Industry


- Energy storage systems
- Power converters
- Solar inverters
- Drive inverters
- Power supplies like UPS, isolated power supplies

### WBG power modules



CeraLink allows low inductive commutation loops as it is small, likes higher temperatures, and has low parasitics  
 → allowing fast switching transitions and keeping voltage **overshoots low**.  
 → Fast switching transitions result in **low switching losses** with WBG power semiconductors (SiC, GaN).

## EV charging landscape



# CeraLink: Ideal for Demanding Applications

## Key Facts


### Known customer applications

#### Automotive

- OBC
- DC/DC
- Auxiliary inverters for xEV (HV compressor, HV pump, HV heater)
- Power modules for inverters

#### Industry

- Drives
- Energy storage systems
- Power converters
- Solar inverters
- Power supplies like UPS, isolated power supply



- Suitable for HV designs like **400 V/800 V**
- Increasing capacitance with DC bias and best in class capacitance density at operating point ( $V_{op} + T_{op}$ )
- Supports **miniaturization** with low inductive design


### Basic facts

Qualification based on AECQ-200  
 Manufacturing site in EU (Deutschlandsberg, AT)  
 Quality management system according to IATF 16949:2016  
 Soldering method: Reflow



### Unique features

Innovative anti-ferroelectric ceramic material (positive bias behavior)  
 High cooling efficiency due to high thermal conductivity  
 Good self-regulating properties



### Resulting advantages

High capacitance density  
 High current capability  
 Low ESL (typ. 3 nH)  
 Low losses at high frequencies and high temperatures (up to +150 °C)  
 Very high dV/dt ratios possible

→ **Ideal as snubber, filter capacitor or flying capacitor for SiC and GaN applications**





[www.tdk-electronics.tdk.com](http://www.tdk-electronics.tdk.com)