

PTC

Material Data Sheet

Product Class	B59xxxCxxxx						
Date 18.12.2019							
IMDS ID if available							
Version 5.06							
Product Part (IMDS: semi component)	Material Class (IMDS: Material)	Material (Classification) VDA 231	Substance	TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Ceramic	3B	Ba-titanates Pb-titanates Sr-titanates Ca-titanates	69 15 10 5	12047-27-7 12060-00-3 12060-59-2 12049-50-2	67.8	
			others*)	1	12043 00 2		
Termination	Heavy Metal	1C12	Cu	100	7440-50-8	0.09	
	Heavy Metal	1C14	Ni	100	7440-02-0	0.06	
	Heavy Metal	1C2	Cr	100	7440-47-3	0.05	
Solder	Heavy Metal	1C15	Pb +) Sn	93 5	7439-92-1 7440-31-5	6	
			Ag	2	7440-22-4		
Leads	Heavy Metal	1C12	Cu	100	7440-50-8	21.1	
	Heavy Metal	1C8	Sn	100	7440-31-5	0.9	
Encapsulation	Organic, solid	4B1	Silicone Lacquer	100		4	
					Sum of total	100	
sizes [mm] 24.5x1 24.5x1	weight range [g] 3.6 3.6	material numbers B59910C0120* B59910C0160*		sizes [mm] 24 x 2.5 24 x 2.5	weight range [g] 7.6 7.6	material numbers B59810C0120* B59810C0160*	
24.5x1	3.6	B59915C*		24 x 2.5	7.6	B59811C0135*	
20x1	2.2	B59910C0130*		20 x 2.5	4.96	B59810C0130*	
16x1	1.5	B59930C0130*		16x2.5	3.3	B59830C0130*	
10x1	0.73	B59950C0130*		12 x 2.5	1.9	B59840C0130*	

	Not	nart	of a	Product	Class
ı	IVOL	part	uı a	riouuci	viass

5x1

3x1

Contact	Ronner Christoph			
Division	PPD Q QM			
Address	8530 Deutschlandsberg, AUSTRIA			
	Tel: +43 3462 800 2139	mailto: functional.ppd-eqpm.db@tdk-electronics.tdk.com		
*) -th (a-t-da-da-abla -a-a-blifted -a-b-t CADOL)				

B59960C0130*

B59970C0130*

B59980C0130*

*) others: .(not declarable or prohibited substances acc. GADSL)

0.55

0.47

0.22

+) listed in the Candidate list of Substances of Very High Concern acc. to Regulation 1907/2006/EC

B59850C0130*

B59860C0130*

B59870C0130*

B59880C0130*

2) This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

10 x 2.5

8 x 2.5

5 x 2.5

3 x 2.5

Important remarks:

1.5

10

0.57

0.28

RoHS - Exemptions for the Product Class / Product according to Annex III: (☑ valid ☐ not valid)

no exemptions;

- □ Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;
- ☐ Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;
- $\hfill \Box$ Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;
- ☑ Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);
- Exemption 7 (c)-1: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;
- ☐ Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;
- ☐ Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;
- □ Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;
- ☐ Other Exemption than above

^{**)} typical mass percentage of substance

The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated.