

**Product Brief** 

### Point of Care Devices

### Passive electronics components solutions for medical diagnostics and personal healthcare

Point of Care (PoC) devices are very valuable as they provide the ability to perform diagnostic tests close to the individual. An electronic PoC device needs reliable components during its development and subsequent validation by the manufacturer for its performance. Some of these devices include glucose testing meters, blood analyzers, blood pressure monitors, disease testing devices, etc. TDK offers a wide variety of electronic components for use in many different PoC devices.

### **Applications**

- · Coagulation testing devices
- Glucose testing meters
- Blood analyzers
- Handheld ultrasound units
- Pulse oximeters
- DNA analyzers
- Cholesterol/lipid test devices
- Infectious disease testing devices
- Blood pressure monitors
- Alcohol and drug testing units

### **Products**

### **Ceramic Capacitors**

- Disc ceramic for EMI
- General purpose MLCCs
- 3-terminal filters

### Protection Devices

- Surge arresters
- Multilayer varistors
- TVS diodes

sensors

- Chip NTC thermistors
- PTC limit temperature

### Sensors

- BioMEMS
- Temperature sensors
- Pressure sensors
- Humidity sensors

### **RF** Components

- Chip antennas
- Bandpass filters
- Baluns
- Diplexers/triplexers

### **Power Products**

- Solar cells
- Wireless charging coils
- μPOL™ DC-DC converters


### Piezo Products

- Haptic actuators
- Buzzers & sounders
- Stack actuators

### Magnetics

- Transformers
- Power inductors
- Filters





This schematic represents a general PoC device, listed components offer guidance that could help during the design and development of these devices.

Product details	Technical data	Features	Series	1	2	3	4	
Sensors								
BioMEMs	Micro and nano meter structures in silicon, glass, and flexible substrates Multiple metal and coating types	Foundry services and design support	Custom design	•				(
Pressure Sensor Dies	Pressure: 0 40 bar Operating temperature: -40 +150 °C Size: 0.65 x 0.65 mm 2.05 x 2.05 mm	Available for absolute, gauge and back side absolute measurements     Various features on request	B58600, B58601			•		
Humidity Sensors	Accuracy assurance: 20 85% RH at +25 °C Nominal accuracy: ±5% RH Operating voltage: 5 V DC	Sensor units with built-in circuits     Highly accurate     Characteristics are stable over a wide temperature range	CHS-MSS			•		

Product overview								
Product details	Technical data	Features	Series	1	2	3	4	5
Protection Devices					i			
Surge Arresters	DC spark-over voltage: 75 500 V Nom. discharge current 8/20 µs: 0.5; 2; 5; 20 kA	<ul> <li>2-electrode square design</li> <li>Low capacitance</li> <li>High insulation resistance</li> <li>Available in EIA 1812, 1206, 0805, 2.8 x 3.5 mm, and 4.1 x 6.2 mm</li> </ul>	S15, S20, S30, G30, S80		•	•	•	
SMD Varistors	Size (IEC): 0402 2012 Voltage: 6.8 (4.76 8.84) 39 (35 43) V DC (1 mA)	<ul> <li>No polarity, due to symmetrical current- voltage characteristics</li> <li>Excellent electrostatic absorption capability</li> </ul>	B72530, B72540 B72500, B72590 B72660 AVRH, AVRM		•	•	•	
TVS Diodes	ESD protection to IEC 61000-4-2 Maximum contact discharge voltage up to 24 kV	Bidirectional protetion of I/O devices     Low clamping voltage type available	B74111, B74121	•	•	•	•	
Chip NTC Thermistors	B constant: 3250 4750 K ±1% (+25/+125 °C) Nominal resistance value: 22 Ω 1 MΩ (@ 25 °C)	Lead-less terminal electrodes and electroplating (Ni-Sn)     Good stability of resistance value after soldering	NTCSP, NTCG, B57**	•	•	•	•	
Voltage Protection	Breakdown voltage (1 mA): 8 (6.4 9.6) V/8 (6.4 9.6), 27 (21.6 32.4) V ESD clamp voltage: 25/25, 60 max. V	Outstanding ESD absorption and protection characteristic (based on IEC 61000-4-2, Contact-8 kV)	SGNE		•	•	•	
PTC Limit Temperature Sensors	Max. voltage: 30 V Rated resistance: <100 $\leq$ 330 V T <sub>sense</sub> : +60 +160 °C	Available as SMD	B59421, B59641, B59721, B59404, B59601, B59701			•		
Ceramic Capacitors								
General High Cap	Size (IEC): 0402 5750 Rated voltage: 4 50 V Capacitance: 0.5 pF 100 µF	Wide range of case size and superior dimension precision     Available rating up to 50 V	C (SMD)	•	•	•	•	
MEGACAP	Size (IEC): 3225 7563 Rated voltage: 16 1 kV Capacitance: 1 nF 100 µF	Advanced design for 2 to 3x capacitance for greater efficiency     Improved vibration and thermal/mechanical stress performance	CKG, CAA (SMD)	•	•	•	•	
Mid/High Voltage	Rated voltage E <sub>ac</sub> : X1: 440 V, Y1: 400 V/300 V Capacitance: 3 pF 10 nF	Flame-resistant, reinforced outer insulation prevents potential hazards     Halogen-free external resin coating	CS, CD, CK45 (Leaded)	•	•	•	•	
3-terminal Filters	Size (IEC): 1005 3216 Rated voltage: 4 100 V Capacitance: 22 pF 22 µF	Reduction in ESR, ESL, and impedance due to the feed-through structure	CKD, YFF	•	•	•	•	

1 User interface 2 Power management 3 Main unit 4 Connectivity 5 Mems

Product overview								
Product details	Technical data	Features	Series	1	2	3	4	5
RF Components								
Chip Antennas	Size (I x w x t): 0.65 x 0.5 x 0.3 1.6 x 0.8 x 0.4 mm	Single and Dual band versions Compact, low-profile design Omni-directional	ANT				•	
Filters (BPF, HPF, LPF)	Size (I x w x t): 0.65 x 0.5 x 0.3 2.5 x 2.0 x 1.0 mm	Low loss versions     High attenuation versions     Passbands from 900 MHz     to 8 GHz	DEA, TFS				•	
Baluns	Size (I x w x t): 0.65 x 0.5 x 0.3 3.2 x 2.5 x 2.3 mm	Chip balun transformers developed for 50, 75, 100 Ω impedance	АТВ, ННМ				•	
Diplexers	Size (l x w x t): 1.0 x 0.5 x 0.33 2.5 x 2.0 x 1.0 mm	Multiple band combinations     High attenuation/low loss options     Typical usage 2.4 GHz / 5 GHz	DPX, TFS				•	
Triplexers	Size (I x w x t): 2.0 x 1.25 x 0.75 2.5 x 2.0 x 1.0 mm	Multiple band combinations     Low loss, high isolation	TPX				•	
RF Inductors	Size (IEC): 04021005 Rated current: 50 1200 mA Inductance: 0.2 560 nH	Achieves high Q characteristics     Equivalent to an air-core wire wound inductor	MHQ, MLG				•	
Power Management								
CeraCharge® SMD Solid State Batteries	EIA 1812 package size Capacitance of 100 μAh Rated voltage: 1.4 V	Easy placement and processing using reflow soldering techniques	B7318		•			
Solar Cells	Thickness: 0.2 mm Sheet bending capability: Ø20 mm	<ul> <li>Thin, lightweight, flexbile</li> <li>Output stability in low and dim light</li> <li>Customizable to various shapes</li> </ul>	BCS		•			
Wireless Power Transfer	WPT coils available in various sizes Electrical characteristics vary by size	Flexible sheet type is used     Custom design is     available based on     requirements	WT, WR	•	•			
μPOL™ Power Module	Very small footprint Output curent rated at 3 to 12A Operating temperature range from -40 +125 °C Size (I x w x t): 3.3 x 3.3 x 1.62 mm, 5.8 x 4.9 x 1.71 mm	High current density of more than 1000 A per cubic inch     Scalable and highly configurable with mutli- time programmable memory	FS14		•		•	





Product overview								
Product details	Technical data	Features	Series	1	2	3	4	5
Magnetics								
SMT Power Inductors	Size (IEC): 3012 12577 Inductance: 0.18 470 µH Rated current: 280 mA 46 A Temperature: up to +150 °C	<ul> <li>High rated DC current</li> <li>High reliability with welding connection</li> <li>Ferrite shielded component</li> </ul>	CLF, SPM, VLS, MLP, MLH, TFM, TMS, PLEA B82477, B82559, B82462, B82464, B82472	•	•	•		
SMD / SMT Inductors (Coils)	Size (IEC): 1005 3225 Inductance: 0.047 680 µH Rated current: 2 1150 mA Temperature: up to +150 °C	Magnetically shielded / suitable for high-density mounting     Very high current handling     Best DC superimposition characteristics     Lowest DC resistance     Excellent effect mainly on the decoupling of power circuits	B82422 MLF, MLZ NLV, NLCV, NLFV	•	•	•	•	
Common Mode Filters	Size (IEC): 1211 2520 Impedance: 300 1000 V (100 MHz) Rated current: 0.15 8 A	<ul><li>Miniaturized wire-wound chip-type filter</li><li>Extremely effective noise</li><li>suppression</li></ul>	ACM1211, ACM2520	•	•	•	•	
Power Line Chokes	Rated current: 0.4 2.8 A Rated inductance: 0.4 47 mH Rated voltage: 250 V	High resonance frequency due to special winding technique     VDE and UL approvals	B82721, B82723	•	•	•	•	
Signal Transformers	Size (IEC): 3232, 4532 Inductance (at 100 kHz/DC bias = 8 mA) 170 200 µH min.	Compatible with 10BASE-T, 100BASE-TX, and 1000BASE-T	ALT3232, ALT4532	•	•	•	•	
Flexield Noise Suppression Ferrite Shield	Dimensions: 300 x 200 mm Thickness: 0.025 0.2 mm Recommended frequency range: 0.1 MHz 10 GHz	<ul> <li>Highly flexible and shock-resistant</li> <li>Noise suppression across a wide frequency range</li> <li>Also available in Heat-resistant and Hybrid types</li> </ul>	IFL, IFF, IFM	•	•	•	•	

1 User interface 2 Power management 3 Main unit 4 Connectivity 5 Mems

Product details	Technical data	Features	Series	1	2	3	4	5
Piezo Products and Buzz	ers							
PiezoHapt™ Haptic Actuators	Vibration plate: 30 x 15 x 0.1 mm Operation voltage: 12 V P-P (±6 V) max.	Clear response/low-voltage drive Response in an instant Variegated vibration pattern	PHUA3015	•				
PowerHap™ Haptic Actuators	Acceleration (100 g mass): 2.5 35 G peak Operating voltage: -10 120 V Max. displacement: 32 230 µm Multiple sizes avaiable	Specific actuator feedback adjustable     Supports bipolar driving mode     Low power consumption     Qualified to AEC-Q200	B5410	•				
Piezoelectric Buzzers	Sound pressure: 60 70 dBA/10 cm min. (4 kHz)	Extremely low power consumption compared to electromagnetic units	PS1240	•				
Electromagnetic Buzzers	Rated voltage: 3 12 V (Eo-p) Operating temperature: -40 +85/-10 +70 °C	Good frequency response and high quality sound	SD16, SDR08540	•				
Piezo Stacks for Medical Dosing	Voltage: -10 +180 V Current: -30 +30 A Stroke at 160 V (s): 59 µm ±10 % Charge at 160 V (Q): 1.0 mC ±10 %	Highly efficient actuator design     Robust design avoids polarization cracks     High melting metal bond & reliability	B58004			•		

Important information: Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products. We expressly point out that these statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. It is incumbent on the customer to check and decide whether a product is suitable for use in a particular application. This publication is only a brief product survey which may be changed from time to time. Our products are described in detail in our data sheets. The Important notes (www.tdk-electronics.tdk.com/ImportantNotes) and the product-specific Cautions and warnings must be observed. All relevant information is available through our sales offices.