

Varistor

Material Data Sheet

| Date IMDS ID if available | 14.10.2019 | | | | | | |
|---|------------------------------------|---|---|------------------------|---|---------------------------------------|---------------|
| | | |] | | | | |
| available | 5.05 | | | | | | |
| Version | | | | | | | |
| | Material Class (IMDS: Material) | Material (Classification) VDA 231 | Substance | TMPS**) [wt%] | CAS if applicable | typical mass of material [wt-%] | Traces see 1) |
| Active Part - MLV | Ceramic | 3B | ZnO Bi2O3 Sb2O3 Co3O4 NiO others*) | 89 3 5 1 1 | 1314-13-2 1304-76-3 1309-64-4 1308-06-1 1313-99-1 | 9.4 | |
| Inner electrode - I MLV | Noble Metal | 1D7 | Ag Pd | 75-90 10-25 | 7440-22-4 7440-05-3 | 0.1 | |
| Termination - MLV | Composite | 4D | Ag Pt Glass frit (lead-boro-silicate) | 95.4 2 2.6 | 7440-22-4 7440-06-4 | 0.42 | |
| Ī | Heavy Metal | 1C8 | Sn | 100 | 7440-31-5 | 0.05 | |
| Ī | Heavy Metal | 1C14 | Ni | 100 | 7440-02-0 | 0.03 | |
| Active Part - MLCC | Ceramic | 3B | BaTiO3 others*) | 96 4 | | 34.85 | |
| Inner electrode - I | Heavy Metal | 1C14 | Ni | 100 | 7440-02-0 | 1.23 | |
| Termination - MLCC | Composite | 4D | Cu Glass frit | 94 6 | 7440-50-8 | 3.9 | |
| | Heavy Metal | 1C8 | Sn | 100 | 7440-31-5 | 0.62 | |
| | Heavy Metal | 1C14 | Ni | 100 | 7440-02-0 | 0.4 | |
| Solder | Heavy Metal | 1C15 | Sn Pb+) Ag | 1 98 1 | 7440-31-5 7439-92-1 7440-22-4 | 11 | |
| | Iron & Steel incl. Alloys | 1A | Fe | 100 | 7439-89-6 | 28.2 | |
| | Heavy Metal | 1C8 | Sn | 100 | 7440-31-5 | 1.2 | |
| | Heavy Metal | 1C14 | Ni | 100 | 7440-02-0 | 0.6 | |
| Encapsulation | Duromer | 2D | SiO2 | 49 | 60676-86-0 | 8 | |
| | | | Epoxy Brominated epoxy Sb2O3 | 35 12 2.5 | 25068-38-6 68929-70-1 1309-64-4 | | |
| | | | others*) | 1.5 | | | |
| | weight range [g] | material numbers | part numbers | | Sum of total | 100 | |
| 6.0 x 7.5 x 4.5 (Not part of a Product CI | 0.25 | B72527*V1 | SR6 | | | | |



Varistor

Material Data Sheet

| Hicap SHCV / X7R B725xx* (suffix V1) | | | | | |
|--|---|--|--|--|--|
| 14.10.2019 | | | | | |
| | | | | | |
| 5.05 | | | | | |
| Ronner Christoph | | Important remarks: | | | |
| PPD Q QM | | 1) The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are | | | |
| 8530 Deutschlandsberg, AUSTRIA | | product parts, substances etc. that are below a percentage of 0.1 % by weight, if not other regulated. | | | |
| ole or prohibited substances acc. GADSL) tage of substance te list of Substances of Very High Concern acc. to 16/EC | , | 2) This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE. | | | |
| ment and of the Council of June 8 th , 2011 on the r or the Product Class / Product according to Anti- ead as an alloying element in steel for machining purposes ead as an alloying element in aluminium containing up to 0 opper alloy containing up to 4 % lead by weight; | restriction of the use of certain nex III: (☑ valid □ not valid s and in galvanized steel containing 4,4 % lead by weight; | hazardous substances in electrical and electronic equipment. d) up to 0,35 % lead by weight; | | | |
| | B725xx* (suffix V1) 14.10.2019 5.05 Ronner Christoph PPD Q QM 8530 Deutschlandsberg, AUSTRIA Tel: mailto: +43 3462 800 2139 functional.ppd-eqpm.db@td Die or prohibited substances acc. GADSL) tage of substance te list of Substances of Very High Concern acc. to 6/EC Therein are "RoHS-compatible". RoHS-compatinent and of the Council of June 8th, 2011 on the for the Product Class / Product according to An ead as an alloying element in steel for machining purposes and as an alloying element in steel for machining purposes and as an alloying element in aluminium containing up to 60 copper alloy containing up to 4 % lead by weight. | B725xx* (suffix V1) 14.10.2019 5.05 Ronner Christoph PPD Q QM 8530 Deutschlandsberg, AUSTRIA Tel: mailto: +43 3462 800 2139 functional.ppd-eqpm.db@tdk-electronics.tdk.com ble or prohibited substances acc. GADSL) tage of substance tel list of Substances of Very High Concern acc. to 16/EC Therein are "RoHS-compatible". RoHS-compatible means that products are coment and of the Council of June 8 th , 2011 on the restriction of the use of certain or the Product Class / Product according to Annex III: (☑ valid ☐ not valid goad as an alloying element in steel for machining purposes and in galvanized steel containing goad as an alloying element in aluminium containing up to 0,4 % lead by weight; | | | |

Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;

Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;

Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC;

Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

Other Exemption 1 (c)-III: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;