

Varistor

Material Data Sheet

Product Class	SMD Varistor Monolithic (CU-Type) B726xxM*
Date	30.09.2019
IMDS ID if available	
Version	5.06

Product Part (IMDS: semi component)	Material Class (IMDS Material		Material (Classification) VDA 231	Subs	tance		TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Part Ceramic 3		3B	ZnO Bi2O3 Sb2O3 Co3O4 NiO others*)			89 4 3 1 1 2	1314-13-2 1304-76-3 1309-64-4 1308-06-1 1313-99-1	39,8	
Termination	Composite		4D	Ag 95			7440-22-4	0,2		
				Glass frit (boro-silicate) 5						
Solder	Heavy Metal		1C8	Sn 95 5				7440-31-5 7440-22-4	3	
Leads	Heavy Metal		1C12	Cu			100	7440-50-8	2,8	
	Heavy Metal		1C8	Sn			100	7440-31-5	0,2	
Encapsulation	Thermoplastic		2A	PPS	(CI content [wt	%] : 0,29%)	100	26125-40-6	54	
								Sum in total:	100	
sizes [mm] 8.0 x 6.3 10.2 x 8.0	weight range [g] 0.3 – 0.7 0.5 – 1.3	material number B7265xM* B7266xM*	part numbers CU3225* CU4032*		sizes [mm] 11.7 x 12.2	weight range [g] 1.0 – 3.0	material number B7267xM*	part numbers CU4648*		

Contact	Mr. Christoph Ronner				
Division	PPD Q QM				
Address	8530 Deutschlandsberg, AUSTRIA				
	Tel: +43 3462 800 2139	mailto: functional.ppd-eqpm.db@tdk-electronics.tdk.com			

^{*)} others: .(not declarable or prohibited substances acc. GADSL)

Important remarks:

- The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated.
- This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE.

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

RoHS - Exemptions for the Product Class / Product according to Annex III: (☑ valid ☐ not valid)

☑ no exemptions

□ Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;

☐ Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;

☐ Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;

□ Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);

☐ Exemption 7 (c)-1: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;

☐ Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;

☐ Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;

□ Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

☐ Other Exemption than above

^{**)} typical mass percentage of substance