

## Varistor

Product Class	Leaded MLV B72526R*						
Date	28.10.2020						
IMDS ID if available							
Version	ersion 5.01						
Product Part (IMDS: semi component)	Material Class (IMDS: Material)	<b>Material</b> (Classification) VDA 231	Substance	TMPS**) [wt%]	CAS if applicable	typical mass of material [wt-%]	Traces see 1)
Active Part	Ceramic	3B	ZnO Bi2O3 Sb2O3 Co3O4 NiO others*)	89 3 5 1 1 1	1314-13-2 1304-76-3 1309-64-4 1308-06-1 1313-99-1	14,1	
Inner Electrode	Noble Metal	1D7	Ag Pd	75-90 10-25	7440-22-4 7440-05-3	0,1	
Termination	Composite	4D	Ag Glass frit (boro-silicate)	90 10	7440-22-4	0,65	
	Heavy Metal	1C8	Sn	100	7440-31-5	0,09	
	Heavy Metal	1C14	Ni	100	7440-02-0	0,06	
Solder	Heavy Metal	1C15	Sn Pb +) Ag	1 98 1	7440-31-5 7439-92-1 7440-22-4	25	
Leads	Iron & Steel incl.	1A	Fe	100	7439-89-6	42,4	
	Heavy Metal	1C8	Sn	100	7440-31-5	1,8	
	Heavy Metal	1C14	Ni	100	7440-02-0	0,8	
Encapsulation	Duromer	2D	SiO2 Epoxy Brominated epoxy Sb2O3 others*)	49 35 12 2,5 1,5	60676-86-0 25068-38-6 68929-70-1 1309-64-4	15	
					Sum of total	100	
sizes [ mm] 6,0 x 7,5 x 4,0 Not part of a Product (	weight range [ g ] 0,20 - 0,25 Class	material numbers B72526R*	part numbers SR1206				

## Varistor



Product Class	Leaded MLV B72526R*
Date	28.10.2020
IMDS ID if available	
Version	5.01

Contact	Ronner Christoph		Important remarks:			
Division	PPD Q QM		1) The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are			
Address	8530 Deutschlandsberg,	AUSTRIA	product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise			
	Tel:	mailto:	regulated. 2) This Material Data Sheet contains typical values of the respective products set forth			
**) typical mass percentage of substance			2) This waterial bad sited contains typical values on the respective products set of the herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY			

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8<sup>th</sup>, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

## RoHS - Exemptions for the Product Class / Product according to Annex III: ( 2 valid D not valid )

no exemptions;

Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;

D Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;

Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;

Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);

Exemption 7 (c)-1: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;

Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;

Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;

Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;

Other Exemption than above