

Aluminum Electrolytic Capacitors

Axial-lead and soldering star capacitors – Selection chart

Date: December 2016

© EPCOS AG 2016. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

Selection chart

Automotive – Axial-lead and soldering star capacitors

Low-voltage series

125 ... 140 °C

Ultra compact

<p>B41690/B41790 25 ... 40 V 125 °C / > 5000 h 140 °C / > 2000 h</p>
Page

125 ... 150 °C

Very high ripple current

<p>B41689/B41789 25 ... 63 V 125 °C / > 10000 h 150 °C / > 2000 h</p>
Page

High-voltage series

125 ... 140 °C

Compact

<p>B41692/B41792 25 ... 75 V 125 °C / > 5000 h 140 °C / > 2000 h</p>
Page

Low ESR

<p>B41691/B41791 25 ... 63 V 125 °C / > 10000 h 150 °C / > 2000 h</p>
Page

High voltage

<p>B43693/B43793 140 ... 250 V 125 °C / > 2500 h</p>
Page

Very low ESR

<p>B41696/B41796 25 and 40 V 125 °C / > 3000 h</p>
Page

High reliability

<p>B41693/B41793 25 ... 100 V 125 °C / > 5000 h 150 °C / > 1000 h</p>
Page