

# **Ceramic transient voltage suppressors, CTVS**

## **Symbols and terms**

Date: April 2026

## Symbols and terms

### For ceramic transient voltage suppressors (CTVS)

| Symbol                   | Term                                             |
|--------------------------|--------------------------------------------------|
| $C_{\text{line,max}}$    | Maximum capacitance per line                     |
| $C_{\text{line,min}}$    | Minimum capacitance per line                     |
| $C_{\text{line,typ}}$    | Typical capacitance per line                     |
| $C_{\text{max}}$         | Maximum capacitance                              |
| $C_{\text{min}}$         | Minimum capacitance                              |
| $C_{\text{nom}}$         | Nominal capacitance                              |
| $\Delta C_{\text{nom}}$  | Tolerance of nominal capacitance                 |
| $C_{\text{typ}}$         | Typical capacitance                              |
| $f_{\text{cut-off,max}}$ | Maximum cut-off frequency                        |
| $f_{\text{cut-off,min}}$ | Minimum cut-off frequency                        |
| $f_{\text{cut-off,typ}}$ | Typical cut-off frequency                        |
| $f_{\text{res,typ}}$     | Typical resonance frequency                      |
| $I$                      | Current                                          |
| $I_{\text{clamp}}$       | Clamping current                                 |
| $I_{\text{leak}}$        | Leakage current                                  |
| $I_{\text{leak,max}}$    | Maximum leakage current                          |
| $I_{\text{leak,typ}}$    | Typical leakage current                          |
| $I_{\text{PP}}$          | Peak pulse current                               |
| $I_{\text{surge,max}}$   | Maximum surge current (also termed peak current) |
| LCT                      | Lower category temperature                       |
| $L_{\text{typ}}$         | Typical inductance                               |
| $P_{\text{diss,max}}$    | Maximum power dissipation                        |
| $P_{\text{PP}}$          | Peak pulse power                                 |
| $R_{\text{ins}}$         | Insulation resistance                            |
| $R_{\text{min}}$         | Minimum resistance                               |
| $R_{\text{S}}$           | Resistance per line                              |
| $R_{\text{S,typ}}$       | Typical resistance per line                      |
| $T_{\text{A}}$           | Ambient temperature                              |
| $T_{\text{op}}$          | Operating temperature                            |
| $T_{\text{op,max}}$      | Maximum operating temperature                    |
| $T_{\text{stg}}$         | Storage temperature                              |

## Symbols and terms

| Symbol                   | Term                                                       |
|--------------------------|------------------------------------------------------------|
| $t_r$                    | Duration of equivalent rectangular wave                    |
| $t_{\text{resp}}$        | Response time                                              |
| $t_{\text{resp,max}}$    | Maximum response time                                      |
| UCT                      | Upper category temperature                                 |
| V                        | Voltage                                                    |
| $V_{\text{BR,min}}$      | Minimum breakdown voltage                                  |
| $V_{\text{clamp,max}}$   | Maximum clamping voltage                                   |
| $V_{\text{DC,max}}$      | Maximum DC operating voltage (also termed working voltage) |
| $V_{\text{ESD,air}}$     | Air discharge ESD capability                               |
| $V_{\text{ESD,contact}}$ | Contact discharge ESD capability                           |
| $V_{\text{jump}}$        | Maximum jump-start voltage                                 |
| $V_{\text{RMS,max}}$     | Maximum AC operating voltage, root-mean-square value       |
| $V_V$                    | Varistor voltage (also termed breakdown voltage)           |
| $V_{\text{LD}}$          | Maximum load dump voltage                                  |
| $V_{\text{leak}}$        | Measurement voltage for leakage current                    |
| $V_{V,\text{min}}$       | Minimum varistor voltage                                   |
| $V_{V,\text{max}}$       | Maximum varistor voltage                                   |
| $\Delta V_V$             | Tolerance of varistor voltage                              |
| $W_{\text{LD}}$          | Maximum load dump energy                                   |
| $W_{\text{max}}$         | Maximum energy absorption (also termed transient energy)   |
| $\alpha_{\text{typ}}$    | Typical insertion loss                                     |
| $\tan \delta$            | Dissipation factor                                         |
| $e$                      | Lead spacing                                               |
| $\ll * \gg$              | Maximum possible application conditions                    |

All dimensions are given in mm.

The commas used in numerical values denote decimal points.

## Symbols and terms

### For CeraDiodes

| CeraDiode                | Semiconductor diode                                           |                                                                                           |
|--------------------------|---------------------------------------------------------------|-------------------------------------------------------------------------------------------|
| $C_{\max}$               |                                                               | Maximum capacitance                                                                       |
| $C_{\text{typ}}$         |                                                               | Typical capacitance                                                                       |
| $I_{\text{BR}}$          | $I_{\text{R}}, I_{\text{T}}$                                  | (Reverse) current @ breakdown voltage                                                     |
| $I_{\text{leak}}$        | $I_{\text{RM}}$                                               | (Reverse) leakage current                                                                 |
| $I_{\text{PP}}$          | $I_{\text{P}}, I_{\text{PP}}$                                 | Current @ clamping voltage; peak pulse current                                            |
| $P_{\text{PP}}$          | $P_{\text{PP}}$                                               | Peak pulse power                                                                          |
| $T_{\text{op}}$          |                                                               | Operating temperature                                                                     |
| $T_{\text{stg}}$         |                                                               | Storage temperature                                                                       |
| $V_{\text{BR}}$          | $V_{\text{BR}}$                                               | (Reverse) breakdown voltage                                                               |
| $V_{\text{BR,min}}$      |                                                               | Minimum breakdown voltage                                                                 |
| $V_{\text{clamp}}$       | $V_{\text{cl}}, V_{\text{C}}$                                 | Clamping voltage                                                                          |
| $V_{\text{clamp,max}}$   |                                                               | Maximum clamping voltage                                                                  |
| $V_{\text{DC}}$          | $V_{\text{RM}}, V_{\text{RWM}}, V_{\text{WM}}, V_{\text{DC}}$ | (Reverse) stand-off voltage, working voltage, operating voltage                           |
| $V_{\text{DC,max}}$      |                                                               | Maximum DC operating voltage                                                              |
| $V_{\text{ESD,air}}$     |                                                               | Air discharge ESD capability                                                              |
| $V_{\text{ESD,contact}}$ |                                                               | Contact discharge ESD capability                                                          |
| $V_{\text{leak}}$        | $V_{\text{RM}}, V_{\text{RWM}}, V_{\text{WM}}, V_{\text{DC}}$ | (Reverse) voltage @ leakage current                                                       |
| - *)                     | $I_{\text{F}}$                                                | Current @ forward voltage                                                                 |
| - *)                     | $I_{\text{RM}}, I_{\text{RM,max}} @ V_{\text{RM}}$            | (Reverse) current @ maximum reverse stand-off voltage, working voltage, operating voltage |
| - *)                     | $V_{\text{F}}$                                                | Forward voltage                                                                           |

\*) Not applicable due to bidirectional characteristics of CeraDiodes.