

Surge arrester

Stacked surge arresters

Series/Type: LN8-A450DC-2 Ordering code: B88069X1983B102

Date: 2019-07-25

Version: 05

 $[\]odot$ TDK Electronics AG 2019. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



Stacked surge arresters

LN8-A450DC-2

Features

- Fast response time
- High current rating
- Stable performance over life
- Very low capacitance
- High insulation resistance
- Excellent SMD handling
- RoHS-compatible

Applications

DC power supply protection 24 V

Electrical specifications		Arrester only	w. capacitors ²⁾	Unit
DC spark-over voltage 1)		450 ±30	< 500	V %
Front of wave spark-over voltage at 6 kV, 1.2/50 µs - initial - after service life		< 1100 < 1500	< 780 < 1200	V V
DC operating voltage 3)	24 ±25		V _{DC} %	
Service life				
5 operations	50 Hz, 1 s	1		Α
10 operations [5× (+) & 5× (-)]	5/320 µs	25		Α
10 operations [5x (+) & 5x (-)]	8/20 µs	10		kA
2 operations	10/350 µs	3		kA
300 operations (+/– alternating polarity)	10/1000 µs	100		Α
Insulation resistance at 100 V _{DC}		> 10		$G\Omega$
Capacitance at 1 MHz		< 1		pF
Weight		~ 2.2		g
Operation and storage temperature		−40 +12 5		°C
Climatic category (IEC 60068-1)		40/125/21		
Marking, red positive		YY 24DC YY - Year of production 24DC - DC operating voltage		
Certifications		UL 1449 (E319264)		. 74 ° us

¹⁾ At delivery AQL 0.65 level II, DIN ISO 2859

Terms in accordance with IEC 61643-11.

PPD AB PD / PPD AB PM

²⁾ Refer to circuit diagram on page 3


³⁾ DC current source 30 A



Stacked surge arresters


LN8-A450DC-2

Circuit diagram (C1 = 100 pF to 470 pF)



Recommended capacitor: TDK C4520X7R3D471K130KA

Test circuit 10/350 µs or 8/20 µs circuit







Stacked surge arresters


LN8-A450DC-2

Dimensional drawing in mm





pad outline acc. to IPC-7351 (producibility level A; density level A)







tin-plated

Ordering code and packing advice

B88069X1983**B102** = 100 pcs. in foam trays





PPD AB PD / PPD AB PM Version: 05 / 2019-07-25




Stacked surge arresters

LN8-A450DC-2

Soldering parameter

Reflow soldering



Reflow profile features		Sn- Pb eutectic assembly	Pb-free assembly
Preheat and soak - Temperature min - Temperature max - Time Average ramp-up	T _{smin} T _{smax} t _{smin} to t _{smax}	100 °C 150 °C 60 120 s	150 °C 200 °C 60 180 s
rate	T_{smax} to T_p	max. 3 °C/ s	max. 3 °C/ s
Liquidous temperature Time at liquidous	T _L	183 °C 60 150 s	217 °C 60 150 s
Peak package body temperature *, Classification temperature **	T_p, T_C	220 235 °C **	245 260 °C **
Time (t _p) ** within 5 °C of the specified classification temperature (T _C)		20 s ***	30 s ***
Average ramp-down rate	T_p to T_{smax}	max. 6 °C/ s	max. 6 °C/ s
Time 25 °C to peak temperature		max. 6 min	max. 8 min

⁼ Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Surface mounted components (SMD) may exhibit a temporary increase in the DC spark-over voltage after the solder reflow process. The components will recover within 24 hours. There is no quality defect nor change in protection levels during the temporary change in DC spark-over voltage.

Cautions and warnings

- The follow current must be limited (see test circuit) so that the arrester can be properly extinguished when the surge has decayed. The arrester might otherwise heat up and ignite adjacent components.
- If the contacts of the surge arresters are defective, current load can cause sparks and loud noises.
- Surge arresters may become hot in the event of longer periods of current stress (burn risk). In the event of overload the connectors may fail or the component may be destroyed.
- Do not operate surge arresters in power supply networks, whose maximum operating voltage exceeds the minimum spark-over voltage of the surge arresters.
- Surge arresters must be handled with care and must not be dropped.
- Do not continue to use damaged surge arresters.
- The shown SMD pad dimensions represent a safe way to mount the arrester and are a recommendation of the manufacturer. During the reflow process it must be assured that no solder material reduces the insulation distance between the pads below the arrester.
- SMD surge arresters should be soldered within 24 month after shipment.

^{** =} For details please refer to JEDEC J-STD-020D.

^{*** =} Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.



Stacked surge arresters

LN8-A450DC-2

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.



Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
 - We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.
- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.



Important notes

8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10