




Sample Kit

D-Core Chokes

B82734R EMC for power lines



www.tdk-electronics.tdk.com


D-Core Chokes – EMC for power lines

L_N	mH	3.3	6.8	10	15	27
I_R	A	4.6	3.2	2.6	2.3	1.7
$L_{\text{stray,typ}}$	μH	17	35	53	80	140
R_{typ}	$\text{m}\Omega$	46	85	130	185	320
T_R	$^{\circ}\text{C}$	+40	+40	+40	+40	+40
Approx. weight	g	30	30	30	30	30
Ordering code	B82734R*	2462B030	2322B030	2262B030	2232B030	2172B030

Technical data

- Rated voltage 250 V AC
- Approx. 0.55% stray inductance for symmetrical interference suppression
- Low leakage due to closed core shape
- High pulse strength
- Low whirring noise
- Suitable for wave soldering
- Delivery mode: Blister tray in cardboard box
- UL and ENEC (VDE) approvals
- RoHS compatible

Vertical version



No polarity

IND2390-8-E

- 1) Tin tips permissible
- 2) Dimension does not include tin tip

Content: 3 pcs. per ordering code

3.3 mH



6.8 mH



10 mH



15 mH



27 mH



Important information: It is incumbent on the customer to check and decide whether a product is suitable for use in a particular application. Our products are described in detail in our data sheets. Our *Important notes* and the product-specific *Cautions and warnings* must be observed. All relevant information is available through our sales offices.