

SMT Power Inductors

Size 12.8 x 12.8 x 8.0 (mm)

Series/Type:B82477GOrdering code:B82477G4473M003Date:June 2012

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

②TDK

B82477G

B82477G4473M003

SMT Power Inductors

Size 12.8 x 12.8 x 8.0 (mm)

Rated inductance 47 µH

Construction

- Ferrite core
- Magnetically shielded
- Winding: enamel copper wire
- Winding: soldered to terminals

Features

- High mechanical stability
- Temperature range up to +125 °C
- Increased current handling capability compared to standard device B82477G4473M000 (I_{sat} +30%)
- Low DC resistance
- Suitable for lead-free reflow soldering
- RoHS-compatible

Applications

- Filtering of supply voltages
- Coupling, decoupling
- DC/DC converters

Terminals

- Base material CuSn6P
- Layer composition Ni, Sn (lead-free)
- Electro-plated

Marking

- Marking on component: Manufacturer, L value (µH, coded), manufacturing date (YWWD)
- Minimum data on reel: Manufacturer, ordering code, L value, quantity, date of packing

Delivery mode and packing unit

- 24-mm blister tape, wound on 330-mm reel
- Packing unit: 400 pcs./reel



公TDK


B82477G

B82477G4473M003

SMT Power Inductors


Size 12.8 x 12.8 x 8.0 (mm)

Dimensional Drawing and layout recommendation






IND0492-V-E



Dimensions in mm

Taping and packing

Blister tape and reel



Dimensions in mm



SMT Power Inductors

Size 12.8 x 12.8 x 8.0 (mm)

Technical data and measuring conditions

Rated inductance L _R	Measured with LCR meter Agilent 4284A at frequency f_L , 0.1 V, +20 °C			
Rated temperature T _R	+85 °C			
Rated current I _R	Max. permissible DC with temperature increase of \leq 40 K at rated temperature			
Saturation current I _{Sat}	Permissible DC with inductance decrease $\Delta L/L_0$ of approx. 10%			
DC resistance R _{typ}	Measured at +20 °C			
Solderability (lead-free)	Dip and look method Sn95.5Ag3.8Cu0.7: +(245 \pm 5) °C, (3 \pm 0.3) s Wetting of soldering area \geq 90% (based on IEC 60068-2-58)			
Resistance to soldering heat	+260 °C, 10 s			
Climatic category	55/125/56 (to IEC 60068-1)			
Storage conditions	ge conditions Mounted: $-55 \ ^{\circ}C \dots +125 \ ^{\circ}C$ Packaged: $-25 \ ^{\circ}C \dots +40 \ ^{\circ}C, \leq 75\% \ RH$			
Weight	Approx. 4 g			

Characteristics and ordering codes

L _R μΗ	Tolerance	f∟ MHz	I _R A	I _{sat} A	R _{typ} Ω	R_{max}	Ordering code
47	20% = M	0.1	3.00	5.00	0.051	0.055	B82477G4473M003


B82477G4473M003 B82477G

公TDK

SMT Power Inductors


Size 12.8 x 12.8 x 8.0 (mm)

Inductance derating versus DC superposition



Current derating I_{OP}/I_R versus ambient temperature T_A

(rated temperature $T_R = +85^{\circ}C$)



谷TDK

SMT Power Inductors

Size 12.8 x 12.8 x 8.0 (mm)

Cautions and warnings

- Please note the recommendations in our Inductors data book (latest edition) and in the data sheets.
 - Particular attention should be paid to the derating curves given there.
 - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not the housing.
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation

Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.

- The following points must be observed if the components are potted in customer applications:
 Many potting materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
 - It is necessary to check whether the potting material used attacks or destroys the wire insulation, plastics or glue.
 - The effect of the potting material can change the high-frequency behaviour of the components.
- Ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.
- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10