

Ring core chokes with iron powder core 250 V AC, 0.3 ... 3 A, 0.033 ... 1.2 mH, +60 °C

 Series/Type:
 B82623

 Date:
 July 2012

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



## Ring core chokes with iron powder core

Rated voltage 250 V AC/350 V DC Rated current 0.3 ... 3 A Rated inductance 0.033 ... 1.2 mH

#### Construction

- Ring core double choke
- Iron powder core with epoxy coating
- Polycarbonate case (UL 94 V-0)
- Polyurethane potting (UL 94 V-0)
- Sector winding

#### **Features**

- Effective suppression of differential-mode interferences at higher frequencies
- Moderate inductance decrease at current load
- Suitable for wave soldering
- Design complies with EN 60938-2 (VDE 0565-2) and UL 1283
- UL and ENEC (VDE) approvals 🔊 🕸 📤
- RoHS-compatible

## **Applications**

- Suppression of differential-mode interferences
- Compact switch-mode applications
- Reduction of harmonics and PFC

### **Terminals**

- Base material CuNi18Zn20
- Layer composition Ni, Sn
- Hot-dipped
- $\blacksquare$  Pins  $0.7 \times 0.7$  (mm)
- Lead spacing 15 × 25 (mm)

#### Marking

Manufacturer, approval signs and VDE standard number, ordering code, rated current, rated inductance, rated voltage, "GKC", graphic symbol, date of manufacture (YYWWD.internal ID code)

## **Delivery mode**


Blister tray in cardboard box





## Ring core chokes with iron powder core

## Dimensional drawing and pin configuration



Tolerances to ISO 2768-C unless otherwise noted. Dimensions in mm.



## Technical data and measuring conditions

Rated voltage V <sub>R</sub>	250 V AC (50/60 Hz) / 350 V DC			
Test voltage V <sub>test</sub>	1500 V AC, 2 s (winding/winding)			
Rated temperature T <sub>R</sub>	+60 °C			
Rated current I <sub>R</sub>	Referred to 50 Hz and rated temperature			
Rated inductance L <sub>R</sub>	Defined at zero DC current bias Measured with Agilent 4284A at 0.1 mA, +20 °C Measuring frequency: $L_R \le 1$ mH = 100 kHz $L_R > 1$ mH = 10 kHz Inductance is specified per winding.			
Inductance tolerance	±20% at +20 °C			
Inductance at rated current	Measured at DC magnetic bias with $I_R$ with Agilent 4284A at 0.1 mA, +20 °C, typical values Measuring frequency: $L_R \le 1$ mH = 100 kHz $L_R > 1$ mH = 10 kHz			
DC resistance R <sub>typ</sub>	Measured at +20 °C, typical values, specified per winding			
Solderability (lead-free)	Sn96.5Ag3.0Cu0.5: +(245 $\pm$ 5) °C, (3 $\pm$ 0.3) s Wetting of soldering area $\geq$ 95% (to IEC 60068-2-20, test Ta)			
Resistance to soldering heat (wave soldering)	+(260 ±5) °C, (10 ±1) s (to IEC 60068-2-20, test Tb)			
Climatic category	40/125/56 (to IEC 60068-1)			
Storage conditions (packaged)	–25 °C +40 °C, ≤ 75% RH			
Weight	Approx. 20 g			
Approvals	EN 60938-2, UL 1283			



## Ring core chokes with iron powder core

## Characteristics and ordering codes


I <sub>R</sub>	L <sub>R</sub>	L at I <sub>R</sub> , typ.	R <sub>typ</sub>	Ordering code	Approvals	
Α	mH	mH	Ω		<b>7/1</b>	<u> </u>
0.3	1.2	1.05	1.9	B82623G0001A003	×	×
0.5	1.0	0.75	1.1	B82623G0001A005	×	×
1	0.33	0.25	0.4	B82623G0001A008	×	×
2	0.082	0.062	0.1	B82623G0001A010	×	×
3	0.033	0.025	0.045	B82623G0001A011	×	×

x = approval granted




## Ring core chokes with iron powder core


## Impedance IZI versus frequency f (differential-mode) measured with windings in series at +20 °C, typical values




# Relative inductance $L_{op}/L_R$ versus relative current $l_{op}/l_R$ measured at +20 °C, typical values



## Impedance IZI versus frequency f (common-mode) measured with windings in parallel at +20 °C, typical values



## Current derating $I_{op}/I_R$ versus ambient temperature $T_\Delta$





## Cautions and warnings

## Current-compensated ring core double chokes

- Please note the recommendations in our Inductors data book (latest edition) and in the data sheets.
  - Particular attention should be paid to the derating curves given there. Derating must be applied
    in case the ambient temperature in the application exceeds the rated temperature of the
    component.
  - Ensure the operation temperature (which is the sum of the ambient temperature and the temperature rise caused by losses / self-heating) of the component in the application does not exceed the maximum value specified in the climatic category.
  - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not the housing.
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation.
  - Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.
- The following points must be observed if the components are potted in customer applications:
  - Many potting materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
  - It is necessary to check whether the potting material used attacks or destroys the wire insulation, plastics or glue.
  - The effect of the potting material can change the high-frequency behaviour of the components.
- Ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.



#### Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
  - We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.
- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10