

# NTC thermistors for temperature measurement

Probe assemblies

Series/Type: B57504K
Date: January 2018

© EPCOS AG 2018. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



Tomporatare measurement	20100 III
Probe assemblies	K504

#### **Applications**

 Temperature measurement in household appliances (e.g. dryers, dish washers, small appliances)

#### **Features**

- NTC thermistor potted in a medium-resistant stainless steel case
- Short thermal response time in water
- Wire heat-resistant up to 125 °C (XLPE-insulated wire)

Temperature measurement


#### **Options**

Alternative casing, cable lengths, cable material (PTFE), R/T characteristics and connectors available on request.

#### **Delivery mode**

Bulk

## **Dimensional drawing**



Dimensions in mm Approx. weight 2.3 g

#### General technical data

Climatic category	(IEC 60068-1)		20/125/42	
Upper category temperature	(wire)		125	°C
Maximum operating temperature	(sensor head)	$T_{op,max}$	150	°C
Resistance tolerance		$\Delta R_R/R_R$	±2	%
Rated temperature		$T_R$	70	°C
Dissipation factor	(in air)	$\delta_{th}$	approx. 2	mW/K
Thermal time constant	(in water)	$\tau_{a}$	< 2	s
Insulation resistance	(V = 500 V DC)	R <sub>ins</sub>	> 100	$M\Omega$
Test voltage	(t = 1 s)	$V_{test}$	1250	V AC

#### Electrical specification and ordering codes

$R_{70}$ $\Omega$	$R_{25}$ $\Omega$	No. of R/T characteristic	B <sub>25/100</sub> K	Ordering code
2055	10000	7003	3625 ±0.8%	B57504K0103A009



Temperature measurement	B57504K
Probe assemblies	K504

#### Reliability data

Test	Standard	Test conditions	$\Delta R_{25}/R_{25}$ (typical)	Remarks
Storage in dry heat	IEC 60068-2-2	Storage at max. operating temperature T: 150 °C t: 168 h Medium: air	< 3%	No visible damage
Storage in coldness		Storage at lower category temperature T: -20 °C t: 1000 h Medium: air	< 3%	No visible damage
Storage in damp heat, steady state		Temperature of air: 60 °C Relative humidity of air: 93% Duration: 1000 h	< 3%	No visible damage
Rapid temperature cycling (in water)		Lower test temperature: 15 °C Upper test temperature: 96 °C Dwell time: 30 s Time to change from lower to upper temperature: <10 s Number of cycles: 1000 Medium: water	< 3%	No visible damage
Vibration resistance	IEC 60068-2-6	Frequency range: 10 to 2000 Hz Amplitude: 1.5 mm, 10 <i>g</i> Linear sweep; X, Y and Z direction Duration: 3 × 2 h	< 3%	No visible damage
Natural falling test		Drop sensor 3 times from a height of 75 cm spontaneously onto hard surface	< 3%	No visible damage
Boiling test		Storage at 96 °C in water for 6 h, then natural cooling for 16 h	< 3%	No visible damage

#### Note

- Contact of NTC thermistors with any liquids and solvents shall be prevented. It must be ensured that no water enters the NTC thermistors (e.g. through plug terminals).
- Avoid dewing and condensation unless thermistor is specified for these conditions.



B57504K

K504

#### R/T characteristics

Probe assemblies

R/T No.	/T No.   <b>7003</b>							
T (°C)	$B_{25/100} = 3625$	K	T (°C)	$B_{25/100} = 3625$	K	T (°C)	$B_{25/100} = 3625$	K
	R <sub>T</sub> /R <sub>25</sub>	α (%/K)		R <sub>T</sub> /R <sub>25</sub>	α (%/K)		R <sub>T</sub> /R <sub>25</sub>	α (%/K)
-55.0	63.225	6.7	65.0	0.24049	3.2	185.0	0.013448	1.8
-50.0	45.46	6.5	70.0	0.20553	3.1	190.0	0.012297	1.8
-45.0	33.07	6.3	75.0	0.17637	3.0	195.0	0.011265	1.7
-40.0	24.324	6.0	80.0	0.15195	2.9	200.0	0.010338	1.7
-35.0	18.081	5.8	85.0	0.13141	2.9	205.0	0.009504	1.7
-30.0	13.575	5.6	90.0	0.11406	2.8	210.0	0.0087516	1.6
-25.0	10.29	5.4	95.0	0.099352	2.7	215.0	0.0080718	1.6
-20.0	7.8716	5.3	100.0	0.086837	2.7	220.0	0.0074567	1.6
-15.0	6.0739	5.1	105.0	0.076149	2.6	225.0	0.0068989	1.5
-10.0	4.7258	4.9	110.0	0.066989	2.5	230.0	0.0063925	1.5
-5.0	3.7062	4.8	115.0	0.059112	2.5	235.0	0.0059318	1.5
0.0	2.9287	4.6	120.0	0.052316	2.4	240.0	0.005512	1.5
5.0	2.3311	4.5	125.0	0.046433	2.4	245.0	0.005129	1.4
10.0	1.8684	4.4	130.0	0.041327	2.3	250.0	0.004779	1.4
15.0	1.5075	4.2	135.0	0.03688	2.3	255.0	0.0044586	1.4
20.0	1.224	4.1	140.0	0.032998	2.2	260.0	0.004165	1.4
25.0	1.0000	4.0	145.0	0.029598	2.2	265.0	0.0038955	1.3
30.0	0.82176	3.9	150.0	0.026612	2.1	270.0	0.0036478	1.3
35.0	0.67909	3.8	155.0	0.023984	2.1	275.0	0.0034199	1.3
40.0	0.56422	3.7	160.0	0.021665	2.0	280.0	0.0032098	1.3
45.0	0.47122	3.6	165.0	0.019613	2.0	285.0	0.003016	1.2
50.0	0.3955	3.5	170.0	0.017793	1.9	290.0	0.002837	1.2
55.0	0.33355	3.4	175.0	0.016176	1.9	295.0	0.0026714	1.2
60.0	0.2826	3.3	180.0	0.014735	1.8	300.0	0.002518	1.2



remperature measurement	BOTOGHI
5	L/E04

Probe assemblies K504

#### Cautions and warnings

Tomporature measurement

#### General

See "Important notes" on page 2.

#### Storage

- Store thermistors only in original packaging. Do not open the package prior to processing.
- Storage conditions in original packaging: storage temperature −25 °C ... +45 °C, relative humidity ≤75% annual mean, <95% maximum 30 days per annum, dew precipitation is inadmissible.</p>
- Do not store thermistors where they are exposed to heat or direct sunlight. Otherwise, the packing material may be deformed or components may stick together, causing problems during mounting.
- Avoid contamination of thermistor surface during storage, handling and processing.
- Avoid storage of thermistors in harmful environments like corrosive gases (SO<sub>x</sub>, Cl etc).
- Use the components as soon as possible after opening the original packaging.
- Solder thermistors within the time specified after shipment from EPCOS.
  For leaded components this is 24 months, for SMD components with nickel barrier termination 12 months, for leadless components this is 12 months, for SMD components with AgPd termination 6 months.

#### Handling

- NTC thermistors must not be dropped. Chip-offs or any other damage must not be caused during handling of NTCs.
- Do not touch components with bare hands. Gloves are recommended.
- Avoid contamination of thermistor surface during handling.
- Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.

#### Bending / twisting leads

A lead (wire) may be bent at a minimum distance of twice the wire's diameter plus 4 mm from the component head or housing. When bending ensure the wire is mechanically relieved at the component head or housing. The bending radius should be at least 0.75 mm.

#### Soldering

- Use resin-type flux or non-activated flux.
- Insufficient preheating may cause ceramic cracks.
- Rapid cooling by dipping in solvent is not recommended.
- Complete removal of flux is recommended.



B57504K

Temperature measurement

Probe assemblies K504

#### Mounting

- Ensure that no thermo-mechanical stress occurs due to production processes (curing or overmolding processes) when thermistors are sealed, potted or overmolded or during their subsequent operation. The maximum temperature of the thermistor must not be exceeded. Ensure that the materials used (sealing/potting compound and plastic material) are chemically neutral.
- Electrodes/contacts must not be scratched or damaged before/during/after the mounting process.
- Contacts and housing used for assembly with the thermistor must be clean before mounting.
- Ensure that adjacent materials are designed for operation at temperatures comparable to the surface temperature of the thermistor. Be sure that surrounding parts and materials can withstand the temperature.
- Avoid contamination of the thermistor surface during processing.
- The connections of sensors (e.g. cable end, wire end, plug terminal) may only be exposed to an environment with normal atmospheric conditions.
- Tensile forces on cables or leads must be avoided during mounting and operation.
- Bending or twisting of cables or leads directly on the thermistor body is not permissible.
- Avoid using chemical substances as mounting aids. It must be ensured that no water or other liquids enter the NTC thermistors (e.g. through plug terminals). In particular, water based substances (e.g. soap suds) must not be used as mounting aids for sensors.
- The use of no-clean solder products is recommended. In any case mild, non-activated fluxes should be used. Flux residues after soldering should be minimized.

#### Operation

- Use thermistors only within the specified operating temperature range.
- Use thermistors only within the specified power range.
- Environmental conditions must not harm the thermistors. Only use the thermistors under normal atmospheric conditions or within the specified conditions.
- Contact of NTC thermistors with any liquids and solvents shall be prevented. It must be ensured that no water enters the NTC thermistors (e.g. through plug terminals). For measurement purposes (checking the specified resistance vs. temperature), the component must not be immersed in water but in suitable liquids (e.g. perfluoropolyethers such as Galden).
- Avoid dewing and condensation unless thermistor is specified for these conditions.
- Bending or twisting of cables and/or wires is not permissible during operation of the sensor in the application.
- Be sure to provide an appropriate fail-safe function to prevent secondary product damage caused by malfunction.

This listing does not claim to be complete, but merely reflects the experience of EPCOS AG.

#### Display of ordering codes for EPCOS products

The ordering code for one and the same EPCOS product can be represented differently in data



Temperature measurement	B57504K
Probe assemblies	K504

sheets, data books, other publications, on the EPCOS website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.epcos.com/orderingcodes



Temperature measurement	B57504K
Probe assemblies	K504

# Symbols and terms

Symbol	English	German
A AWG	Area American Wire Gauge	Fläche Amerikanische Norm für Drahtquerschnitte
B B <sub>25/100</sub>	B value B value determined by resistance measurement at 25 °C and 100 °C	B-Wert B-Wert, ermittelt durch Widerstands- messungen bei 25 °C und 100 °C
$C_{th}$	Heat capacitance	Wärmekapazität
1	Current	Strom
N	Number (integer)	Anzahl (ganzzahliger Wert)
$egin{aligned} & P_{25} \ & P_{diss} \ & P_{el} \ & P_{max} \end{aligned}$	Maximum power at 25 °C Power dissipation Electrical power Maximum power within stated temperature range	Maximale Leistung bei 25 °C Verlustleistung Elektrische Leistung Maximale Leistung im angegebenenTemperaturbereich
$\begin{array}{l} \Delta R_{\text{B}}/R_{\text{B}} \\ \\ R_{\text{ins}} \\ R_{\text{P}} \\ \\ R_{\text{R}} \\ \Delta R_{\text{R}}/R_{\text{R}} \\ \\ R_{\text{S}} \\ \\ R_{\text{T}} \end{array}$	Resistance tolerance caused by spread of B value Insulation resistance Parallel resistance Rated resistance Resistance tolerance Series resistance Resistance at temperature T (e.g. R <sub>25</sub> = resistance at 25 °C)	Widerstandstoleranz, die durch die Streuung des B-Wertes verursacht wird Isolationswiderstand Parallelwiderstand Nennwiderstand Widerstandstoleranz Serienwiderstand Widerstand bei Temperatur T (z.B. R <sub>25</sub> = Widerstand bei 25 °C)
$T$ $\Delta T$ $t$ $T_A$ $T_{max}$ $T_{min}$ $T_{op}$ $T_R$	Temperature Temperature tolerance Time Ambient temperature Upper category temperature Lower category temperature Operating temperature Rated temperature	Temperatur Temperaturtoleranz Zeit Umgebungstemperatur Obere Grenztemperatur (Kategorietemperatur) Untere Grenztemperatur (Kategorietemperatur) Betriebstemperatur Nenntemperatur
T <sub>surf</sub> V V <sub>ins</sub> V <sub>op</sub> V <sub>test</sub>	Surface temperature  Voltage Insulation test voltage Operating voltage Test voltage	Oberflächentemperatur Spannung Isolationsprüfspannung Betriebsspannung Prüfspannung



Temperature measurement	B57504K
Probe assemblies	K504

Symbol	English	German
α	Temperature coefficient	Temperaturkoeffizient
Δ	Tolerance, change	Toleranz, Änderung
$\delta_{\text{th}}$	Dissipation factor	Wärmeleitwert
$\tau_c \\ \tau_a$	Thermal cooling time constant Thermal time constant	Thermische Abkühlzeitkonstante Thermische Zeitkonstante

### Abbreviations / Notes

Symbol	English	German
SMD	Surface-mounted devices	Oberflächenmontierbares Bauelement
*	To be replaced by a number in ordering codes, type designations etc.	Platzhalter für Zahl im Bestellnummern- code oder für die Typenbezeichnung.
+	To be replaced by a letter.	Platzhalter für einen Buchstaben.
	All dimensions are given in mm.	Alle Maße sind in mm angegeben.
	The commas used in numerical values denote decimal points.	Verwendete Kommas in Zahlenwerten bezeichnen Dezimalpunkte.



#### Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
  - We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.
- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.



#### Important notes

8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10