

PTC thermistors

Motorstart applications

Series/Type: A0590-A0100-A020 Ordering code: B59590A0100A020

Date: 2022-10-04

Version:

 $[\]odot$ TDK Electronics AG 2022. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



Motorstart applications

A0590-A0100-A020

Applications

Starting of single-phase compressor motors


Features

- Non leaded thermistor disk
- Migration-free silver metallization
- For clamp contacting, not suitable for soldering
- High thermal stability
- RoHS-compatible

Delivery mode

Trays

Dimensional drawing



D	16.0+/-0.2	mm
d	14.4+/-0.3	mm
th	3.2+/-0.2	mm
е	< 0.4	mm

Metallization according to drawing

Ordering code

B59590A0100A020



Motorstart applications


A0590-A0100-A020

General technical data

Max. operating voltage	V_{max}	350	V _{RMS}
Rated voltage	VR	230	V _{RMS}
Breakdown voltage @ T _{amb} =80 °C ¹)	VBD	> 560	V _{RMS}
Max. current at V _{max} ²⁾	I _{max}	6.0	ARMS
Max. current at V = 300 V _{RMS} ²⁾	I _{max}	8.0	ARMS
Residual current, V = 230 V _{RMS} , soak time 10 min ¹⁾	I _R	< 7.0	mA _{RMS}
Rated resistance (measured current <1 mA; 25+/-0.1 °C)	R(25 °C)	24.0+/-20%	Ω
Rated resistance (measured with sine voltage V_{p})	R(25 °C,141 V _p)	21.0+/-25%	Ω
Operating time, R_L = 30 Ω , V = 230 V_{RMS} 1)	t _S	0.30 - 0.60	s
Recovery time V = 230 V _{RMS} ; soak time 10 min ¹⁾	t _r	< 130	s
Reference temperature	T _{ref}	94 - 106	°C
Operating temperature range	Тор	-10 – 100	°C

¹⁾ Measurement conditions according to Product Specification RD.PL.006.01 (January 2002)

Allowed current as a function of voltage



²⁾ As per diagram on page 2



Motorstart applications

A0590-A0100-A020

Reliability


- Component must withstand reliability tests according to CECC 60738-1-3-003 (tests performed in ACC motor start housing)
- Component must withstand reliability tests according to Product Specification RD.PL.006.01 (January 2002), item 6.

Handling and Mounting Instructions

According to "Cautions and Warnings"

Packaging

PTCs are on carton trays (100 pieces each tray) as per following draft:



10 trays are stapled and put into outer carton which is sealed with a plastic foil.



Motorstart applications

A0590-A0100-A020

Cautions and warnings

General

- EPCOS thermistors are designed for specific applications and should not be used purposes not identified in our specifications, application notes and data sheets unless otherwise agreed with us during the design-in-phase.
- Ensure suitability of thermistor through reliability testing during the design-in phase. The thermistors should be evaluated taking into consideration worst-case conditions.

Storage

- Store thermistors only in original packaging. Do not open the package before storage.
- Storage conditions in original packaging: storage temperature -25 °C to +45 °C, relative humidity <75% annual mean, maximum 95%, dew precipitation is inadmissible.
- Avoid contamination of thermistors surface during storage, handling and processing.
- Avoid storage of thermistor in harmful environment with effect on function on long-term operation (examples given under operation precautions).
- Use thermistor within 6 months after delivery.

Handling

- PTCs must not be dropped. Chip-offs must not be caused during handling of PTCs.
- Components must not be touched with bare hands. Gloves are recommended.
- · Avoid contamination of thermistor surface during handling.

Soldering

- Use rosin-type flux or non-activated flux.
- Insufficient preheating may cause ceramic cracks.
- Rapid cooling by dipping in solvent is not recommended.
- Compete removal of flux is recommended.

Mounting

- Electrode must not be scratched before/during/after in the mounting process.
- Contacts and housing used for assembly with thermistor have to be clean before mounting.
 Especially grease or oil must be removed.
- When PTC thermistors are encapsulated with sealing material, the precautions given in chapter "Mounting instructions", "Sealing and potting" must be observed.
- When the thermistor is mounted, there must not be any foreign body between the electrode of the thermistor and the clamping contact.
- The minimum force of the clamping contacts pressing against the PTC must be 10 N.
- During operation, the thermistor's surface temperature can be very high. Ensure that adjacent components are placed at a sufficient distance from the thermistor to allow for proper cooling at the thermistors.



Motorstart applications

A0590-A0100-A020

 Ensure that adjacent materials are designed for operation at temperature comparable to the surface temperature of thermistor. Be sure that surrounding parts and materials can withstand this temperature.

Avoid contamination of thermistor surface during processing.

Operation

- Use thermistors only within the specified temperature operating range.
- Use thermistors only within the specified voltage and current ranges.
- Environmental conditions must not harm the thermistors. Use thermistors only in normal
 atmospheric conditions. Avoid use in deoxidizing gases (chlorine gas, hydrogen sulfide gas,
 ammonia gas, sulfuric acid gas etc), corrosive agents, humid or salty conditions. Contact with any
 liquids and solvents should be prevented.
- Be sure to provide and appropriate fail-safe function to prevent secondary product damage caused by abnormal function (e.g. use VDR for limitation of overvoltage condition).

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.

Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
 - We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.
- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.



Important notes

8. The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, InsuGate, LeaXield, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap, XieldCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2022-07