



Transformers


Transformers for IGBT/FET

Series/Type: E16 EMHV
Ordering Code: B78310A2546A003

Date: July 2026

Construction

- Ferrite core
- Gullwing pins (SMD)
- Plastic bobbin (UL94-V0, CTI $\geq$ 600)
- Plastic pick&place cap (CTI $\geq$ 175)
- Triple insulated wire
- Color of materials may vary



Features

- RoHS compatible
- Qualification: AEC-Q200 REV E
- Height: 13.8 mm max
- Suitable for lead-free reflow soldering as referenced in JEDEC-J-SDT 020F

Applications

- Isolated DC/DC converters
- Forward and Push-Pull Topology

Insulation Characteristics

- (N1, N2) / secondaries:
Creepage min. 3.5 mm
Clearance min. 3.2 mm
- Between secondaries:
Creepage min. 3.5 mm
Clearance min. 3.2 mm



Marking

- Product brand, middle block of ordering code, date code, pin1 marker, production place, identification code

Delivery Mode

- Blister tape
- Packing unit 140 pcs per reel


Dimensional drawing



IND2567-Y

Dimensions in mm


Recommended PCB Layout (Top View)



IND2568-Z

Dimensions in mm

Circuit diagram




Technical data and measuring conditions

specified @ 25°C if not mentioned otherwise, all values without tolerance are typical values

Inductance $L_{(N1+N2)}$	> 4 mH @ 10 kHz, 100 mV
Turns ratio N1 : N2 : N3 : N4 : N5 : N6 : N7 : N8	33 : 33 : 20 : 9 : 20 : 9 : 20 : 9
Leakage inductance $L_{\text{leak}(N1+N2)}$	10 μ H @ 10 kHz, 1 V, short (1,2,3,7,8,9,10,11,12)
Coupling Capacitance C_p (N1, N2) / (N3, N4, N5, N6, N7, N8)	$\leq$ 50 pF @ 10 kHz, 1 V, short (1,2,3,7,8,9,10,11,12)
Voltage time product $E \cdot dt$ (N1 or N2)	134 μ Vs @ $T \leq 150$ °C, $B_{\text{max}} = 220$ mT, $\Delta B = 220$ mT, unipolar
$R_{\text{DC} \cdot N1, N2}$	730 m Ω , 790 m Ω
$R_{\text{DC} \cdot N3, N5, N7}$	895 m Ω , 935 m Ω , 825 m Ω
$R_{\text{DC} \cdot N4, N6, N8}$	400 m Ω , 435 m Ω , 395 m Ω
High voltage test AC (N1, N2) / (N3, N4, N5, N6, N7, N8)	3125 V (50 Hz, 60 s), type test
High voltage test AC (N1, N2) / (N3, N4, N5, N6, N7, N8)	2500 V (50 Hz, 1 s), routine test
Partial discharge peak inception voltage (N1, N2) / (N3, N4, N5, N6, N7, N8)	Min. 1200 V, type test
Partial discharge peak extinction voltage (N1, N2) / (N3, N4, N5, N6, N7, N8)	Min. 960 V, type test
High voltage test AC (N3, N4) / (N5, N6) / (N7, N8)	1250 V (50 Hz, 60 s), type test
High voltage test AC (N3, N4) / (N5, N6) / (N7, N8)	1000 V (50 Hz, 1 s), routine test
Storage conditions	-25 °C ... +40 °C, humidity $\leq$ 75% RH
Resistance to reflow heat	In accordance with JEDEC J-STD-020F +245 °C ($T_{\text{Peak}} -5$ °C for 30 seconds)
Solderability (lead-free)	Sn96.5Ag3.0Cu0.5: +(245 $\pm$ 3) °C, (3 $\pm$ 0.3) s Wetting of soldering area $\geq$ 95% (to IEC 60068-2-58, test Td1, method 1)
Operating temperature range	-40 °C ... +150 °C (component)
Weight	Approx. 7 g


Taping and packing

Blister tape



Dimensions in mm

Reel



Dimensions in mm

Three isolated outputs

Cautions and warnings

- Please note the recommendations in our Inductors data book (latest edition), online catalogs and in the data sheets.
 - Particular attention should be paid to the derating curves, if given. Derating applies in the case the ambient temperature in application exceeds the rated temperature of the component.
 - Ensure the operation temperature of the component in application not to exceed the maximum specified value or the upper climatic category temperature.
 - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pins only. Temperatures specified in relation to reflow soldering can also refer to the pins or terminals for products with larger thermal mass, as in such cases, the temperature difference to the top of the component is too big (e.g., high proportion of core within the component).
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. It is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation.

Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g., ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.
- The following points must be observed if the components are potted, sealed, or varnished in customer applications:
 - Many potting, sealing, or varnishing materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
 - It is necessary to check whether the potting, sealing or varnishing materials used attack or destroy the wire insulation, plastics, or glue.
 - The effect of the potting, sealing, or varnishing materials may change the high-frequency behavior of the components.
- Magnetic core materials such as ferrites are sensitive to direct impact. This can cause the core material to flake or lead to breakage of the magnetic core material.
- Any type of tension or pressure on the product may result in damage and affect its functionality and reliability.
 - The products are only to be attached to fixings or mounting holes provided for this purpose in accordance with the data sheet.
 - If additional mechanical forces are applied to the component, e.g., application of gap pads, it is necessary to check whether they attack or destroy any part of the component.
 - It is not permitted for the product specified in the data sheet to assume a mechanical function in the final application.
- Inductance value can drop if external metallic or magnetic parts will be put close to the coil or into the air gap of the coil or core or magnetic material.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.

Release 2024-08-08

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. **The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.** Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.

Important notes

The following applies to all products named in this publication:

- 1 Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2 We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3 **The warnings, cautions and product-specific notes must be observed.**
- 4 In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5 We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6 Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.
- 7 **Our manufacturing sites serving the automotive business apply the IATF 16949 standard**. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System**. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.

Important notes

- 8 The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, FilterCap, FormFit, InsuGate, LeaXield, MediPlas, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PiezoBrush, PlasmaBrush, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SurfIND, ThermoFuse, WindCap, XieldCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2024-02