

SMT current sense transformers

EE 12.6

Series/Type: B82801C Date: March 2017

© EPCOS AG 2017. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

公TDK

B82801C EE12.6

SMT current sense transformers

Application

- Switching power supplies
- Feedback control
- Overload sensing
- Load drop/shut down detection

Features

- Very low DC resistance
- Different turns ratios
- Small package
- Other pinning on request
- RoHS compatible

Marking

Middle block of ordering code

Delivery mode and packing units

- 32 mm blister tape, 330 mm Ø reel
- Carton packaging
- Packing units: 200 pcs./reel;
- 800 pcs./carton




公TDK


B82801C

EE12.6

Dimensional drawing



Recommanded PCB Layout (Top View)



Dimensions in mm

14.22max.

lal

0,15

14.48max.

P₀


n n

公TDK

B82801C

EE12.6

Application circuit and pinning



Technical data and measuring conditions

Frequency range	50 500 kHz			
Hi-pot	1500 V AC, 50 Hz, 2 s (winding to winding)			
Inductance L (2-4)	100 kHz, 100 mV, @ +25 °C			
DC resistance R _{max}	Measured at +25 °C (specified per winding)			
Sensed current	The max. primary current of 40 A causes approx. +40 °C temperature rise			
Solderability	\geq 99.9 Sn, lead-free. Or Sn96.5Ag3.0Cu0.5: +(245 ±5) °C, (3 ±0.3) s Wetting of soldering area \geq 95% (to IEC 60068-2-58)			
Resistance to soldering heat	+(260 ± 5) °C, (10 ± 1 s) to IEC 60068-2-58			
Storage conditions	–20 °C … +40 °C, ≤ 75% RH			
Operating temperature range	–40 °C +125 °C			
Weight	Approx. 4.8 g			

4

⊗TDK

B82801C

EE12.6

$$B_{max} = \frac{V_{sense, max} \cdot \delta_{max}}{n_s \cdot A_e \cdot f_{osc}}$$

With:

B _{max}	Maximum magnetic flux density in the ferrite core of the current sense transformer			
V _{sense,max}	Maximum output voltage of the measurement signal			
δ_{max}	Maximum duty cycle			
n _s	Number of turns of the secondary winding of the current sense transformer			
A _e	Effective magnetic area of the ferrite core			
f _{osc}	Operating frequency of the switching operator IC			
Typical value for A _e : 12.4 x 10 ⁻⁶ m ²				

Typical B_{max}: 200 mT

$$R_{T} = \frac{V_{sense, max} \cdot n_{s}}{I_{prim, max}}$$

With:

R _T	Resistance of burden resistor
V _{sense,max}	Maximum output voltage of the measurement signal
n _s	Number of turns on the secondary side of the CT
I _{prim,max}	Maximum primary current (peak current)

Characteristics and ordering codes


L _{min}	Turns ratio	DC resistance R _{max} (mΩ)		Voltage- time product	Recomm. R _T	Ordering code
mH	N _p : N _s	primary	secondary	V•µs	Ω	
1.4	1 : 50	0.28	400	124	50	B82801C0145A050
5.6	1:100	0.28	1000	248	100	B82801C0565A100
12.6	1 : 150	0.28	2200	372	150	B82801C1265A150
22.4	1:200	0.28	2900	496	200	B82801C2245A200

②TDK

B82801C


EE12.6

Taping and packing Blister tape



Dimensions in mm


Reel



②TDK

SMT current sense transformers	B82801C
	EE12.6

Recommended reflow soldering curve



T ₁	T ₂	T ₃	T ₄	T ₁	T ₂	T ₃
°C	°C	°C	°C	sec	sec	sec
150	200	217	245	<110	<90	20 40

Max. time from +25 °C to T: 300 seconds Max. 3 reflow cycles



Cautions and warnings

<u>SMD</u>

- Please note the recommendations in our Inductors data book (latest edition) and in the data sheets.
 - Particular attention should be paid to the derating curves given there.
 - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not the housing.
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation.

Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.

- The following points must be observed if the components are potted in customer applications:
 - Many potting materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
 - It is necessary to check whether the potting material used attacks or destroys the wire insulation, plastics or glue.
 - The effect of the potting material can change the high-frequency behaviour of the components.
- Ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.

Display of ordering codes for EPCOS products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications and the website of EPCOS, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.epcos.com/orderingcodes.

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.
- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10