

Film Capacitors

Metallized Polypropylene Film Capacitors (MKP)

Series/Type: B32613, B32614

Date: September 2018

Series/Type: B32922*7 ... B32924*7

Date: May 2009

The following products presented in this data sheet are being withdrawn.

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A0104J008		2023-09-29	2023-01-12	2023-04-12
B32613A0104J010		2023-09-29	2023-01-12	2023-04-12
B32613A0104J020		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A0104J189		2023-09-29	2023-01-12	2023-04-12
B32613A0104J289		2023-09-29	2023-01-12	2023-04-12
B32613A0104K008		2023-09-29	2023-01-12	2023-04-12
B32613A0104K010		2023-09-29	2023-01-12	2023-04-12
B32613A0104K020		2023-09-29	2023-01-12	2023-04-12
B32613A0104K189		2023-09-29	2023-01-12	2023-04-12
B32613A0104K289		2023-09-29	2023-01-12	2023-04-12
B32613A0154J008		2023-09-29	2023-01-12	2023-04-12
B32613A0154J010		2023-09-29	2023-01-12	2023-04-12
B32613A0154J020		2023-09-29	2023-01-12	2023-04-12
B32613A0154J189		2023-09-29	2023-01-12	2023-04-12
B32613A0154J289		2023-09-29	2023-01-12	2023-04-12
B32613A0154K008		2023-09-29	2023-01-12	2023-04-12
B32613A0154K010		2023-09-29	2023-01-12	2023-04-12
B32613A0154K020		2023-09-29	2023-01-12	2023-04-12
B32613A0154K189		2023-09-29	2023-01-12	2023-04-12
B32613A0154K289		2023-09-29	2023-01-12	2023-04-12
B32613A0333J008		2023-09-29	2023-01-12	2023-04-12
B32613A0333J010		2023-09-29	2023-01-12	2023-04-12
B32613A0333J020		2023-09-29	2023-01-12	2023-04-12
B32613A0333J189		2023-09-29	2023-01-12	2023-04-12
B32613A0333J289		2023-09-29	2023-01-12	2023-04-12
B32613A0333K008		2023-09-29	2023-01-12	2023-04-12
B32613A0333K010		2023-09-29	2023-01-12	2023-04-12
B32613A0333K020		2023-09-29	2023-01-12	2023-04-12
B32613A0333K189		2023-09-29	2023-01-12	2023-04-12
B32613A0333K289		2023-09-29	2023-01-12	2023-04-12
B32613A0473J008		2023-09-29	2023-01-12	2023-04-12
B32613A0473J010		2023-09-29	2023-01-12	2023-04-12
B32613A0473J020		2023-09-29	2023-01-12	2023-04-12
B32613A0473J189		2023-09-29	2023-01-12	2023-04-12
B32613A0473J289		2023-09-29	2023-01-12	2023-04-12
B32613A0473K008		2023-09-29	2023-01-12	2023-04-12
B32613A0473K010		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A0473K020		2023-09-29	2023-01-12	2023-04-12
B32613A0473K189		2023-09-29	2023-01-12	2023-04-12
B32613A0473K289		2023-09-29	2023-01-12	2023-04-12
B32613A0683J008		2023-09-29	2023-01-12	2023-04-12
B32613A0683J010		2023-09-29	2023-01-12	2023-04-12
B32613A0683J020		2023-09-29	2023-01-12	2023-04-12
B32613A0683J189		2023-09-29	2023-01-12	2023-04-12
B32613A0683J289		2023-09-29	2023-01-12	2023-04-12
B32613A0683K008		2023-09-29	2023-01-12	2023-04-12
B32613A0683K010		2023-09-29	2023-01-12	2023-04-12
B32613A0683K020		2023-09-29	2023-01-12	2023-04-12
B32613A0683K189		2023-09-29	2023-01-12	2023-04-12
B32613A0683K289		2023-09-29	2023-01-12	2023-04-12
B32613A1103J008		2023-09-29	2023-01-12	2023-04-12
B32613A1103J010		2023-09-29	2023-01-12	2023-04-12
B32613A1103J020		2023-09-29	2023-01-12	2023-04-12
B32613A1103J189		2023-09-29	2023-01-12	2023-04-12
B32613A1103J289		2023-09-29	2023-01-12	2023-04-12
B32613A1103K008		2023-09-29	2023-01-12	2023-04-12
B32613A1103K010		2023-09-29	2023-01-12	2023-04-12
B32613A1103K020		2023-09-29	2023-01-12	2023-04-12
B32613A1103K189		2023-09-29	2023-01-12	2023-04-12
B32613A1103K289		2023-09-29	2023-01-12	2023-04-12
B32613A1153J008		2023-09-29	2023-01-12	2023-04-12
B32613A1153J010		2023-09-29	2023-01-12	2023-04-12
B32613A1153J020		2023-09-29	2023-01-12	2023-04-12
B32613A1153J189		2023-09-29	2023-01-12	2023-04-12
B32613A1153J289		2023-09-29	2023-01-12	2023-04-12
B32613A1153K008		2023-09-29	2023-01-12	2023-04-12
B32613A1153K010		2023-09-29	2023-01-12	2023-04-12
B32613A1153K020		2023-09-29	2023-01-12	2023-04-12
B32613A1153K189		2023-09-29	2023-01-12	2023-04-12
B32613A1153K289		2023-09-29	2023-01-12	2023-04-12
B32613A1223J008		2023-09-29	2023-01-12	2023-04-12

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A1223J010		2023-09-29	2023-01-12	2023-04-12
B32613A1223J020		2023-09-29	2023-01-12	2023-04-12
B32613A1223J189		2023-09-29	2023-01-12	2023-04-12
B32613A1223J289		2023-09-29	2023-01-12	2023-04-12
B32613A1223K008		2023-09-29	2023-01-12	2023-04-12
B32613A1223K010		2023-09-29	2023-01-12	2023-04-12
B32613A1223K020		2023-09-29	2023-01-12	2023-04-12
B32613A1223K189		2023-09-29	2023-01-12	2023-04-12
B32613A1223K289		2023-09-29	2023-01-12	2023-04-12
B32613A1333J008		2023-09-29	2023-01-12	2023-04-12
B32613A1333J010		2023-09-29	2023-01-12	2023-04-12
B32613A1333J020		2023-09-29	2023-01-12	2023-04-12
B32613A1333J189		2023-09-29	2023-01-12	2023-04-12
B32613A1333J289		2023-09-29	2023-01-12	2023-04-12
B32613A1333K008		2023-09-29	2023-01-12	2023-04-12
B32613A1333K010		2023-09-29	2023-01-12	2023-04-12
B32613A1333K020		2023-09-29	2023-01-12	2023-04-12
B32613A1333K189		2023-09-29	2023-01-12	2023-04-12
B32613A1333K289		2023-09-29	2023-01-12	2023-04-12
B32613A2103J008		2023-09-29	2023-01-12	2023-04-12
B32613A2103J010		2023-09-29	2023-01-12	2023-04-12
B32613A2103J020		2023-09-29	2023-01-12	2023-04-12
B32613A2103J189		2023-09-29	2023-01-12	2023-04-12
B32613A2103J289		2023-09-29	2023-01-12	2023-04-12
B32613A2103K008		2023-09-29	2023-01-12	2023-04-12
B32613A2103K010		2023-09-29	2023-01-12	2023-04-12
B32613A2103K020		2023-09-29	2023-01-12	2023-04-12
B32613A2103K189		2023-09-29	2023-01-12	2023-04-12
B32613A2103K289		2023-09-29	2023-01-12	2023-04-12
B32613A2153J008		2023-09-29	2023-01-12	2023-04-12
B32613A2153J010		2023-09-29	2023-01-12	2023-04-12
B32613A2153J020		2023-09-29	2023-01-12	2023-04-12
B32613A2153J189		2023-09-29	2023-01-12	2023-04-12
B32613A2153J289		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A2153K008		2023-09-29	2023-01-12	2023-04-12
B32613A2153K010		2023-09-29	2023-01-12	2023-04-12
B32613A2153K020		2023-09-29	2023-01-12	2023-04-12
B32613A2153K189		2023-09-29	2023-01-12	2023-04-12
B32613A2153K289		2023-09-29	2023-01-12	2023-04-12
B32613A2332J008		2023-09-29	2023-01-12	2023-04-12
B32613A2332J010		2023-09-29	2023-01-12	2023-04-12
B32613A2332J020		2023-09-29	2023-01-12	2023-04-12
B32613A2332J189		2023-09-29	2023-01-12	2023-04-12
B32613A2332J289		2023-09-29	2023-01-12	2023-04-12
B32613A2332K008		2023-09-29	2023-01-12	2023-04-12
B32613A2332K010		2023-09-29	2023-01-12	2023-04-12
B32613A2332K020		2023-09-29	2023-01-12	2023-04-12
B32613A2332K189		2023-09-29	2023-01-12	2023-04-12
B32613A2332K289		2023-09-29	2023-01-12	2023-04-12
B32613A2472J008		2023-09-29	2023-01-12	2023-04-12
B32613A2472J010		2023-09-29	2023-01-12	2023-04-12
B32613A2472J020		2023-09-29	2023-01-12	2023-04-12
B32613A2472J189		2023-09-29	2023-01-12	2023-04-12
B32613A2472J289		2023-09-29	2023-01-12	2023-04-12
B32613A2472K008		2023-09-29	2023-01-12	2023-04-12
B32613A2472K010		2023-09-29	2023-01-12	2023-04-12
B32613A2472K020		2023-09-29	2023-01-12	2023-04-12
B32613A2472K189		2023-09-29	2023-01-12	2023-04-12
B32613A2472K289		2023-09-29	2023-01-12	2023-04-12
B32613A2682J008		2023-09-29	2023-01-12	2023-04-12
B32613A2682J010		2023-09-29	2023-01-12	2023-04-12
B32613A2682J020		2023-09-29	2023-01-12	2023-04-12
B32613A2682J189		2023-09-29	2023-01-12	2023-04-12
B32613A2682J289		2023-09-29	2023-01-12	2023-04-12
B32613A2682K008		2023-09-29	2023-01-12	2023-04-12
B32613A2682K010		2023-09-29	2023-01-12	2023-04-12
B32613A2682K020		2023-09-29	2023-01-12	2023-04-12
B32613A2682K189		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A2682K289		2023-09-29	2023-01-12	2023-04-12
B32613A3105J008		2023-09-29	2023-01-12	2023-04-12
B32613A3105J010		2023-09-29	2023-01-12	2023-04-12
B32613A3105J020		2023-09-29	2023-01-12	2023-04-12
B32613A3105J189		2023-09-29	2023-01-12	2023-04-12
B32613A3105J289		2023-09-29	2023-01-12	2023-04-12
B32613A3105K008		2023-09-29	2023-01-12	2023-04-12
B32613A3105K010		2023-09-29	2023-01-12	2023-04-12
B32613A3105K020		2023-09-29	2023-01-12	2023-04-12
B32613A3105K189		2023-09-29	2023-01-12	2023-04-12
B32613A3105K289		2023-09-29	2023-01-12	2023-04-12
B32613A3224J008		2023-09-29	2023-01-12	2023-04-12
B32613A3224J010		2023-09-29	2023-01-12	2023-04-12
B32613A3224J020		2023-09-29	2023-01-12	2023-04-12
B32613A3224J189		2023-09-29	2023-01-12	2023-04-12
B32613A3224J289		2023-09-29	2023-01-12	2023-04-12
B32613A3224K008		2023-09-29	2023-01-12	2023-04-12
B32613A3224K010		2023-09-29	2023-01-12	2023-04-12
B32613A3224K020		2023-09-29	2023-01-12	2023-04-12
B32613A3224K189		2023-09-29	2023-01-12	2023-04-12
B32613A3224K289		2023-09-29	2023-01-12	2023-04-12
B32613A3334J008		2023-09-29	2023-01-12	2023-04-12
B32613A3334J010		2023-09-29	2023-01-12	2023-04-12
B32613A3334J020		2023-09-29	2023-01-12	2023-04-12
B32613A3334J189		2023-09-29	2023-01-12	2023-04-12
B32613A3334J289		2023-09-29	2023-01-12	2023-04-12
B32613A3334K008		2023-09-29	2023-01-12	2023-04-12
B32613A3334K010		2023-09-29	2023-01-12	2023-04-12
B32613A3334K020		2023-09-29	2023-01-12	2023-04-12
B32613A3334K189		2023-09-29	2023-01-12	2023-04-12
B32613A3334K289		2023-09-29	2023-01-12	2023-04-12
B32613A3474J008		2023-09-29	2023-01-12	2023-04-12
B32613A3474J010		2023-09-29	2023-01-12	2023-04-12
B32613A3474J020		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A3474J189		2023-09-29	2023-01-12	2023-04-12
B32613A3474J289		2023-09-29	2023-01-12	2023-04-12
B32613A3474K008		2023-09-29	2023-01-12	2023-04-12
B32613A3474K010		2023-09-29	2023-01-12	2023-04-12
B32613A3474K020		2023-09-29	2023-01-12	2023-04-12
B32613A3474K189		2023-09-29	2023-01-12	2023-04-12
B32613A3474K289		2023-09-29	2023-01-12	2023-04-12
B32613A3684J008		2023-09-29	2023-01-12	2023-04-12
B32613A3684J010		2023-09-29	2023-01-12	2023-04-12
B32613A3684J020		2023-09-29	2023-01-12	2023-04-12
B32613A3684J189		2023-09-29	2023-01-12	2023-04-12
B32613A3684J289		2023-09-29	2023-01-12	2023-04-12
B32613A3684K008		2023-09-29	2023-01-12	2023-04-12
B32613A3684K010		2023-09-29	2023-01-12	2023-04-12
B32613A3684K020		2023-09-29	2023-01-12	2023-04-12
B32613A3684K189		2023-09-29	2023-01-12	2023-04-12
B32613A3684K289		2023-09-29	2023-01-12	2023-04-12
B32613A4154J008		2023-09-29	2023-01-12	2023-04-12
B32613A4154J010		2023-09-29	2023-01-12	2023-04-12
B32613A4154J020		2023-09-29	2023-01-12	2023-04-12
B32613A4154J189		2023-09-29	2023-01-12	2023-04-12
B32613A4154J289		2023-09-29	2023-01-12	2023-04-12
B32613A4154K008		2023-09-29	2023-01-12	2023-04-12
B32613A4154K010		2023-09-29	2023-01-12	2023-04-12
B32613A4154K020		2023-09-29	2023-01-12	2023-04-12
B32613A4154K189		2023-09-29	2023-01-12	2023-04-12
B32613A4154K289		2023-09-29	2023-01-12	2023-04-12
B32613A4224J008		2023-09-29	2023-01-12	2023-04-12
B32613A4224J010		2023-09-29	2023-01-12	2023-04-12
B32613A4224J020		2023-09-29	2023-01-12	2023-04-12
B32613A4224J189		2023-09-29	2023-01-12	2023-04-12
B32613A4224J289		2023-09-29	2023-01-12	2023-04-12
B32613A4224K008		2023-09-29	2023-01-12	2023-04-12
B32613A4224K010		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A4224K020		2023-09-29	2023-01-12	2023-04-12
B32613A4224K189		2023-09-29	2023-01-12	2023-04-12
B32613A4224K289		2023-09-29	2023-01-12	2023-04-12
B32613A4334J008		2023-09-29	2023-01-12	2023-04-12
B32613A4334J010		2023-09-29	2023-01-12	2023-04-12
B32613A4334J020		2023-09-29	2023-01-12	2023-04-12
B32613A4334J189		2023-09-29	2023-01-12	2023-04-12
B32613A4334J289		2023-09-29	2023-01-12	2023-04-12
B32613A4334K008		2023-09-29	2023-01-12	2023-04-12
B32613A4334K010		2023-09-29	2023-01-12	2023-04-12
B32613A4334K020		2023-09-29	2023-01-12	2023-04-12
B32613A4334K189		2023-09-29	2023-01-12	2023-04-12
B32613A4334K289		2023-09-29	2023-01-12	2023-04-12
B32613A4474J008		2023-09-29	2023-01-12	2023-04-12
B32613A4474J010		2023-09-29	2023-01-12	2023-04-12
B32613A4474J020		2023-09-29	2023-01-12	2023-04-12
B32613A4474J189		2023-09-29	2023-01-12	2023-04-12
B32613A4474J289		2023-09-29	2023-01-12	2023-04-12
B32613A4474K008		2023-09-29	2023-01-12	2023-04-12
B32613A4474K010		2023-09-29	2023-01-12	2023-04-12
B32613A4474K020		2023-09-29	2023-01-12	2023-04-12
B32613A4474K189		2023-09-29	2023-01-12	2023-04-12
B32613A4474K289		2023-09-29	2023-01-12	2023-04-12
B32613A4684J008		2023-09-29	2023-01-12	2023-04-12
B32613A4684J010		2023-09-29	2023-01-12	2023-04-12
B32613A4684J020		2023-09-29	2023-01-12	2023-04-12
B32613A4684J189		2023-09-29	2023-01-12	2023-04-12
B32613A4684J289		2023-09-29	2023-01-12	2023-04-12
B32613A4684K008		2023-09-29	2023-01-12	2023-04-12
B32613A4684K010		2023-09-29	2023-01-12	2023-04-12
B32613A4684K020		2023-09-29	2023-01-12	2023-04-12
B32613A4684K189		2023-09-29	2023-01-12	2023-04-12
B32613A4684K289		2023-09-29	2023-01-12	2023-04-12
B32613A6104J008		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A6104J010		2023-09-29	2023-01-12	2023-04-12
B32613A6104J020		2023-09-29	2023-01-12	2023-04-12
B32613A6104J189		2023-09-29	2023-01-12	2023-04-12
B32613A6104J289		2023-09-29	2023-01-12	2023-04-12
B32613A6104K008		2023-09-29	2023-01-12	2023-04-12
B32613A6104K010		2023-09-29	2023-01-12	2023-04-12
B32613A6104K020		2023-09-29	2023-01-12	2023-04-12
B32613A6104K189		2023-09-29	2023-01-12	2023-04-12
B32613A6104K289		2023-09-29	2023-01-12	2023-04-12
B32613A6154J008		2023-09-29	2023-01-12	2023-04-12
B32613A6154J010		2023-09-29	2023-01-12	2023-04-12
B32613A6154J020		2023-09-29	2023-01-12	2023-04-12
B32613A6154J189		2023-09-29	2023-01-12	2023-04-12
B32613A6154J289		2023-09-29	2023-01-12	2023-04-12
B32613A6154K008		2023-09-29	2023-01-12	2023-04-12
B32613A6154K010		2023-09-29	2023-01-12	2023-04-12
B32613A6154K020		2023-09-29	2023-01-12	2023-04-12
B32613A6154K189		2023-09-29	2023-01-12	2023-04-12
B32613A6154K289		2023-09-29	2023-01-12	2023-04-12
B32613A6224J008		2023-09-29	2023-01-12	2023-04-12
B32613A6224J010		2023-09-29	2023-01-12	2023-04-12
B32613A6224J020		2023-09-29	2023-01-12	2023-04-12
B32613A6224J189		2023-09-29	2023-01-12	2023-04-12
B32613A6224J289		2023-09-29	2023-01-12	2023-04-12
B32613A6224K008		2023-09-29	2023-01-12	2023-04-12
B32613A6224K010		2023-09-29	2023-01-12	2023-04-12
B32613A6224K020		2023-09-29	2023-01-12	2023-04-12
B32613A6224K189		2023-09-29	2023-01-12	2023-04-12
B32613A6224K289		2023-09-29	2023-01-12	2023-04-12
B32613A6334J008		2023-09-29	2023-01-12	2023-04-12
B32613A6334J010		2023-09-29	2023-01-12	2023-04-12
B32613A6334J020		2023-09-29	2023-01-12	2023-04-12
B32613A6334J189		2023-09-29	2023-01-12	2023-04-12
B32613A6334J289		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A6334K008		2023-09-29	2023-01-12	2023-04-12
B32613A6334K010		2023-09-29	2023-01-12	2023-04-12
B32613A6334K020		2023-09-29	2023-01-12	2023-04-12
B32613A6334K189		2023-09-29	2023-01-12	2023-04-12
B32613A6334K289		2023-09-29	2023-01-12	2023-04-12
B32613A6474J008		2023-09-29	2023-01-12	2023-04-12
B32613A6474J010		2023-09-29	2023-01-12	2023-04-12
B32613A6474J020		2023-09-29	2023-01-12	2023-04-12
B32613A6474J189		2023-09-29	2023-01-12	2023-04-12
B32613A6474J289		2023-09-29	2023-01-12	2023-04-12
B32613A6474K008		2023-09-29	2023-01-12	2023-04-12
B32613A6474K010		2023-09-29	2023-01-12	2023-04-12
B32613A6474K020		2023-09-29	2023-01-12	2023-04-12
B32613A6474K189		2023-09-29	2023-01-12	2023-04-12
B32613A6474K289		2023-09-29	2023-01-12	2023-04-12
B32613A8103J008		2023-09-29	2023-01-12	2023-04-12
B32613A8103J010		2023-09-29	2023-01-12	2023-04-12
B32613A8103J020		2023-09-29	2023-01-12	2023-04-12
B32613A8103J189		2023-09-29	2023-01-12	2023-04-12
B32613A8103J289		2023-09-29	2023-01-12	2023-04-12
B32613A8103K008		2023-09-29	2023-01-12	2023-04-12
B32613A8103K010		2023-09-29	2023-01-12	2023-04-12
B32613A8103K020		2023-09-29	2023-01-12	2023-04-12
B32613A8103K189		2023-09-29	2023-01-12	2023-04-12
B32613A8103K289		2023-09-29	2023-01-12	2023-04-12
B32613A8332J008		2023-09-29	2023-01-12	2023-04-12
B32613A8332J010		2023-09-29	2023-01-12	2023-04-12
B32613A8332J020		2023-09-29	2023-01-12	2023-04-12
B32613A8332J189		2023-09-29	2023-01-12	2023-04-12
B32613A8332J289		2023-09-29	2023-01-12	2023-04-12
B32613A8332K008		2023-09-29	2023-01-12	2023-04-12
B32613A8332K010		2023-09-29	2023-01-12	2023-04-12
B32613A8332K020		2023-09-29	2023-01-12	2023-04-12
B32613A8332K189		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32613A8332K289		2023-09-29	2023-01-12	2023-04-12
B32613A8472J008		2023-09-29	2023-01-12	2023-04-12
B32613A8472J010		2023-09-29	2023-01-12	2023-04-12
B32613A8472J020		2023-09-29	2023-01-12	2023-04-12
B32613A8472J189		2023-09-29	2023-01-12	2023-04-12
B32613A8472J289		2023-09-29	2023-01-12	2023-04-12
B32613A8472K008		2023-09-29	2023-01-12	2023-04-12
B32613A8472K010		2023-09-29	2023-01-12	2023-04-12
B32613A8472K020		2023-09-29	2023-01-12	2023-04-12
B32613A8472K189		2023-09-29	2023-01-12	2023-04-12
B32613A8472K289		2023-09-29	2023-01-12	2023-04-12
B32613A8682J008		2023-09-29	2023-01-12	2023-04-12
B32613A8682J010		2023-09-29	2023-01-12	2023-04-12
B32613A8682J020		2023-09-29	2023-01-12	2023-04-12
B32613A8682J189		2023-09-29	2023-01-12	2023-04-12
B32613A8682J289		2023-09-29	2023-01-12	2023-04-12
B32613A8682K008		2023-09-29	2023-01-12	2023-04-12
B32613A8682K010		2023-09-29	2023-01-12	2023-04-12
B32613A8682K020		2023-09-29	2023-01-12	2023-04-12
B32613A8682K189		2023-09-29	2023-01-12	2023-04-12
B32613A8682K289		2023-09-29	2023-01-12	2023-04-12
B32614A0104J008		2023-09-29	2023-01-12	2023-04-12
B32614A0104J010		2023-09-29	2023-01-12	2023-04-12
B32614A0104J020		2023-09-29	2023-01-12	2023-04-12
B32614A0104K008		2023-09-29	2023-01-12	2023-04-12
B32614A0104K010		2023-09-29	2023-01-12	2023-04-12
B32614A0104K020		2023-09-29	2023-01-12	2023-04-12
B32614A0154J008		2023-09-29	2023-01-12	2023-04-12
B32614A0154J010		2023-09-29	2023-01-12	2023-04-12
B32614A0154J020		2023-09-29	2023-01-12	2023-04-12
B32614A0154K008		2023-09-29	2023-01-12	2023-04-12
B32614A0154K010		2023-09-29	2023-01-12	2023-04-12
B32614A0154K020		2023-09-29	2023-01-12	2023-04-12
B32614A0224J008		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32614A0224J010		2023-09-29	2023-01-12	2023-04-12
B32614A0224J020		2023-09-29	2023-01-12	2023-04-12
B32614A0224K008		2023-09-29	2023-01-12	2023-04-12
B32614A0224K010		2023-09-29	2023-01-12	2023-04-12
B32614A0224K020		2023-09-29	2023-01-12	2023-04-12
B32614A1223J008		2023-09-29	2023-01-12	2023-04-12
B32614A1223J010		2023-09-29	2023-01-12	2023-04-12
B32614A1223J020		2023-09-29	2023-01-12	2023-04-12
B32614A1223K008		2023-09-29	2023-01-12	2023-04-12
B32614A1223K010		2023-09-29	2023-01-12	2023-04-12
B32614A1223K020		2023-09-29	2023-01-12	2023-04-12
B32614A1333J008		2023-09-29	2023-01-12	2023-04-12
B32614A1333J010		2023-09-29	2023-01-12	2023-04-12
B32614A1333J020		2023-09-29	2023-01-12	2023-04-12
B32614A1333K008		2023-09-29	2023-01-12	2023-04-12
B32614A1333K010		2023-09-29	2023-01-12	2023-04-12
B32614A1333K020		2023-09-29	2023-01-12	2023-04-12
B32614A1473J008		2023-09-29	2023-01-12	2023-04-12
B32614A1473J010		2023-09-29	2023-01-12	2023-04-12
B32614A1473J020		2023-09-29	2023-01-12	2023-04-12
B32614A1473K008		2023-09-29	2023-01-12	2023-04-12
B32614A1473K010		2023-09-29	2023-01-12	2023-04-12
B32614A1473K020		2023-09-29	2023-01-12	2023-04-12
B32614A1683J008		2023-09-29	2023-01-12	2023-04-12
B32614A1683J010		2023-09-29	2023-01-12	2023-04-12
B32614A1683J020		2023-09-29	2023-01-12	2023-04-12
B32614A1683K008		2023-09-29	2023-01-12	2023-04-12
B32614A1683K010		2023-09-29	2023-01-12	2023-04-12
B32614A1683K020		2023-09-29	2023-01-12	2023-04-12
B32614A2103J008		2023-09-29	2023-01-12	2023-04-12
B32614A2103J010		2023-09-29	2023-01-12	2023-04-12
B32614A2103J020		2023-09-29	2023-01-12	2023-04-12
B32614A2103K008		2023-09-29	2023-01-12	2023-04-12
B32614A2103K010		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32614A2103K020		2023-09-29	2023-01-12	2023-04-12
B32614A2153J008		2023-09-29	2023-01-12	2023-04-12
B32614A2153J010		2023-09-29	2023-01-12	2023-04-12
B32614A2153J020		2023-09-29	2023-01-12	2023-04-12
B32614A2153K008		2023-09-29	2023-01-12	2023-04-12
B32614A2153K010		2023-09-29	2023-01-12	2023-04-12
B32614A2153K020		2023-09-29	2023-01-12	2023-04-12
B32614A2223J008		2023-09-29	2023-01-12	2023-04-12
B32614A2223J010		2023-09-29	2023-01-12	2023-04-12
B32614A2223J020		2023-09-29	2023-01-12	2023-04-12
B32614A2223K008		2023-09-29	2023-01-12	2023-04-12
B32614A2223K010		2023-09-29	2023-01-12	2023-04-12
B32614A2223K020		2023-09-29	2023-01-12	2023-04-12
B32614A2333J008		2023-09-29	2023-01-12	2023-04-12
B32614A2333J010		2023-09-29	2023-01-12	2023-04-12
B32614A2333J020		2023-09-29	2023-01-12	2023-04-12
B32614A2333K008		2023-09-29	2023-01-12	2023-04-12
B32614A2333K010		2023-09-29	2023-01-12	2023-04-12
B32614A2333K020		2023-09-29	2023-01-12	2023-04-12
B32614A2473J008		2023-09-29	2023-01-12	2023-04-12
B32614A2473J010		2023-09-29	2023-01-12	2023-04-12
B32614A2473J020		2023-09-29	2023-01-12	2023-04-12
B32614A2473K008		2023-09-29	2023-01-12	2023-04-12
B32614A2473K010		2023-09-29	2023-01-12	2023-04-12
B32614A2473K020		2023-09-29	2023-01-12	2023-04-12
B32614A3105J008		2023-09-29	2023-01-12	2023-04-12
B32614A3105J010		2023-09-29	2023-01-12	2023-04-12
B32614A3105J020		2023-09-29	2023-01-12	2023-04-12
B32614A3105K008		2023-09-29	2023-01-12	2023-04-12
B32614A3105K010		2023-09-29	2023-01-12	2023-04-12
B32614A3105K020		2023-09-29	2023-01-12	2023-04-12
B32614A3155J008		2023-09-29	2023-01-12	2023-04-12
B32614A3155J010		2023-09-29	2023-01-12	2023-04-12
B32614A3155J020		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32614A3155K008		2023-09-29	2023-01-12	2023-04-12
B32614A3155K010		2023-09-29	2023-01-12	2023-04-12
B32614A3155K020		2023-09-29	2023-01-12	2023-04-12
B32614A3225J008		2023-09-29	2023-01-12	2023-04-12
B32614A3225J010		2023-09-29	2023-01-12	2023-04-12
B32614A3225J020		2023-09-29	2023-01-12	2023-04-12
B32614A3225K008		2023-09-29	2023-01-12	2023-04-12
B32614A3225K010		2023-09-29	2023-01-12	2023-04-12
B32614A3225K020		2023-09-29	2023-01-12	2023-04-12
B32614A3474J008		2023-09-29	2023-01-12	2023-04-12
B32614A3474J010		2023-09-29	2023-01-12	2023-04-12
B32614A3474J020		2023-09-29	2023-01-12	2023-04-12
B32614A3474K008		2023-09-29	2023-01-12	2023-04-12
B32614A3474K010		2023-09-29	2023-01-12	2023-04-12
B32614A3474K020		2023-09-29	2023-01-12	2023-04-12
B32614A3684J008		2023-09-29	2023-01-12	2023-04-12
B32614A3684J010		2023-09-29	2023-01-12	2023-04-12
B32614A3684J020		2023-09-29	2023-01-12	2023-04-12
B32614A3684K008		2023-09-29	2023-01-12	2023-04-12
B32614A3684K010		2023-09-29	2023-01-12	2023-04-12
B32614A3684K020		2023-09-29	2023-01-12	2023-04-12
B32614A4105J008		2023-09-29	2023-01-12	2023-04-12
B32614A4105J010		2023-09-29	2023-01-12	2023-04-12
B32614A4105J020		2023-09-29	2023-01-12	2023-04-12
B32614A4105K008		2023-09-29	2023-01-12	2023-04-12
B32614A4105K010		2023-09-29	2023-01-12	2023-04-12
B32614A4105K020		2023-09-29	2023-01-12	2023-04-12
B32614A4155J008		2023-09-29	2023-01-12	2023-04-12
B32614A4155J010		2023-09-29	2023-01-12	2023-04-12
B32614A4155J020		2023-09-29	2023-01-12	2023-04-12
B32614A4155K008		2023-09-29	2023-01-12	2023-04-12
B32614A4155K010		2023-09-29	2023-01-12	2023-04-12
B32614A4155K020		2023-09-29	2023-01-12	2023-04-12
B32614A4225J008		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32614A4225J010		2023-09-29	2023-01-12	2023-04-12
B32614A4225J020		2023-09-29	2023-01-12	2023-04-12
B32614A4225K008		2023-09-29	2023-01-12	2023-04-12
B32614A4225K010		2023-09-29	2023-01-12	2023-04-12
B32614A4225K020		2023-09-29	2023-01-12	2023-04-12
B32614A4474J008		2023-09-29	2023-01-12	2023-04-12
B32614A4474J010		2023-09-29	2023-01-12	2023-04-12
B32614A4474J020		2023-09-29	2023-01-12	2023-04-12
B32614A4474K008		2023-09-29	2023-01-12	2023-04-12
B32614A4474K010		2023-09-29	2023-01-12	2023-04-12
B32614A4474K020		2023-09-29	2023-01-12	2023-04-12
B32614A4684J008		2023-09-29	2023-01-12	2023-04-12
B32614A4684J010		2023-09-29	2023-01-12	2023-04-12
B32614A4684J020		2023-09-29	2023-01-12	2023-04-12
B32614A4684K008		2023-09-29	2023-01-12	2023-04-12
B32614A4684K010		2023-09-29	2023-01-12	2023-04-12
B32614A4684K020		2023-09-29	2023-01-12	2023-04-12
B32614A6105J008		2023-09-29	2023-01-12	2023-04-12
B32614A6105J010		2023-09-29	2023-01-12	2023-04-12
B32614A6105J020		2023-09-29	2023-01-12	2023-04-12
B32614A6105K008		2023-09-29	2023-01-12	2023-04-12
B32614A6105K010		2023-09-29	2023-01-12	2023-04-12
B32614A6105K020		2023-09-29	2023-01-12	2023-04-12
B32614A6474J008		2023-09-29	2023-01-12	2023-04-12
B32614A6474J010		2023-09-29	2023-01-12	2023-04-12
B32614A6474J020		2023-09-29	2023-01-12	2023-04-12
B32614A6474K008		2023-09-29	2023-01-12	2023-04-12
B32614A6474K010		2023-09-29	2023-01-12	2023-04-12
B32614A6474K020		2023-09-29	2023-01-12	2023-04-12
B32614A6684J008		2023-09-29	2023-01-12	2023-04-12
B32614A6684J010		2023-09-29	2023-01-12	2023-04-12
B32614A6684J020		2023-09-29	2023-01-12	2023-04-12
B32614A6684K008		2023-09-29	2023-01-12	2023-04-12
B32614A6684K010		2023-09-29	2023-01-12	2023-04-12



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32614A6684K020		2023-09-29	2023-01-12	2023-04-12

For further information please contact your nearest EPCOS sales office, which will also support you in selecting a suitable substitute. The addresses of our worldwide sales network are presented at www.epcos.com/sales.

High pulse (wound)**Typical applications**

- Electronic ballasts
- Switch-mode power supplies

Climatic

- Max. operating temperature: 110 °C
- Climatic category (IEC 60068-1:2013): 55/100/56

Construction

- Dielectric: polypropylene (PP)
- Wound capacitor technology
- Epoxy resin coating (UL 94 V-0)

Features

- Very high pulse strength
- RoHS-compatible

Terminals

- Crimped wire leads, lead-free tinned, lead length (6 – 1) mm
- Double crimped wire leads, lead-free tinned
- Straight wire leads, lead-free tinned, lead length (17 ±3) mm
- Different lead spacings (reduced and enlarged) available, lead length (6 – 1) mm

Marking





Manufacturer's logo, style and type (P61x),
rated capacitance (coded),
capacitance tolerance (code letter),
rated DC voltage, date of manufacture (code)

Delivery mode

Bulk (untaped)

Taped (Ammo pack or reel)

For notes on taping, refer to chapter "Taping and packing".


Dimensional drawings
Crimped leads

Double crimped leads

Detail of double crimped version

Straight leads

Dimensions in mm

Lead spacing	Lead diameter	Type
$e \pm 0.8$	$d_1 \pm 0.05$	
22.5	0.8	B32613
27.5	0.8	B32614



B32613, B32614

High pulse (wound)

Overview of available types

Lead spacing	22.5 mm						
Type	B32613						
Page	6						
V_R (V DC)	250	400	630	1000	1600	2000	2000
V_{RMS} (V AC)	160	200	250	250	500	700	1000
C_R (nF)							
3.3							
4.7							
6.8							
10							
15							
22							
33							
47							
68							
100							
150							
220							
330							
470							
680							
1000							

Lead configurations


Serie	Standard	Reduced	Enlarged	Straight	Double crimped
B32613	22.5 mm	15 / 17.5 / 20 mm	25 mm	22.5 mm	22.5 mm
B32614	27.5 mm	25 mm	—	27.5 mm	27.5 mm


Overview of available types

Lead spacing	27.5 mm					
Type	B32614					
Page	8					
V_R (V DC)	250	400	630	1000	1600	2000
V_{RMS} (V AC)	160	200	250	250	500	700
C_R (nF)						
10						
15						
22						
33						
47						
68						
100						
150						
220						
470						
680						
1000						
1500						
2200						

Lead configurations

Serie	Standard	Reduced	Enlarged	Straight	Double crimped
B32613	22.5 mm	15 / 17.5 / 20 mm	25 mm	22.5 mm	22.5 mm
B32614	27.5 mm	25 mm	–	27.5 mm	27.5 mm



B32613

High pulse (wound)

Ordering codes and packing units (lead spacing 22.5 mm)

V_R	V_{RMS} $f \leq 1$ kHz	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./MOQ	Untaped pcs./MOQ
V DC	V AC	nF					
250	160	220	7.0 × 14.5 × 26.5	B32613A3224+***	2000	2800	2000
		330	7.0 × 14.5 × 26.5	B32613A3334+***	2000	2800	2000
		470	8.0 × 15.5 × 26.5	B32613A3474+***	1800	2400	2000
		680	9.5 × 16.0 × 26.5	B32613A3684+***	1400	2000	2000
		1000	11.0 × 19.0 × 26.5	B32613A3105+***	1200	1800	1000
400	200	150	7.0 × 13.5 × 26.5	B32613A4154+***	2000	2800	2000
		220	7.0 × 14.0 × 26.5	B32613A4224+***	2000	2800	2000
		330	8.0 × 16.0 × 26.5	B32613A4334+***	1800	2400	2000
		470	9.5 × 16.0 × 26.5	B32613A4474+***	1400	2000	1000
		680	11.5 × 17.5 × 26.5	B32613A4684+***	1200	1600	1000
630	250	100	7.0 × 12.5 × 26.5	B32613A6104+***	2000	2800	1000
		150	7.5 × 14.0 × 26.5	B32613A6154+***	1800	2600	1000
		220	9.0 × 15.5 × 26.5	B32613A6224+***	1600	2200	1000
		330	10.0 × 18.0 × 26.5	B32613A6334+***	1400	2000	1000
		470	11.0 × 20.0 × 26.5	B32613A6474+***	1200	1800	1000
1000	250	33	8.5 × 14.5 × 26.5	B32613A0333+***	1600	2200	2000
		47	10.0 × 15.5 × 26.5	B32613A0473+***	1400	2000	1000
		68	11.0 × 17.5 × 26.5	B32613A0683+***	1200	1800	1000
		100	10.0 × 16.5 × 26.5	B32613A0104+***	1400	2000	1000
		150	12.0 × 18.0 × 26.5	B32613A0154+***	1200	1600	1000
1600	500	10	7.0 × 13.5 × 26.5	B32613A1103+***	2000	2800	2000
		15	8.0 × 14.5 × 26.5	B32613A1153+***	1800	2400	2000
		22	9.0 × 17.0 × 26.5	B32613A1223+***	1600	2200	1000
		33	10.5 × 18.5 × 26.5	B32613A1333+***	1400	1800	1000

MOQ = Minimum Order Quantity, consisting of 4 packing units.
Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

K = ±10%

J = ±5%

*** = Packaging code:

289 = Ammo pack

189 = Reel


010 = Untaped crimped (lead length 6 – 1 mm)

008 = Untaped straight (lead length 17±3 mm)

020 = Double crimped (lead length 6 – 1 mm)

Packaging codes for further lead configurations (untaped):

Lead configuration (lead length 6 – 1 mm)	Reduced	Reduced	Reduced	Enlarged
Lead spacing (mm)	15 mm	17.5 mm	20 mm	25 mm
Packaging code	055	060	070	080


Ordering codes and packing units (lead spacing 22.5 mm)

V_R	V_{RMS} $f \leq 1$ kHz	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./MOQ	Untaped pcs./MOQ
V DC	V AC	nF					
2000	700	3.3	7.0 × 13.0 × 26.5	B32613A2332+***	2000	2800	2000
		4.7	7.5 × 14.0 × 26.5	B32613A2472+***	1800	2600	2000
		6.8	8.5 × 16.0 × 26.5	B32613A2682+***	1600	2200	2000
		10	10.5 × 17.0 × 26.5	B32613A2103+***	1400	1800	1000
		15	12.0 × 20.5 × 26.5	B32613A2153+***	1200	1600	1000
2000	1000	3.3	8.0 × 14.5 × 26.5	B32613A8332+***	1800	2400	2000
		4.7	8.5 × 16.5 × 26.5	B32613A8472+***	1600	2200	1000
		6.8	10.0 × 18.5 × 26.5	B32613A8682+***	1400	2000	1000
		10	11.5 × 21.5 × 26.5	B32613A8103+***	1200	1600	1000

MOQ = Minimum Order Quantity, consisting of 4 packing units.
Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

K = ±10%

J = ±5%

*** = Packaging code:

289 = Ammo pack

189 = Reel


010 = Untaped crimped (lead length 6 – 1 mm)

008 = Untaped straight (lead length 17±3 mm)

020 = Double crimped (lead length 6 – 1 mm)

Packaging codes for further lead configurations (untaped):

Lead configuration (lead length 6 – 1 mm)	Reduced	Reduced	Reduced	Enlarged
Lead spacing (mm)	15 mm	17.5 mm	20 mm	25 mm
Packaging code	055	060	070	080


B32614
High pulse (wound)
Ordering codes and packing units (lead spacing 27.5 mm)

V_R	V_{RMS} $f \leq 1$ kHz	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Untaped pcs./MOQ
V DC	V AC	nF			
250	160	470	7.0 × 15.0 × 31.5	B32614A3474+***	2000
		680	8.0 × 16.5 × 31.5	B32614A3684+***	2000
		1000	9.5 × 17.5 × 31.5	B32614A3105+***	800
		1500	11.5 × 19.5 × 31.5	B32614A3155+***	800
		2200	14.0 × 22.0 × 31.5	B32614A3225+***	800
400	200	470	9.5 × 15.0 × 31.5	B32614A4474+***	800
		680	10.0 × 17.5 × 31.5	B32614A4684+***	800
		1000	11.5 × 19.5 × 31.5	B32614A4105+***	800
		1500	14.0 × 22.0 × 31.5	B32614A4155+***	800
		2200	16.5 × 24.5 × 31.5	B32614A4225+***	600
630	250	470	10.5 × 18.5 × 31.5	B32614A6474+***	800
		680	12.0 × 21.5 × 31.5	B32614A6684+***	800
		1000	14.0 × 24.0 × 31.5	B32614A6105+***	800
1000	250	100	11.5 × 17.5 × 31.5	B32614A0104+***	2000
		150	13.0 × 21.0 × 31.5	B32614A0154+***	800
		220	14.5 × 24.5 × 31.5	B32614A0224+***	800
1600	500	22	9.0 × 14.5 × 31.5	B32614A1223+***	2000
		33	10.5 × 16.0 × 31.5	B32614A1333+***	2000
		47	11.0 × 19.5 × 31.5	B32614A1473+***	800
		68	13.0 × 21.5 × 31.5	B32614A1683+***	800
2000	700	10	9.0 × 15.5 × 31.5	B32614A2103+***	2000
		15	11.0 × 17.5 × 31.5	B32614A2153+***	800
		22	13.0 × 19.5 × 31.5	B32614A2223+***	800
		33	14.5 × 23.0 × 31.5	B32614A2333+***	800
		47	16.5 × 25.5 × 31.5	B32614A2473+***	600

MOQ = Minimum Order Quantity, consisting of 4 packing units.
Further E series and intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

K = ±10%

J = ±5%

*** = Packaging code:

010 = Untaped crimped (lead length 6 – 1 mm)

008 = Untaped straight (lead length 17±3 mm)

020 = Double crimped (lead length 6 – 1 mm)

Packaging codes for further lead configurations (untaped):

Lead configuration (lead length 6 – 1 mm)	Reduced
Lead spacing (mm)	25 mm
Packaging code	090


Technical data

 Reference standard: IEC 60384-16:2005. All data given at $T = 20\text{ }^{\circ}\text{C}$, unless otherwise specified.

Operating temperature range	Max. operating temperature $T_{op,max}$			+110 °C
	Upper category temperature T_{max}			+100 °C
	Lower category temperature T_{min}			-55 °C
	Rated temperature T_R			+85 °C
Dissipation factor $\tan \delta$ (in 10^{-3}) at 20 °C (upper limit values)	at	$C_R \leq 0.1\ \mu\text{F}$	$0.1\ \mu\text{F} < C_R \leq 1\ \mu\text{F}$	$C_R > 1\ \mu\text{F}$
	1 kHz	–	0.5	0.5
	10 kHz	–	0.8	1.5
	100 kHz	5.0	–	–
Insulation resistance R_{ins} or time constant $\tau = C_R \cdot R_{ins}$ at 20 °C, rel. humidity $\leq 65\%$ (minimum as-delivered values)	$C_R \leq 0.33\ \mu\text{F}$		$C_R > 0.33\ \mu\text{F}$	
	100 G Ω		30000 s	
DC test voltage	$1.6 \cdot V_R$, 2 s			
Category voltage V_C (continuous operation with V_{DC} or V_{AC} at $f \leq 1\text{ kHz}$)	T_{op} (°C)	DC voltage derating		AC voltage derating
	$T_{op} \leq 85$	$V_C = V_R$		$V_{C,RMS} = V_{RMS}$
	$85 < T_{op} \leq 100$	$V_C = V_R \cdot (165 - T_{op})/80$		$V_{C,RMS} = V_{RMS} \cdot (165 - T_{op})/80$
Operating voltage V_{op} for short operating periods (V_{DC} or V_{AC} at $f \leq 1\text{ kHz}$)	T_{op} (°C)	DC voltage (max. hours)		AC voltage (max. hours)
	$T_{op} \leq 100$	$V_{op} = 1.25 \cdot V_C$ (2000 h)		$V_{op} = 1.0 \cdot V_{C,RMS}$ (2000 h)
	$100 < T_{op} \leq 110$	$V_{op} = 1.25 \cdot V_C$ (1000 h)		$V_{op} = 1.0 \cdot V_{C,RMS}$ (1000 h)
Reliability: Failure rate λ Service life t_{SL}	1 fit ($\leq 1 \cdot 10^{-9}$ /h) at $0.5 \cdot V_R$, 40 °C 200 000 h at $1.0 \cdot V_R$, 85 °C For conversion to other operating conditions and temperatures, refer to chapter "Quality, 2 Reliability".			
Failure criteria: Total failure Failure due to variation of parameters	Short circuit or open circuit Capacitance change $ \Delta C/C $ > 10% Dissipation factor $\tan \delta$ > 4 · upper limit value Insulation resistance R_{ins} < 1500 M Ω ($C_R \leq 0.33\ \mu\text{F}$) or time constant $\tau = C_R \cdot R_{ins}$ < 500 s ($C_R > 0.33\ \mu\text{F}$)			

Characteristic voltages V_{DC} , V_{AC} , V_{pp}

V_{DC} V	V_{AC} V	V_{pp} V
1000	250	700
1250	500	1250
1600	500	1400
1600	700	1600
2000	700	1600
2000	1000	2000



B32613, B32614

High pulse (wound)

Pulse handling capability

"dV/dt" represents the maximum permissible voltage change per unit of time for non-sinusoidal voltages, expressed in V/ μ s.

"k₀" represents the maximum permissible pulse characteristic of the waveform applied to the capacitor, expressed in V²/ μ s.

Note:


The values of dV/dt and k₀ provided below must not be exceeded in order to avoid damaging the capacitor. These parameters are given for isolated pulses in such a way that the heat generated by one pulse will be completely dissipated before applying the next pulse. For a train of pulses, please refer to the curves of permissible AC voltage-current versus frequency.

dV/dt values


Lead spacing		22.5 mm	27.5 mm
V _R V DC	V _{RMS} V AC	dV/dt in V/ μ s	
250	160	120	50
400	200	180	100
630	250	300	150
1000	250	600	300
1250	500	1150	600
1600	500	2400	1000
1600	700	–	–
2000	700	7000	2300
2000	1000	7500	–


k₀ values

Lead spacing		22.5 mm	27.5 mm
V _R V DC	V _{RMS} V AC	k ₀ in V ² / μ s	
250	160	60 000	25 000
400	200	200 000	110 000
630	250	350 000	250 000
1000	250	1 500 000	1 000 000
1250	500	3 750 000	2 000 000
1600	500	10 000 000	4 000 000
1600	700	–	–
2000	700	40 000 000	15 000 000
2000	1000	50 000 000	–



Impedance Z versus frequency f
(typical values)





B32613


High pulse (wound)

Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 90^\circ C$)


For $T_A > 90^\circ C$, please use derating factor F_T .

Lead spacing 22.5 mm


250 V DC/160 V AC




400 V DC/200 V AC



630 V DC/250 V AC




1000 V DC/250 V AC



B32613

High pulse (wound)




Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 90^\circ C$)


For $T_A > 90^\circ C$, please use derating factor F_T .

Lead spacing 22.5 mm


1600 V DC/500 V AC




2000 V DC/700 V AC



2000 V DC/1000 V AC





B32614


High pulse (wound)

Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 90^\circ C$)


For $T_A > 90^\circ C$, please use derating factor F_T .

Lead spacing 27.5 mm


250 V DC/160 V AC




400 V DC/200 V AC



630 V DC/250 V AC




1000 V DC/250 V AC



B32614

High pulse (wound)




Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 90^\circ C$)


For $T_A > 90^\circ C$, please use derating factor F_T .

Lead spacing 27.5 mm

1600 V DC/500 V AC



2000 V DC/700 V AC





B32613, B32614

High pulse (wound)


Maximum AC voltage (V_{RMS}), current (I_{RMS}) versus frequency and temperature for $T_A > 90\text{ }^\circ\text{C}$

The graphs described in the previous section for the permissible AC voltage (V_{RMS}) or current (I_{RMS}) versus frequency are given for a maximum ambient temperature $T_A \leq 90\text{ }^\circ\text{C}$. In case of higher ambient temperatures (T_A), the self-heating (ΔT) of the component must be reduced to avoid that temperature of the component ($T_{op} = T_A + \Delta T$) reaches values above maximum operating temperature. The factor F_T shall be applied in the following way:

$$I_{RMS}(T_A) = I_{RMS, T_A \leq 90\text{ }^\circ\text{C}} \cdot F_T(T_A)$$

$$V_{RMS}(T_A) = V_{RMS, T_A \leq 90\text{ }^\circ\text{C}} \cdot F_T(T_A)$$

And F_T is given by the following curve:



Testing and Standards

Test	Reference	Conditions of test	Performance requirements
Electrical parameters	IEC 60384-16:2005	Voltage proof, $1.6 V_R$, 1 minute Insulation resistance, R_{ins} Capacitance, C Dissipation factor, $\tan \delta$	Within specified limits
Robustness of terminations	IEC 60068-2-21:2006	Tensile strength (test Ua1) Wire diameter Tensile force $0.5 < d_1 \leq 0.8 \text{ mm}$ 10 N	Capacitance and $\tan \delta$ within specified limits
Resistance to soldering heat	IEC 60068-2-20:2008, test Tb, method 1A	Solder bath temperature at $260 \pm 5 \text{ }^\circ\text{C}$, immersion for 10 seconds	$\Delta C/C_0 \leq 2\%$ $ \Delta \tan \delta \leq 0.002$
Rapid change of temperature	IEC 60384-16:2005	T_A = lower category temperature T_B = upper category temperature Five cycles, duration $t = 30 \text{ min.}$	$ \Delta C/C_0 \leq 2\%$ $ \Delta \tan \delta \leq 0.002$ $R_{ins} \geq 50\%$ of initial limit
Vibration	IEC 60384-16:2005	Test F_C : vibration sinusoidal Displacement: 0.75 mm Acceleration: 98 m/s^2 Frequency: 10 Hz ... 500 Hz Test duration: 3 orthogonal axes, 2 hours each axe	No visible damage
Bump	IEC 60384-16:2005	Test Eb: Total 4000 bumps with 390 m/s^2 mounted on PCB Duration: 6 ms	No visible damage $ \Delta C/C_0 \leq 2\%$ $ \Delta \tan \delta \leq 0.002$ $R_{ins} \geq 50\%$ of initial limit
Climatic sequence	IEC 60384-16:2005	Dry heat Tb / 16 h Damp heat cyclic, 1 st cycle $+55 \text{ }^\circ\text{C} / 24 \text{ h} / 95\% \dots 100\% \text{ RH}$ Cold Ta / 2 h Damp heat cyclic, 5 cycles $+55 \text{ }^\circ\text{C} / 24 \text{ h} / 95\% \dots 100\% \text{ RH}$	No visible damage $ \Delta C/C_0 \leq 3\%$ $ \Delta \tan \delta \leq 0.001$ $R_{ins} \geq 50\%$ of initial limit
Damp heat, steady state	IEC 60384-16:2005	Test Ca $40 \text{ }^\circ\text{C} / 93\% \text{ RH} / 56 \text{ days}$	No visible damage $ \Delta C/C_0 \leq 3\%$ $ \Delta \tan \delta \leq 0.001$ $R_{ins} \geq 50\%$ of initial limit
Endurance A	IEC 60384-16:2005	$85 \text{ }^\circ\text{C} / 1.25 V_R / 2000 \text{ hours}$	No visible damage $ \Delta C/C_0 \leq 5\%$ $ \Delta \tan \delta \leq 0.002$ $R_{ins} \geq 50\%$ of initial limit



B32613, B32614

High pulse (wound)

Test	Reference	Conditions of test	Performance requirements
Endurance B	IEC 60384-16:2005	100 °C / 1.25 V _C / 2000 hours	No visible damage ΔC/C ₀ ≤ 5% Δ tan δ ≤ 0.002 R _{ins} ≥ 50% of initial limit

Mounting guidelines

1 Soldering

1.1 Solderability of leads

The solderability of terminal leads is tested to IEC 60068-2-20, test Ta, method 1.

Before a solderability test is carried out, terminals are subjected to accelerated ageing (to IEC 60068-2-2, test Ba: 4 h exposure to dry heat at 155 °C). Since the ageing temperature is far higher than the upper category temperature of the capacitors, the terminal wires should be cut off from the capacitor before the ageing procedure to prevent the solderability being impaired by the products of any capacitor decomposition that might occur.

Solder bath temperature	235 ±5 °C
Soldering time	2.0 ±0.5 s
Immersion depth	2.0 +0/-0.5 mm from capacitor body or seating plane
Evaluation criteria:	
Visual inspection	Wetting of wire surface by new solder ≥90%, free-flowing solder




1.2 Resistance to soldering heat

Resistance to soldering heat is tested to IEC 60068-2-20, test Tb, method 1.

Conditions:

Series	Solder bath temperature	Soldering time
MKT boxed (except 2.5 × 6.5 × 7.2 mm) coated uncoated (lead spacing >10 mm)	260 ±5 °C	10 ±1 s
MFP MKP (lead spacing >7.5 mm)		
MKT boxed (case 2.5 × 6.5 × 7.2 mm)		5 ±1 s
MKT uncoated (lead spacing ≤10 mm) insulated (B32559)		<4 s recommended soldering profile for MKT uncoated (lead spacing ≤ 10 mm) and insulated (B32559)



Immersion depth	2.0 +0/−0.5 mm from capacitor body or seating plane
Shield	Heat-absorbing board, (1.5 ±0.5) mm thick, between capacitor body and liquid solder
Evaluation criteria:	
Visual inspection	No visible damage
$\Delta C/C_0$	2% for MKT/MKP/MFP 5% for EMI suppression capacitors
$\tan \delta$	As specified in sectional specification



B32613, B32614

High pulse (wound)

1.3 General notes on soldering


Permissible heat exposure loads on film capacitors are primarily characterized by the upper category temperature T_{max} . Long exposure to temperatures above this type-related temperature limit can lead to changes in the plastic dielectric and thus change irreversibly a capacitor's electrical characteristics. For short exposures (as in practical soldering processes) the heat load (and thus the possible effects on a capacitor) will also depend on other factors like:

- Pre-heating temperature and time
- Forced cooling immediately after soldering
- Terminal characteristics:
diameter, length, thermal resistance, special configurations (e.g. crimping)
- Height of capacitor above solder bath
- Shadowing by neighboring components
- Additional heating due to heat dissipation by neighboring components
- Use of solder-resist coatings

The overheating associated with some of these factors can usually be reduced by suitable countermeasures. For example, if a pre-heating step cannot be avoided, an additional or reinforced cooling process may possibly have to be included.

Recommendations


As a reference, the recommended wave soldering profile for our film capacitors is as follows:



T_s : Capacitor body maximum temperature at wave soldering

T_p : Capacitor body maximum temperature at pre-heating

KMK1745-A-E



Body temperature should follow the description below:

- MKP capacitor
 - During pre-heating: $T_p \leq 110 \text{ }^\circ\text{C}$
 - During soldering: $T_s \leq 120 \text{ }^\circ\text{C}$, $t_s \leq 45 \text{ s}$
- MKT capacitor
 - During pre-heating: $T_p \leq 125 \text{ }^\circ\text{C}$
 - During soldering: $T_s \leq 160 \text{ }^\circ\text{C}$, $t_s \leq 45 \text{ s}$

When SMD components are used together with leaded ones, the film capacitors should not pass into the SMD adhesive curing oven. The leaded components should be assembled after the SMD curing step.

Leaded film capacitors are not suitable for reflow soldering.

In order to ensure proper conditions for manual or selective soldering, the body temperature of the capacitor (T_s) must be $\leq 120 \text{ }^\circ\text{C}$.

One recommended condition for manual soldering is that the tip of the soldering iron should be $< 360 \text{ }^\circ\text{C}$ and the soldering contact time should be no longer than 3 seconds.

For uncoated MKT capacitors with lead spacings $\leq 10 \text{ mm}$ (B32560/B32561) the following measures are recommended:

- pre-heating to not more than $110 \text{ }^\circ\text{C}$ in the preheater phase
- rapid cooling after soldering

Please refer to our Film Capacitors Data Book in case more details are needed.



B32613, B32614

High pulse (wound)

Cautions and warnings

- Do not exceed the upper category temperature (UCT).
- Do not apply any mechanical stress to the capacitor terminals.
- Avoid any compressive, tensile or flexural stress.
- Do not move the capacitor after it has been soldered to the PC board.
- Do not pick up the PC board by the soldered capacitor.
- Do not place the capacitor on a PC board whose PTH hole spacing differs from the specified lead spacing.
- Do not exceed the specified time or temperature limits during soldering.
- Avoid external energy inputs, such as fire or electricity.
- Avoid overload of the capacitors.
- Consult us if application is with severe temperature and humidity condition.
- There are no serviceable or repairable parts inside the capacitor. Opening the capacitor or any attempts to open or repair the capacitor will void the warranty and liability of TDK Electronics.
- Please note that the standards referred to in this publication may have been revised in the meantime.

The table below summarizes the safety instructions that must always be observed. A detailed description can be found in the relevant sections of the chapters "General technical information" and "Mounting guidelines".

Topic	Safety information	Reference chapter "General technical information"
Storage conditions	Make sure that capacitors are stored within the specified range of time, temperature and humidity conditions.	4.5 "Storage conditions"
Flammability	Avoid external energy, such as fire or electricity (passive flammability), avoid overload of the capacitors (active flammability) and consider the flammability of materials.	5.3 "Flammability"
Resistance to vibration	Do not exceed the tested ability to withstand vibration. The capacitors are tested to IEC 60068-2-6:2007. TDK Electronics offers film capacitors specially designed for operation under more severe vibration regimes such as those found in automotive applications. Consult our catalog "Film Capacitors for Automotive Electronics".	5.2 "Resistance to vibration"



Topic	Safety information	Reference chapter "Mounting guidelines"
Soldering	Do not exceed the specified time or temperature limits during soldering.	1 "Soldering"
Cleaning	Use only suitable solvents for cleaning capacitors.	2 "Cleaning"
Embedding of capacitors in finished assemblies	When embedding finished circuit assemblies in plastic resins, chemical and thermal influences must be taken into account. Caution: Consult us first, if you also wish to embed other uncoated component types!	3 "Embedding of capacitors in finished assemblies"

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.

Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.

Correlation of data sheet values and modelling tool outputs

Data sheet values and results of design tools may deviate as they have not been derived in the same context.

While data sheets show individual parameter statements without considering a possible dependency to other parameters. Tools model a complete given scenario as input and processed inside the tool.

Furthermore as we constantly strive to improve our models, the results of tools can change over time and be a non-binding indication only.



B32613, B32614

High pulse (wound)

Symbols and terms

Symbol	English	German
α	Heat transfer coefficient	Wärmeübergangszahl
α_C	Temperature coefficient of capacitance	Temperaturkoeffizient der Kapazität
A	Capacitor surface area	Kondensatoroberfläche
β_C	Humidity coefficient of capacitance	Feuchteoeffizient der Kapazität
C	Capacitance	Kapazität
C_R	Rated capacitance	Nennkapazität
ΔC	Absolute capacitance change	Absolute Kapazitätsänderung
$\Delta C/C$	Relative capacitance change (relative deviation of actual value)	Relative Kapazitätsänderung (relative Abweichung vom Ist-Wert)
$\Delta C/C_R$	Capacitance tolerance (relative deviation from rated capacitance)	Kapazitätstoleranz (relative Abweichung vom Nennwert)
dt	Time differential	Differentielle Zeit
Δt	Time interval	Zeitintervall
ΔT	Absolute temperature change (self-heating)	Absolute Temperaturänderung (Selbsterwärmung)
$\Delta \tan \delta$	Absolute change of dissipation factor	Absolute Änderung des Verlustfaktors
ΔV	Absolute voltage change	Absolute Spannungsänderung
dV/dt	Time differential of voltage function (rate of voltage rise)	Differentielle Spannungsänderung (Spannungsflankensteilheit)
$\Delta V/\Delta t$	Voltage change per time interval	Spannungsänderung pro Zeitintervall
E	Activation energy for diffusion	Aktivierungsenergie zur Diffusion
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatz-Serienwiderstand
f	Frequency	Frequenz
f_1	Frequency limit for reducing permissible AC voltage due to thermal limits	Grenzfrequenz für thermisch bedingte Reduzierung der zulässigen Wechselspannung
f_2	Frequency limit for reducing permissible AC voltage due to current limit	Grenzfrequenz für strombedingte Reduzierung der zulässigen Wechselspannung
f_r	Resonant frequency	Resonanzfrequenz
F_D	Thermal acceleration factor for diffusion	Therm. Beschleunigungsfaktor zur Diffusion
F_T	Derating factor	Deratingfaktor
i	Current (peak)	Stromspitze
I_C	Category current (max. continuous current)	Kategoriestrom (max. Dauerstrom)



Symbol	English	German
I_{RMS}	(Sinusoidal) alternating current, root-mean-square value	(Sinusförmiger) Wechselstrom
i_z	Capacitance drift	Inkonstanz der Kapazität
k_0	Pulse characteristic	Impulskenwert
L_S	Series inductance	Serieninduktivität
λ	Failure rate	Ausfallrate
λ_0	Constant failure rate during useful service life	Konstante Ausfallrate in der Nutzungsphase
λ_{test}	Failure rate, determined by tests	Experimentell ermittelte Ausfallrate
P_{diss}	Dissipated power	Abgegebene Verlustleistung
P_{gen}	Generated power	Erzeugte Verlustleistung
Q	Heat energy	Wärmeenergie
ρ	Density of water vapor in air	Dichte von Wasserdampf in Luft
R	Universal molar constant for gases	Allg. Molarkonstante für Gas
R	Ohmic resistance of discharge circuit	Ohmscher Widerstand des Entladekreises
R_i	Internal resistance	Innenwiderstand
R_{ins}	Insulation resistance	Isolationswiderstand
R_P	Parallel resistance	Parallelwiderstand
R_S	Series resistance	Serienwiderstand
S	severity (humidity test)	Schärfegrad (Feuchtetest)
t	Time	Zeit
T	Temperature	Temperatur
τ	Time constant	Zeitkonstante
$\tan \delta$	Dissipation factor	Verlustfaktor
$\tan \delta_D$	Dielectric component of dissipation factor	Dielektrischer Anteil des Verlustfaktors
$\tan \delta_P$	Parallel component of dissipation factor	Parallelanteil des Verlustfaktors
$\tan \delta_S$	Series component of dissipation factor	Serienanteil des Verlustfaktors
T_A	Temperature of the air surrounding the component	Temperatur der Luft, die das Bauteil umgibt
T_{max}	Upper category temperature	Obere Kategorietemperatur
T_{min}	Lower category temperature	Untere Kategorietemperatur
t_{OL}	Operating life at operating temperature and voltage	Betriebszeit bei Betriebstemperatur und -spannung
T_{op}	Operating temperature, $T_A + \Delta T$	Betriebstemperatur, $T_A + \Delta T$
T_R	Rated temperature	Nenntemperatur
T_{ref}	Reference temperature	Referenztemperatur
t_{SL}	Reference service life	Referenz-Lebensdauer



B32613, B32614

High pulse (wound)

Symbol	English	German
V_{AC}	AC voltage	Wechselspannung
V_C	Category voltage	Kategoriespannung
$V_{C,RMS}$	Category AC voltage	(Sinusförmige) Kategorie-Wechselspannung
V_{CD}	Corona-discharge onset voltage	Teilentlade-Einsatzspannung
V_{ch}	Charging voltage	Ladespannung
V_{DC}	DC voltage	Gleichspannung
V_{FB}	Fly-back capacitor voltage	Spannung (Flyback)
V_i	Input voltage	Eingangsspannung
V_o	Output voltage	Ausgangssspannung
V_{op}	Operating voltage	Betriebsspannung
V_p	Peak pulse voltage	Impuls-Spitzenspannung
V_{pp}	Peak-to-peak voltage Impedance	Spannungshub
V_R	Rated voltage	Nennspannung
\hat{V}_R	Amplitude of rated AC voltage	Amplitude der Nenn-Wechselspannung
V_{RMS}	(Sinusoidal) alternating voltage, root-mean-square value	(Sinusförmige) Wechselspannung
V_{SC}	S-correction voltage	Spannung bei Anwendung "S-correction"
V_{sn}	Snubber capacitor voltage	Spannung bei Anwendung "Beschaltung"
Z	Impedance	Scheinwiderstand
e	Lead spacing	Rastermaß

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.

Important notes

7. **Our manufacturing sites serving the automotive business apply the IATF 16949 standard.** The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements (“CSR”) TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System.** For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
8. The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap, XieldCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2020-06