

# **Aluminum electrolytic capacitors**

Single-ended capacitors

Series/Type:B43891Status:In developmentDate:May 2025

© TDK Electronics AG 2025. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



Long useful life - 105 °C

### In development



#### Important information

This series is not yet released for mass production and subject to change. The products delivered are engineering samples, prototypes or pre-series products, which are not intended for commercial use in series products of the purchaser. The supplier assumes no warranty or liability. Any use is at the sole risk of the purchaser.

#### Long-life grade capacitors

#### Applications

- Automotive electronics
- Industrial electronics
- On-board chargers

#### Features

- Compact dimensions
- High ripple current capability
- Long useful life, 10000 h at 105 °C
- RoHS-compatible

#### Construction

- Radial leads
- Charge-discharge proof, polar
- Aluminum case with PET sleeve
- Minus pole marking on the sleeve
- Case with pressure relief vent

#### **Delivery mode**

Terminal configurations and packing:

- Bulk
- Taped, Ammo pack
- Cut
- Kinked
- PAPR (Protection Against Polarity Reversal): crimped leads, J leads, bent leads

Refer to chapter "Single-ended capacitors - Taping, packing and lead configurations" for further details.





### Single-ended capacitors

# Long useful life - 105 °C

#### In development

#### Specifications and characteristics in brief

Rated voltage V <sub>R</sub> Surge voltage V <sub>S</sub>	450 V DC 1.1 • V <sub>P</sub>			
Rated capacitance C <sub>R</sub> Capacitance tolerance	82 160 µF ±20% ≙ M			
Dissipation factor tan $\delta$ (20 °C, 120 Hz)	≤ 0.24			
Leakage current l <sub>leak</sub> (20 °C, 5 min)	$I_{\text{leak}} \leq 0.03 \mu \text{A} \cdot \left(\frac{6}{\mu}\right)$	$\frac{C_R}{\mu F} \cdot \frac{V_R}{V} +$	15µA	
Self-inductance ESL	Diameter (mm)	16	18	
	Approx. ESL (nH)	26	34	
Useful life <sup>1),2)</sup>			Requir	ements:
105 °C; V <sub>R</sub> ; I <sub>AC,R</sub>	> 10000 h		∆C/C	$\leq$ 20% of initial value
			tan $\delta$	$\leq$ 3 times initial specified limit
			I <sub>leak</sub>	≤ initial specified limit
Voltage endurance test			Post te	st requirements:
105 °C; V <sub>R</sub>	3000 h		∆C/C	$\leq$ 15% of initial value
			${\rm tan}\delta$	$\leq$ 1.5 times initial specified limit
			l <sub>leak</sub>	$\leq$ initial specified limit
Vibration resistance test	To IEC 60068-2-6	:2007, tes	t Fc:	
	Frequency range 1	10 Hz 2	kHz, di	splacement amplitude max. 1.5 mm,
	acceleration max.	20 <i>g</i> , dura	ation 3 ×	<sup>2</sup> 2 h.
	Capacitor rigidly cl fixture.	amped by	the alu	minum case e.g. using our standard
Characteristics at low temperature	Max. impedance ratio at 120 Hz	$\overline{V_R}$	V DC) <sub>5 °C</sub> / Z <sub>2</sub>	450 V <u>0 °C</u> 6 0 °C 10
IFC climatic catagony	TO IEC 60068 1.20	`` \13∙	E	
	40/105/56 (-40 °C/	+105 °C/5	6 davs o	damp heat test)
Sectional specification <sup>3)</sup>	IEC 60384-4:2016			

1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.

2) Useful life specification shall apply for capacitors subjected to DC voltage with the rated ripple current (the peak voltage shall not exceed the rated voltage).

3) Refer to chapter "General technical information, 2 Standards and specifications" for further details.

3



### Single-ended capacitors

# Long useful life - 105 °C

#### In development

#### **Dimensional drawing** With stand-off rubber seal Diameters (mm): 16, 18

Stand-off rubber seal å (+) $\overline{\Theta}$ പ 5 min. 15 min. Vent<sup>1)</sup> Minus pole

marking

<sup>1)</sup> Supplied components may have different vent designs. They all offer the same functionality of pressure relief.

KAL1961-Q-E

#### **Dimensions and weights**

Dimensions	Approx. weight			
d +0.5	l +2	a ±0.5	b	g
16	31.5	7.5	0.80 ±0.05	11
16	35.5	7.5	0.80 ±0.05	13
16	40	7.5	0.80 ±0.05	15
18	31.5	7.5	0.80 ±0.1	15
18	35	7.5	0.80 ±0.1	16
18	40	7.5	0.80 ±0.1	18

#### Overview of available types

Other voltage and capacitance ratings are available upon request.

V <sub>R</sub> (V DC)	450
	Case dimensions d × I (mm)
C <sub>R</sub> (μF)	
82	16 × 31.5
100	16 × 35.5
110	18 × 31.5
120	16 × 40
130	18 × 35
160	18 × 40

4



# Long useful life - 105 °C

#### In development

#### Technical data and ordering codes

C <sub>R</sub> 120 Hz	Case dimensions	I <sub>AC,R</sub> 120 Hz	Ordering code (composition see
μF	mm	mA	Delowy
V <sub>R</sub> = 450 V	DC		
82	16 × 31.5	650	B43891A5826M***
100	16 × 35.5	750	B43891A5107M***
110	18 × 31.5	800	B43891A5117M***
120	16 × 40	860	B43891A5127M***
130	18 × 35	920	B43891A5137M***
160	18 × 40	980	B43891A5167M***

#### Composition of ordering code

- \*\*\* = Version
  - 000 = for standard leads, bulk
  - 001 = for kinked leads, bulk
  - 002 = for cut leads, bulk
  - 003 = for crimped leads, blister
  - 004 = for J leads, blister
  - 009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (for d × I = 16 × 31.5 mm and 18 × 31.5 mm)
  - 012 = for bent 90° leads, blister (for  $\emptyset$  16 ... 18 mm)

### Useful life<sup>1)</sup>

Calculations of useful life are performed on request, based on operational conditions stated by the customer.

1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.

5 5/25



# Single-ended capacitors

# Long useful life - 105 °C

### In development

# Taping

Single-ended capacitors are available taped in Ammo pack from diameter 8 to 18 mm as follows:

Lead spacing  $F = 3.5 \text{ mm} (\emptyset \text{ d} = 8 \text{ mm})$ 

Lead spacing F = 5.0 mm (Ø d = 8 ... 12.5 mm)

Lead spacing F = 7.5 mm ( $\emptyset$  d = 16 ... 18 mm).

The dimensions for F, P1 and 1 max. are specified with reference to the center of the terminal wires.

# Lead spacing 3.5 mm ( $\emptyset$ d = 8 mm)

Last 3 digits of ordering code: 006



#### Dimensions in mm

Ød	F	H	W	W <sub>0</sub>	W <sub>1</sub>	$W_2$	Ρ	P <sub>0</sub>	P <sub>1</sub>	I <sub>1</sub>	t	Δh	D <sub>0</sub>
8	3.5	18.5	18	9.5	9.0	3.0	12.7	12.7	4.6	1.0	0.7	1.0	4.0
Toler- ance	+0.8 -0.2	±1.0	±0.5	min.	±0.5	max.	±1.0	±0.3	±0.6	max.	±0.2	max.	±0.2

Leads can also run straight through the taping area.

6



#### Single-ended capacitors

# Long useful life - 105 °C

#### In development

#### Lead spacing 5.0 mm (Ø d = 8 mm)

Last 3 digits of ordering code: 008



## Lead spacing 5.0 mm (Ø d = 10 ... 12.5 mm)

Last 3 digits of ordering code: 008



## Dimensions in mm

Ød	F	Н	W	W <sub>0</sub>	W <sub>1</sub>	$W_2$	H <sub>0</sub>	Р	P <sub>0</sub>	P <sub>1</sub>	I <sub>1</sub>	t	Δh	D <sub>0</sub>
8		20.0		9.5			16.0	12.7	12.7	3.85				
10	5.0	19.0	18	9.5	9.0	1.5	_	12.7	12.7	3.85	1.0	0.6	1.0	4.0
12.5		19.0		11.5			_	15.0	15.0	5.0				
Toler- ance	+0.8 -0.2	±0.75	±0.5	min.	±0.5	max.	±0.5	±1.0	±0.2	±0.5	max.	+0.3 -0.2	max.	±0.2

Taping is available up to dimensions  $d \times I = 12.5 \times 25$  mm.

Please read *Cautions and warnings* and *Important notes* at the end of this document.



## Long useful life - 105 °C

#### In development

### Lead spacing 7.5 mm (Ø d = 16 ... 18 mm)

Last 3 digits of ordering code: 009



#### **Dimensions in mm**

Ød	F	Н	W	W <sub>0</sub>	W <sub>1</sub>	$W_2$	Р	P <sub>0</sub>	P <sub>1</sub>	Ι <sub>1</sub>	t	ΔP	Δh	D <sub>0</sub>
16	75	19.5	19.0	12.5	0.0	15	30.0	15.0	3 75	10	0.7	0	0	10
18	1.5	10.5	10.0	12.5	9.0	1.5	30.0	15.0	5.75	1.0	0.7	0	0	4.0
Toler- ance	±0.8	-0.5 +0.75	±0.5	min.	±0.5	max.	±1.0	±0.2	±0.5	max.	±0.2	±1.0	±1.0	±0.2

Taping is available up to dimensions  $d \times I = 16 \times 31.5$  mm and  $18 \times 31.5$  mm.

8



# Single-ended capacitors

# Long useful life - 105 °C

#### In development

### Cut or kinked leads

Single-ended capacitors are available with cut or kinked leads. Other lead configurations also available upon request.

### **Cut leads**

Last 3 digits of ordering code: 002

#### With stand-off rubber seal



KAL1085-I

#### With flat rubber seal



Case size	Dimensions (mm)
d x I (mm)	a ±0.5
10 x 12.5	5.0
10 x 16	5.0
10 x 20	5.0
12.5 x 20	5.0
12.5 x 25	5.0
16 x 20	7.5
16 x 25	7.5
16 x 31.5	7.5
16 x 35.5	7.5
16 x 40	7.5
18 x 20	7.5
18 x 25	7.5
18 x 31.5	7.5
18 x 35	7.5
18 x 40	7.5



# Single-ended capacitors

# Long useful life - 105 °C

#### In development

### **Kinked leads**

Last 3 digits of ordering code: 001

#### With stand-off rubber seal







KAL1083-2

#### With flat rubber seal



KAL1082-T



KAL1084-A

)
-

Please read Cautions and warnings and Important notes at the end of this document.



# Long useful life - 105 °C

#### In development

PAPR leads (Protection Against Polarity Reversal)

These lead configurations ensure correct placement of the capacitor on the PCB with regard to polarity. PAPR leads are available for diameters from 10 mm up to 18 mm. There are three configurations available: Crimped leads, J leads, bent 90° leads.

## **Crimped leads**

Last 3 digits of ordering code: 003

#### With stand-off rubber seal



The series B41868, B41897, B41898 and B41899 have no sleeve.

In these series the pole is marked on the aluminum case instead. Refer to the series data sheet for details.

#### Suggestion for PCB hole diameter



Suggestion for PCB hole diameter, wire ø0.8 mm



Case size	Dimensions (	mm)				
d x I (mm)	B ±0.2	C ±0.5	D ±0.1	E ±0.1	a ±0.5	Øb
16 x 20	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16 x 25	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16 x 31.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16 x 35.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
18 x 20	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18 x 25	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18 x 31.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18 x 35	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18 x 40	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1



# Long useful life - 105 °C

#### In development

#### J leads

Last 3 digits of ordering code: 004



The series B41868, B41897, B41898 and B41899 have no sleeve.

In these series the pole is marked on the aluminum case instead. Refer to the series data sheet for details.

#### Suggestion for PCB hole diameter

Suggestion for PCB hole diameter, wire  $\emptyset 0.6 \text{ mm}$ 



Suggestion for PCB hole diameter, wire  $\emptyset 0.8 \text{ mm}$ 



Case size	Dimensio	ns (mm)			
d x I (mm)	C ±0.5	E ±0.5	J ±0.2	a ±0.5	Øb
10 x 12.5	3.2	0.7	1.2	5.0	0.6 ±0.05
10 x 16	3.2	0.7	1.2	5.0	0.6 ±0.05
10 x 20	3.2	0.7	1.2	5.0	0.6 ±0.05
12.5 x 20	3.2	0.7	1.2	5.0	0.6 ±0.05
12.5 x 25	3.2	0.7	1.2	5.0	0.6 ±0.05
16 x 20	3.5	0.7	1.6	7.5	0.8 ±0.05
16 x 25	3.5	0.7	1.6	7.5	0.8 ±0.05
16 x 31.5	3.5	0.7	1.6	7.5	0.8 ±0.05
16 x 35.5	3.5	0.7	1.6	7.5	0.8 ±0.05
16 x 40	3.5	0.7	1.6	7.5	0.8 ±0.05
18 x 20	3.5	0.7	1.6	7.5	0.8 ±0.1
18 x 25	3.5	0.7	1.6	7.5	0.8 ±0.1
18 x 31.5	3.5	0.7	1.6	7.5	0.8 ±0.1
18 x 35	3.5	0.7	1.6	7.5	0.8 ±0.1



# Single-ended capacitors

# Long useful life - 105 °C

#### In development

# Bent 90° leads for horizontal mounting pinning

Last 3 digits of ordering code: 012





The series B41868, B41897, B41898 and B41899 have no sleeve.

In these series the pole is marked on the aluminum case instead. Refer to the series data sheet for details.

Case size	Dimensions (mm)				
d x l (mm)	C ±0.5	E ±0.5	F ±0.5	a ±0.5	Øb
16 x 20	4.0	4.0	12.0	7.5	0.8 ±0.05
16 x 25	4.0	4.0	12.0	7.5	0.8 ±0.05
16 x 31.5	4.0	4.0	12.0	7.5	0.8 ±0.05
16 x 35.5	4.0	4.0	12.0	7.5	0.8 ±0.05
16 x 40	4.0	4.0	13.0	7.5	0.8 ±0.05
18 x 20	4.0	4.0	13.0	7.5	0.8 ±0.1
18 x 25	4.0	4.0	13.0	7.5	0.8 ±0.1
18 x 31.5	4.0	4.0	13.0	7.5	0.8 ±0.1
18 x 35	4.0	4.0	13.0	7.5	0.8 ±0.1
18 x 40	4.0	4.0	13.0	7.5	0.8 ±0.1

Bent leads for diameter 12.5 mm available upon request.



# Long useful life - 105 °C

# In development

# Packing units and box dimensions

#### Ammo pack



Case size	Dimensions (mm)			Packing
d x I (mm)	A <sub>max</sub>	B <sub>max</sub>	C <sub>max</sub>	units (pcs.)
8 x 11.5	345	60	240	1000
10 x 12.5	345	60	280	750
10 x 16	345	65	200	500
10 x 20	345	65	200	500
12.5 x 20	345	65	260	500
12.5 x 25	345	70	260	500
16 x 20	325	65	285	300
16 x 25	325	65	285	300
16 x 31.5	325	80	275	300
18 x 20	325	65	285	250
18 x 25	325	65	285	250
18 x 31.5	325	80	275	250



# Long useful life - 105 °C

# In development

# Overview of packing units and code numbers

								PAPR	
Case size d x l	Stan- dard, bulk	Тарес	I, Ammo	pack	Kinked leads, bulk	Cut leads, bulk	Crimped leads, blister	J leads, blister	Bent 90° leads, blister
mm	pcs.	pcs.			pcs.	pcs.	pcs.	pcs.	pcs.
8 x 11.5	1000	1000			—	_	-	_	
10 x 12.5	1000	750			-	1000	-	900	
10 x 16	1000	500			_	1000	-	675	
10 x 20	500	500			500	500	-	500	
12.5 x 20	350	500			350	350	-	300	1)
12.5 x 25	250	500			500	500	-	225	1)
16 x 20	250	300			200	200	200	200	420
16 x 25	250	300			200	200	216	216	216
16 x 31.5	200	300			250	250	180	180	180
16 x 35.5	100	_			100	100	150	150	150
16 x 40	125	-			100	100	72	72	72
18 x 20	175	250			175	175	200	200	420
18 x 25	150	250			150	150	200	200	200
18 x 31.5	100	250			100	100	150	150	150
18 x 35	100	-			100	100	150	150	150
18 x 40	125	_			100	100	72	-	72
The last three	000	Code	F (mm)	d (mm)	001	002	003	004	012
digits of the		006	3.5	8					
complete		800	5	812.5					
state the lead configuration		009	7.5	1618					

1) Available upon request



#### **Cautions and warnings**

#### **Personal safety**

The electrolytes used have been optimized both with a view to the intended application and with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC). Furthermore, some of the high-voltage electrolytes used are self-extinguishing.

As far as possible, we do not use any dangerous chemicals or compounds to produce operating electrolytes, although in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no alternative materials are currently known. We do, however, restrict the amount of dangerous materials used in our products to an absolute minimum.

Materials and chemicals used in our aluminum electrolytic capacitors are continuously adapted in compliance with the TDK Electronics Corporate Environmental Policy and the latest EU regulations and guidelines such as RoHS, REACH/SVHC, GADSL, and ELV.

MDS (Material Data Sheets) are available on our website for all types listed in the data book. MDS for customer specific capacitors are available upon request.

Nevertheless, the following rules should be observed when handling aluminum electrolytic capacitors: No electrolyte should come into contact with eyes or skin. If electrolyte does come into contact with the skin, wash the affected areas immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment. Avoid inhaling electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.



# Single-ended capacitors Long useful life - 105 °C

# Product safety

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of seperate file chapter "General technical information".

Торіс	Safety information	Reference chapter "General technical information"
Polarity	Make sure that polar capacitors are connected with the right polarity.	1 "Basic construction of aluminum electrolytic capacitors"
Reverse voltage	Voltages of opposite polarity should be prevented by connecting a diode.	3.1.6 "Reverse voltage"
Mounting position of capacitors with screw or multi-pin terminals	Multi-pin capacitors with pressure relief vent on the can base must not be mounted with terminals facing up unless otherwise specified.	11.1 "Mounting positions of capacitors with screw or multi-pin terminals"
Robustness of terminals	The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2.5 Nm M6: 4.0 Nm	11.2 "Mounting torques"
Mounting of single-ended capacitors	The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires. Avoid any compressive, tensile or flexural stress. Do not move the capacitor after soldering to PC board. Do not pick up the PC board by the soldered capacitor. Do not insert the capacitor on the PC board with a hole space different to the lead space specified.	11.3 "Mounting considerations for single-ended capacitors"
Soldering	Do not exceed the specified time or temperature limits during soldering.	11.5 "Soldering"
Soldering, cleaning agents	Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.	11.6 "Cleaning agents"
Upper category temperature	Do not exceed the upper category temperature.	7.2 "Maximum permissible operating temperature"
Passive flammability	Avoid external energy, e.g. fire.	8.1 "Passive flammability"



# Single-ended capacitors Long useful life - 105 °C

B43891

Торіс	Safety information	Reference chapter "General technical information"
Active flammability	Avoid overload of the capacitors.	8.2 "Active flammability"
Maintenance	Make periodic inspections of the capacitors. Before the inspection, make sure that the power supply is turned off and carefully discharge the capacitors. Do not apply excessive mechanical stress to the capacitor terminals when mounting.	10 "Maintenance"
Storage	Do not store capacitors at high temperatures or high humidity. Capacitors should be stored at +5 to +35 °C and a relative humidity of $\leq$ 75%.	7.3 "Shelf life and storage conditions"
		Reference chapter "Capacitors with screw terminals"
Breakdown strength of insulating sleeves	Do not damage the insulating sleeve, especially when ring clips are used for mounting.	"Screw terminals – accessories"

## Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.

Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.



Long useful life - 105 °C

# Symbols and terms

Symbol	English	German
С	Capacitance	Kapazität
C <sub>R</sub>	Rated capacitance	Nennkapazität
CS	Series capacitance	Serienkapazität
C <sub>S.T</sub>	Series capacitance at temperature T	Serienkapazität bei Temperatur T
C <sub>f</sub>	Capacitance at frequency f	Kapazität bei Frequenz f
d	Case diameter, nominal dimension	Gehäusedurchmesser, Nennmaß
d <sub>max</sub>	Maximum case diameter	Maximaler Gehäusedurchmesser
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatzserienwiderstand
ESR <sub>f</sub>	Equivalent series resistance at frequency f	Ersatzserienwiderstand bei Frequenz f
ESR <sub>T</sub>	Equivalent series resistance at temperature T	Ersatzserienwiderstand bei Temperatur T
f	Frequency	Frequenz
I	Current	Strom
I <sub>AC</sub>	Alternating current (ripple current)	Wechselstrom
I <sub>AC.RMS</sub>	Root-mean-square value of alternating current	Wechselstrom, Effektivwert
I <sub>AC,f</sub>	Ripple current at frequency f	Wechselstrom bei Frequenz f
I <sub>AC,max</sub>	Maximum permissible ripple current	Maximal zulässiger Wechselstrom
I <sub>AC.R</sub>	Rated ripple current	Nennwechselstrom
l <sub>leak</sub>	Leakage current	Reststrom
I <sub>leak,op</sub>	Operating leakage current	Betriebsreststrom
1	Case length, nominal dimension	Gehäuselänge, Nennmaß
I <sub>max</sub>	Maximum case length	Maximale Gehäuselänge
	(without terminals and mounting stud)	(ohne Anschlüsse und Gewindebolzen)
R	Resistance	Widerstand
R <sub>ins</sub>	Insulation resistance	Isolationswiderstand
R <sub>symm</sub>	Balancing resistance	Symmetrierwiderstand
Т	Temperature	Temperatur
$\Delta T$	Temperature difference	Temperaturdifferenz
Τ <sub>Α</sub>	Ambient temperature	Umgebungstemperatur
Т <sub>В</sub>	Capacitor base temperature	Temperatur des Gehäusebodens
Т <sub>С</sub>	Case temperature	Gehäusetemperatur
t	Time	Zeit
∆t	Period	Zeitraum
t <sub>b</sub>	Service life (operating hours)	Brauchbarkeitsdauer (Betriebszeit)
V	Voltage	Spannung
V <sub>F</sub>	Forming voltage	Formierspannung
V <sub>op</sub>	Operating voltage	Betriebsspannung
V <sub>R</sub>	Rated voltage, DC voltage	Nennspannung, Gleichspannung
V <sub>S</sub>	Surge voltage	Spitzenspannung
X <sub>C</sub>	Capacitive reactance	Kapazitiver Blindwiderstand



# Long useful life - 105 °C

Symbol	English	German
XL	Inductive reactance	Induktiver Blindwiderstand
Z	Impedance	Scheinwiderstand
Z <sub>T</sub>	Impedance at temperature T	Scheinwiderstand bei Temperatur T
$\tan\delta$	Dissipation factor	Verlustfaktor
λ	Failure rate	Ausfallrate
ε <sub>0</sub>	Absolute permittivity	Elektrische Feldkonstante
ε <sub>r</sub>	Relative permittivity	Dielektrizitätszahl
ω	Angular frequency; $2 \cdot \pi \cdot f$	Kreisfrequenz; $2 \cdot \pi \cdot f$

#### Note:

All dimensions are given in mm.



#### Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.



#### Important notes

- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, FilterCap, FormFit, InsuGate, LeaXield, MediPlas, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PiezoBrush, PlasmaBrush, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SurfIND, ThermoFuse, WindCap, XieldCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2024-02