



# Aluminum Electrolytic Capacitors

## Single-ended Capacitors

<b>Series/Type:</b>	<b>B41864</b>
<b>Status:</b>	<b>In development</b>
<b>Date:</b>	<b>March 2026</b>

**In development**

**Important information**

This series is not yet released for mass production and subject to change. The products delivered are engineering samples, prototypes or pre-series products, which are not intended for commercial use in series products of the purchaser. The supplier assumes no warranty or liability. Any use is at the sole risk of the purchaser.

**Long-life grade capacitors**
**Applications**

- Automotive electronics
- Industrial electronics

**Features**

- Compact dimensions
- High ripple current capability
- Useful life, 5000 h at  $T_A = 105\text{ °C}$
- RoHS-compatible

**Construction**

- Radial leads
- Charge-discharge proof, polar
- Aluminum case with PET sleeve
- Minus pole marking on the sleeve
- Case with pressure relief vent

**Delivery mode**

Terminal configurations and packing:

- Bulk
- Taped, Ammo pack
- Cut
- Kinked
- PAPR (Protection Against Polarity Reversal):  
crimped leads, J leads, bent leads



Refer to chapter “Single-ended capacitors - Taping, packing and lead configurations” for further details.

**In development**
**Specifications and characteristics in brief**


Rated voltage $V_R$ Surge voltage $V_S$	25 ... 35 V DC $1.15 \cdot V_R$			
Rated capacitance $C_R$ Capacitance tolerance	2800 ... 13000 $\mu$ F $0/+30 \triangleq A$			
Dissipation factor $\tan \delta$ ( $T_A = 20 \text{ }^\circ\text{C}$ , 120 Hz)	For capacitance higher than 1000 $\mu$ F add 0.02 for every increase of 1000 $\mu$ F.			
	$V_R$ (V DC)	25	35	
	$\tan \delta$	0.20	0.16	
Leakage current $I_{\text{leak}}$ ( $T_A = 20 \text{ }^\circ\text{C}$ , 2 min)	$I_{\text{leak}} \leq 0.01 \mu\text{A} \cdot \left( \frac{C_R}{\mu\text{F}} \cdot \frac{V_R}{\text{V}} \right)$			
Self-inductance ESL	Diameter (mm)	16	18	
	Approx. ESL (nH)	26	34	
Useful life <sup>1)</sup> $T_A = 105 \text{ }^\circ\text{C}$ ; $V_R$ ; $I_{\text{AC,R}}$	> 5000 h	Requirements: $ \Delta C/C  \leq 30\%$ of initial value $\tan \delta \leq 3$ times initial specified limit $I_{\text{leak}} \leq$ initial specified limit		
Voltage endurance test $T_A = 105 \text{ }^\circ\text{C}$ ; $V_R$	5000 h	Post test requirements: $ \Delta C/C  \leq 30\%$ of initial value $\tan \delta \leq 3$ times initial specified limit $I_{\text{leak}} \leq$ initial specified limit		
Vibration resistance test	To IEC 60068-2-6:2007, test Fc: Frequency range 10 Hz ... 2 kHz, displacement amplitude max. 1.5 mm, acceleration max. 20 g, duration 3 x 2 h. Capacitor rigidly clamped by the aluminum case e.g. using our standard fixture.			
Characteristics at low temperature	Max. impedance ratio at 120 Hz	$V_R$ (V DC)	25 V	35 V
		$Z_{-55 \text{ }^\circ\text{C}} / Z_{20 \text{ }^\circ\text{C}}$	3	3
Operating temperature range	$T_A = -55 \text{ }^\circ\text{C}/+105 \text{ }^\circ\text{C}$			
IEC climatic category	To IEC 60068-1:2013: 40/105/56 ( $-40 \text{ }^\circ\text{C}/+105 \text{ }^\circ\text{C}/56$ days damp heat test)			
Sectional specification <sup>2)</sup>	IEC 60384-4:2016			

1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.

2) Refer to chapter "General technical information, 2 Standards and specifications" for further details.

**In development**
**Dimensional drawing  
With stand-off rubber seal**

Diameters (mm): 16, 18



<sup>1)</sup> Supplied components may have different vent designs.  
They all offer the same functionality of pressure relief.

KAL1961-Q-E

**Dimensions and weights**

Dimensions (mm)				Approx. weight
d +0.5	l +2	a ±0.5	b ±0.05	g
16	20	7.5	0.8	7
16	25	7.5	0.8	9
16	31.5	7.5	0.8	11
16	35.5	7.5	0.8	13
16	40	7.5	0.8	15
18	20	7.5	0.8	10
18	25	7.5	0.8	12
18	31.5	7.5	0.8	15
18	35	7.5	0.8	16
18	40	7.5	0.8	18

**In development**
**Overview of available types**

Other voltage and capacitance ratings are available upon request.

$V_R$ (V DC)	25	35
	Case dimensions d x l (mm)	
$C_R$ (μF)		
2800		16 x 20
3500		16 x 25
3600		18 x 20
4100	16 x 20	
4700		16 x 31.5
4800		18 x 25
5200	16 x 25	
5300	18 x 20	
5400		16 x 35.5
6500		16 x 40
6600		18 x 31.5
6900	16 x 31.5	
7100	18 x 25	
7500		18 x 35
8000	16 x 35.5	
9000		18 x 40
9600	16 x 40	
9800	18 x 31.5	
11000	18 x 35	
13000	18 x 40	

**In development**
**Technical data and ordering codes**

$C_R$ 120 Hz 20 °C <sup>1)</sup> μF	Case dimensions d x l mm	$ESR_{max}$ 100 kHz –40 °C <sup>1)</sup> Ω	$ESR_{max}$ 100 kHz 20 °C <sup>1)</sup> Ω	$I_{AC,R}$ 100 kHz 105 °C <sup>1)</sup> A	Ordering code (composition see below)
$V_R = 25$ V DC					
4100	16 x 20	0.183	0.048	1.8	B41864A5418A***
5200	16 x 25	0.138	0.036	2.3	B41864A5528A***
5300	18 x 20	0.130	0.034	2.2	B41864A5538A***
6900	16 x 31.5	0.099	0.026	2.8	B41864A5698A***
7100	18 x 25	0.107	0.028	2.7	B41864A5718A***
8000	16 x 35.5	0.112	0.034	2.4	B41864A5808A***
9600	16 x 40	0.091	0.027	2.7	B41864A5968A***
9800	18 x 31.5	0.091	0.027	2.7	B41864A5988A***
11000	18 x 35	0.080	0.024	2.9	B41864A5119A***
13000	18 x 40	0.067	0.020	3.3	B41864A5139A***
$V_R = 35$ V DC					
2800	16 x 20	0.183	0.048	1.8	B41864A7288A***
3500	16 x 25	0.138	0.036	2.3	B41864A7358A***
3600	18 x 20	0.130	0.034	2.2	B41864A7368A***
4700	16 x 31.5	0.099	0.026	2.8	B41864A7478A***
4800	18 x 25	0.107	0.028	2.7	B41864A7488A***
5400	16 x 35.5	0.112	0.034	2.4	B41864A7548A***
6500	16 x 40	0.091	0.027	2.7	B41864A7658A***
6600	18 x 31.5	0.091	0.027	2.7	B41864A7668A***
7500	18 x 35	0.080	0.024	2.9	B41864A7758A***
9000	18 x 40	0.067	0.020	3.3	B41864A7908A***

**Composition of ordering code**

\*\*\* = Version

000 = for standard leads, bulk

001 = for kinked leads, bulk

002 = for cut leads, bulk

003 = for crimped leads, blister

004 = for J leads, blister

009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm  
(for d x l = 16 x 31.5 mm and 18 x 31.5 mm)

012 = for bent 90° leads, blister (for Ø 16 ... 18 mm)

1) Ambient temperature  $T_A$

**In development****Useful life<sup>1)</sup>**

Calculations of useful life are performed on request, based on operational conditions stated by the customer.

1) Refer to chapter “General technical information, 5 Useful life” on how to interpret useful life.

**In development**
**Taping**

Single-ended capacitors are available taped in Ammo pack from diameter 8 to 18 mm as follows:


Lead spacing  $F = 5.0$  mm ( $\varnothing d = 10 \dots 12.5$  mm)

Lead spacing  $F = 7.5$  mm ( $\varnothing d = 16 \dots 18$  mm).

The dimensions for  $F$ ,  $P_1$  and  $l_1$  max. are specified with reference to the center of the terminal wires.

**Lead spacing 5.0 mm ( $\varnothing d = 10 \dots 12.5$  mm)**

Last 3 digits of ordering code: 008



**Dimensions in mm**

$\varnothing d$	$F$	$H$	$W$	$W_0$	$W_1$	$W_2$	$H_0$	$P$	$P_0$	$P_1$	$l_1$	$t$	$\Delta h$	$D_0$
10	5.0	19.0	18	9.5	9.0	1.5	-	12.7	12.7	3.85	1.0	0.6	1.0	4.0
12.5				11.5				15.0	15.0	5.0				
Tolerance	+0.8 -0.2	$\pm 0.75$	$\pm 0.5$	min.	$\pm 0.5$	max.	$\pm 0.5$	$\pm 1.0$	$\pm 0.2$	$\pm 0.5$	max.	+0.3 -0.2	max.	$\pm 0.2$

Taping is available up to dimensions  $d \times l = 12.5 \times 25$  mm.

**In development**
**Lead spacing 7.5 mm (Ø d = 16 ... 18 mm)**

Last 3 digits of ordering code: 009


**Dimensions in mm**

Ø d	F	H	W	W <sub>0</sub>	W <sub>1</sub>	W <sub>2</sub>	P	P <sub>0</sub>	P <sub>1</sub>	l <sub>1</sub>	t	ΔP	Δh	D <sub>0</sub>
16	7.5	18.5	18.0	12.5	9.0	1.5	30.0	15.0	3.75	1.0	0.7	0	0	4.0
18														
Tolerance	±0.8	-0.5 +0.75	±0.5	min.	±0.5	max.	±1.0	±0.2	±0.5	max.	±0.2	±1.0	±1.0	±0.2


Taping is available up to dimensions d x l = 16 x 31.5 mm and 18 x 31.5 mm.

**In development**
**Cut or kinked leads**


Single-ended capacitors are available with cut or kinked leads. Other lead configurations also available upon request.

**Cut leads**

Last 3 digits of ordering code: 002

**With stand-off rubber seal**


KAL1085-I

**With flat rubber seal**


KAL1086-R


Case size d x l (mm)	Dimensions (mm) a ±0.5
10 x 12.5	5.0
10 x 16	5.0
10 x 20	5.0
12.5 x 20	5.0
12.5 x 25	5.0
16 x 20	7.5
16 x 25	7.5
16 x 31.5	7.5
16 x 35.5	7.5
16 x 40	7.5
18 x 20	7.5
18 x 25	7.5
18 x 31.5	7.5
18 x 35	7.5
18 x 40	7.5

**In development**


**Kinked leads**

Last 3 digits of ordering code: 001

With stand-off rubber seal




KAL1081-K




KAL1083-2

Case size d x l (mm)	Dimensions (mm) a ±0.5
10 x 20	5.0
12.5 x 20	5.0
12.5 x 25	5.0
16 x 20	7.5
16 x 25	7.5
16 x 31.5	7.5
16 x 35.5	7.5
18 x 20	7.5
18 x 25	7.5
18 x 31.5	7.5
18 x 35	7.5
18 x 40	7.5

**With flat rubber seal**



KAL1082-T



KAL1084-A


**In development**
**PAPR leads (Protection Against Polarity Reversal)**

These lead configurations ensure correct placement of the capacitor on the PCB with regard to polarity. PAPR leads are available for diameters from 10 mm up to 18 mm.

There are three configurations available: Crimped leads, J leads, bent 90° leads.


**Crimped leads**

Last 3 digits of ordering code: 003

**With stand-off rubber seal**


The series B41868, B41897, B41898 and B41899 have no sleeve.



In these series the pole is marked on the aluminum case instead. Refer to the series data sheet for details.

**Suggestion for PCB hole diameter**


Case size d x l (mm)	Dimensions (mm)					
	B ±0.2	C ±0.5	D ±0.1	E ±0.1	a ±0.5	Ø b
16 x 20	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16 x 25	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16 x 31.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16 x 35.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
18 x 20	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18 x 25	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18 x 31.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18 x 35	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18 x 40	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1

**In development**
**J leads**



Last 3 digits of ordering code: 004



KAL1934-H-E

The series B41868, B41897, B41898 and B41899 have no sleeve. In these series the pole is marked on the aluminum case instead. Refer to the series data sheet for details.


**Suggestion for PCB hole diameter**

 Suggestion for PCB hole diameter, wire  $\varnothing 0.6$  mm

 Suggestion for PCB hole diameter, wire  $\varnothing 0.8$  mm


Case size d x l (mm)	Dimensions (mm)				
	C ±0.5	E ±0.5	J ±0.2	a ±0.5	Ø b
10 x 12.5	3.2	0.7	1.2	5.0	0.6 ±0.05
10 x 16	3.2	0.7	1.2	5.0	0.6 ±0.05
10 x 20	3.2	0.7	1.2	5.0	0.6 ±0.05
12.5 x 20	3.2	0.7	1.2	5.0	0.6 ±0.05
12.5 x 25	3.2	0.7	1.2	5.0	0.6 ±0.05
16 x 20	3.5	0.7	1.6	7.5	0.8 ±0.05
16 x 25	3.5	0.7	1.6	7.5	0.8 ±0.05
16 x 31.5	3.5	0.7	1.6	7.5	0.8 ±0.05
16 x 35.5	3.5	0.7	1.6	7.5	0.8 ±0.05
16 x 40	3.5	0.7	1.6	7.5	0.8 ±0.05
18 x 20	3.5	0.7	1.6	7.5	0.8 ±0.1
18 x 25	3.5	0.7	1.6	7.5	0.8 ±0.1
18 x 31.5	3.5	0.7	1.6	7.5	0.8 ±0.1
18 x 35	3.5	0.7	1.6	7.5	0.8 ±0.1

**In development**
**Bent 90° leads for horizontal mounting pinning**


Last 3 digits of ordering code: 012



The series B41868, B41897, B41898 and B41899 have no sleeve. In these series the pole is marked on the aluminum case instead. Refer to the series data sheet for details.

Case size d x l (mm)	Dimensions (mm)				
	C ±0.5	E ±0.5	F ±0.5	a ±0.5	Ø b
16 x 20	4.0	4.0	12.0	7.5	0.8 ±0.05
16 x 25	4.0	4.0	12.0	7.5	0.8 ±0.05
16 x 31.5	4.0	4.0	12.0	7.5	0.8 ±0.05
16 x 35.5	4.0	4.0	12.0	7.5	0.8 ±0.05
16 x 40	4.0	4.0	13.0	7.5	0.8 ±0.05
18 x 20	4.0	4.0	13.0	7.5	0.8 ±0.1
18 x 25	4.0	4.0	13.0	7.5	0.8 ±0.1
18 x 31.5	4.0	4.0	13.0	7.5	0.8 ±0.1
18 x 35	4.0	4.0	13.0	7.5	0.8 ±0.1
18 x 40	4.0	4.0	13.0	7.5	0.8 ±0.1

Bent leads for diameter 12.5 mm available upon request.

**In development**
**Packing units and box dimensions**
**Ammo pack**


Case size d x l (mm)	Dimensions (mm)			Packing units (pcs.)
	A <sub>max</sub>	B <sub>max</sub>	C <sub>max</sub>	
10 x 12.5	345	60	280	750
10 x 16	345	65	200	500
10 x 20	345	65	200	500
12.5 x 20	345	65	260	500
12.5 x 25	345	70	260	500
16 x 20	325	65	285	300
16 x 25	325	65	285	300
16 x 31.5	325	80	275	300
18 x 20	325	65	285	250
18 x 25	325	65	285	250
18 x 31.5	325	80	275	250

**In development**
**Overview of packing units and code numbers**

					<b>PAPR</b>				
Case size d x l	Standard, bulk	Taped, Ammo pack			Kinked leads, bulk	Cut leads, bulk	Crimped leads, blister	J leads, blister	Bent 90° leads, blister
mm	pcs.	pcs.		pcs.	pcs.	pcs.	pcs.	pcs.	
10 x 12.5	1000	750		–	1000	–	900		
10 x 16	1000	500		–	1000	–	675		
10 x 20	500	500		500	500	–	500		
12.5 x 20	350	500		350	350	–	300	1)	
12.5 x 25	250	500		500	500	–	225	1)	
16 x 20	250	300		200	200	200	200	420	
16 x 25	250	300		200	200	216	216	216	
16 x 31.5	200	300		250	250	180	180	180	
16 x 35.5	100	–		100	100	150	150	150	
16 x 40	125	–		100	100	72	72	72	
18 x 20	175	250		175	175	200	200	420	
18 x 25	150	250		150	150	200	200	200	
18 x 31.5	100	250		100	100	150	150	150	
18 x 35	100	–		100	100	150	150	150	
18 x 40	125	–		100	100	72	–	72	
The last three digits of the complete ordering code state the lead configuration	<b>000</b>	Code	F (mm)	d (mm)	<b>001</b>	<b>002</b>	<b>003</b>	<b>004</b>	<b>012</b>
		<b>008</b>	5	10...12.5					
		<b>009</b>	7.5	16...18					

1) Available upon request

## Cautions and warnings

### Personal safety

The electrolytes used have been optimized both with a view to the intended application and with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC). Furthermore, some of the high-voltage electrolytes used are self-extinguishing.

As far as possible, we do not use any dangerous chemicals or compounds to produce operating electrolytes, although in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no alternative materials are currently known.

We do, however, restrict the amount of dangerous materials used in our products to an absolute minimum.

Materials and chemicals used in our aluminum electrolytic capacitors are continuously adapted in compliance with the TDK Electronics Corporate Environmental Policy and the latest EU regulations and guidelines such as RoHS, REACH/SVHC, GADSL, and ELV.

MDS (Material Data Sheets) are available on our website for all types listed in the data book.

MDS for customer specific capacitors are available upon request.

Nevertheless, the following rules should be observed when handling aluminum electrolytic capacitors: No electrolyte should come into contact with eyes or skin. If electrolyte does come into contact with the skin, wash the affected areas immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment. Avoid inhaling electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.

**Product safety**

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of separate file chapter "General technical information"

Topic	Safety information	Reference chapter "General technical information"
Polarity	Make sure that polar capacitors are connected with the right polarity.	1 "Basic construction of aluminum electrolytic capacitors"
Reverse voltage	Voltages of opposite polarity should be prevented by connecting a diode.	3.1.6 "Reverse voltage"
Mounting position of capacitors with screw or multi-pin terminals	Multi-pin capacitors with pressure relief vent on the can base must not be mounted with terminals facing up unless otherwise specified.	11.1 "Mounting positions of capacitors with screw or multi-pin terminals"
Robustness of terminals	The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2.5 Nm M6: 4.0 Nm	11.2 "Mounting torques"
Mounting of single-ended capacitors	The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires. Avoid any compressive, tensile or flexural stress. Do not move the capacitor after soldering to PC board. Do not pick up the PC board by the soldered capacitor. Do not insert the capacitor on the PC board with a hole space different to the lead space specified.	11.3 "Mounting considerations for single-ended capacitors"
Soldering	Do not exceed the specified time or temperature limits during soldering.	11.5 "Soldering"
Soldering, cleaning agents	Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.	11.6 "Cleaning agents"
Upper category temperature	Do not exceed the upper category temperature.	7.2 "Maximum permissible operating temperature"
Passive flammability	Avoid external energy, e.g. fire.	8.1 "Passive flammability"
Active flammability	Avoid overload of the capacitors.	8.2 "Active flammability"

Topic	Safety information	Reference chapter "General technical information"
Maintenance	Make periodic inspections of the capacitors. Before the inspection, make sure that the power supply is turned off and carefully discharge the capacitors. Do not apply excessive mechanical stress to the capacitor terminals when mounting.	10 "Maintenance"
Storage	Do not store capacitors at high temperatures or high humidity. Capacitors should be stored at +5 to +35 °C and a relative humidity of $\leq 75\%$ .	7.3 "Shelf life and storage conditions"
		Reference chapter "Capacitors with screw terminals"
Breakdown strength of insulating sleeves	Do not damage the sleeve, especially when ring clips are used for mounting.	"Screw terminals – accessories"

### Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.

Detailed information can be found on the Internet under [www.tdk-electronics.tdk.com/orderingcodes](http://www.tdk-electronics.tdk.com/orderingcodes).

**Symbols and terms**

Symbol	English	German
C	Capacitance	Kapazität
$\Delta C$	Capacitance difference	Kapazitätsdifferenz
$C_R$	Rated capacitance	Nennkapazität
$C_S$	Series capacitance	Serienkapazität
$C_{S,T}$	Series capacitance at temperature T	Serienkapazität bei Temperatur T
$C_f$	Capacitance at frequency f	Kapazität bei Frequenz f
d	Case diameter, nominal dimension	Gehäusedurchmesser, Nennmaß
$d_{max}$	Maximum case diameter	Maximaler Gehäusedurchmesser
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatzserienwiderstand
$ESR_f$	Equivalent series resistance at frequency f	Ersatzserienwiderstand bei Frequenz f
$ESR_T$	Equivalent series resistance at temperature T	Ersatzserienwiderstand bei Temperatur T
f	Frequency	Frequenz
I	Current	Strom
$I_{AC}$	Alternating current (ripple current)	Wechselstrom
$I_{AC,RMS}$	Root-mean-square value of alternating current	Wechselstrom, Effektivwert
$I_{AC,f}$	Ripple current at frequency f	Wechselstrom bei Frequenz f
$I_{AC,max}$	Maximum permissible ripple current	Maximal zulässiger Wechselstrom
$I_{AC,R}$	Rated ripple current	Nennwechselstrom
$I_{leak}$	Leakage current	Reststrom
$I_{leak,op}$	Operating leakage current	Betriebsreststrom
l	Case length, nominal dimension	Gehäuselänge, Nennmaß
$l_{max}$	Maximum case length (without terminals and mounting stud)	Maximale Gehäuselänge (ohne Anschlüsse und Gewindebolzen)
R	Resistance	Widerstand
$R_{ins}$	Insulation resistance	Isolationswiderstand
$R_{symm}$	Balancing resistance	Symmetrierwiderstand
T	Temperature	Temperatur
$\Delta T$	Temperature difference	Temperaturdifferenz
$T_A$	Ambient temperature	Umgebungstemperatur
$T_B$	Capacitor base temperature	Temperatur des Gehäusebodens
$T_C$	Case temperature	Gehäusetemperatur
t	Time	Zeit
$\Delta t$	Period	Zeitraum
$t_b$	Service life (operating hours)	Brauchbarkeitsdauer (Betriebszeit)
V	Voltage	Spannung
$V_F$	Forming voltage	Formierspannung
$V_{op}$	Operating voltage	Betriebsspannung
$V_R$	Rated voltage, DC voltage	Nennspannung, Gleichspannung
$V_S$	Surge voltage	Spitzenspannung

Symbol	English	German
$X_C$	Capacitive reactance	Kapazitiver Blindwiderstand
$X_L$	Inductive reactance	Induktiver Blindwiderstand
$Z$	Impedance	Scheinwiderstand
$Z_T$	Impedance at temperature T	Scheinwiderstand bei Temperatur T
$\tan \delta$	Dissipation factor	Verlustfaktor
$\lambda$	Failure rate	Ausfallrate
$\epsilon_0$	Absolute permittivity	Elektrische Feldkonstante
$\epsilon_r$	Relative permittivity	Dielektrizitätszahl
$\omega$	Angular frequency; $2 \cdot \pi \cdot f$	Kreisfrequenz; $2 \cdot \pi \cdot f$

**Note:**

All dimensions are given in mm.

## Important notes

The following applies to all products named in this publication:

- 1 Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2 We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3 **The warnings, cautions and product-specific notes must be observed.**
- 4 In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet ([www.tdk-electronics.tdk.com/material](http://www.tdk-electronics.tdk.com/material)). Should you have any more detailed questions, please contact our sales offices.
- 5 We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.  
We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6 Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.
- 7 **Our manufacturing sites serving the automotive business apply the IATF 16949 standard**. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System**. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.

## Important notes

- 8 The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, FilterCap, FormFit, InsuGate, LeaXield, MediPlas, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PiezoBrush, PlasmaBrush, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SurfIND, ThermoFuse, WindCap, XieldCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at [www.tdk-electronics.tdk.com/trademarks](http://www.tdk-electronics.tdk.com/trademarks).

Release 2024-02