

# **Aluminum electrolytic capacitors**

Large-size capacitors

Series/Type: B43268

Date: September 2019

© TDK Electronics AG 2019. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



## Large-size capacitors

Compact - 105 °C

#### Long-life grade capacitors

#### **Applications**

Onboard chargers

#### **Features**

- High CV product, compact
- High reliability
- High ripple current capability
- RoHS-compatible
- Qualification based on the AEC-Q200 standard

#### Construction

- Charge/discharge-proof, polar
- Aluminum case, insulated with PET sleeve and with insulation sheet at the can bottom
- Snap-in solder pins
- Minus pole marking on case surface
- Minus pole not insulated from case
- Overload protection by safety vent on the base

#### **Terminals**

- Standard version with 3 terminals, protection against polarity reversal: length 4.5 mm
- Version with 2 terminals with 2 different lengths available: 6.3 and 4.5 mm





Compact - 105 °C



# Specifications and characteristics in brief

Rated voltage V <sub>R</sub>	400 500 V DC				
Surge voltage V <sub>S</sub>	1.10 · V <sub>R</sub>				
Rated capacitance C <sub>R</sub>	68 820 μF				
Capacitance tolerance	±20% ≙ M				
Dissipation factor tan $\delta$ (20 °C, 120 Hz)	tan δ ≤ 0.20	tan δ ≤ 0.20			
Leakage current I <sub>leak</sub> (5 min, 20 °C)	$I_{leak} \le 0.3 \ \mu A \cdot \left(\frac{C}{\mu l}\right)$	$\frac{R}{F} \cdot \frac{V_R}{V} \Big)^{0.7}$	+ 4 μA		
Self-inductance ESL	Approx. 20 nH				
Useful life <sup>1)</sup> 105 °C; V <sub>R</sub> ; I <sub>AC,R</sub>	$ \Delta C/C  \leq 20\% \ \text{of initial value} \\ \tan\delta  \leq 2 \ \text{times initial specified limit} \\ I_{\text{leak}} \qquad \leq \text{initial specified limit}$			limit	
Voltage endurance test 105 °C; V <sub>R</sub>	2000 h	Post test requirements:			ed limit
Vibration resistance test	To IEC 60068-2-6 Frequency range acceleration max. Capacitor rigidly c	, test Fc: 10 Hz 2 5 <i>g</i> , durat	ion $3 \times 4$	h.	ude max. 0.375 mm,
Characteristics at low	Max. impedance			100 150	
temperature	ratio at 100 Hz	$\frac{V_R}{Z}$	,	400 450	500
		$\frac{Z_{-25} {}^{\circ}_{C} / Z}{Z_{-25} {}^{\circ}_{C}}$		4	8
		$Z_{-40}^{\circ}C/Z$	20 °C	10	14
IEC climatic category	To IEC 60068-1: $V_R \leq 450 \text{ V DC: } 40/105/56 \text{ (}-40 \text{ °C/+}105 \text{ °C/56 days damp heat test)} $ $V_R = 500 \text{ V DC: } 25/105/56 \text{ (}-25 \text{ °C/+}105 \text{ °C/56 days damp heat test)} $ The capacitors can be operated in the temperature range of $-40 \text{ °C to +}105 \text{ °C}$ but the impedance at $-40 \text{ °C must be taken into consideration.} $				
Sectional specification	IEC 60384-4	·			
Reference standard	AEC-Q200 <sup>2)</sup>				
	l .				

<sup>1)</sup> Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.

<sup>2)</sup> Refer to chapter "General technical information, 2.3 AEC-Q200 standard" for further details.






#### Compact - 105 °C

#### **Dimensional drawings**


#### Large-size capacitor, snap-in version with PET insulation



Large-size capacitors, snap-in terminals, length (6.3  $\pm 1$ ) mm.

Also available in a shorter version with a length of (4.5 -1) mm. Safety vent on the base.

Dimensions (mm)		Approx.	Packing units
d +1	l ±2	weight (g)	(pcs.)
22	30	12	160
22	35	15	160
22	40	18	160
22	45	20	160
22	50	24	160
25.4	25	13	130
25.4	30	17	130
25.4	35	19	130
25.4	40	22	130
25.4	45	25	130
25.4	50	29	130



Large-size capacitors, snap-in version with 3 terminals (length (4.5 - 1) mm). Safety vent on the base.

Dimens	ions (mm)	Approx.	Packing units
d +1	l ±2	weight (g)	(pcs.)
30	25	17	80
30	30	23	80
30	35	29	80
30	40	36	80
30	45	41	80
30	50	46	80
Dimens	ions (mm)	Approx.	Packing units
d +1		woight (a)	(noc.)
u + i	I +2.5/-2.0	weight (g)	(pcs.)
35	1 +2.5/-2.0 25	22	60
		- '0'	
35	25	22	60
35 35	25 30	22 29	60 60
35 35 35	25 30 35	22 29 36	60 60 60
35 35 35 35	25 30 35 40	22 29 36 41	60 60 60 60



Compact - 105 °C



## Packing example of large-size capacitors



For ecological reasons the packing is pure cardboard.

# Ordering codes for terminal styles

Identification in 3<sup>rd</sup> block of ordering code

Large-size capacitors				
Terminal version	Insulation			
	PET			
3 terminals 4.5 mm	M062			
2 terminals 4.5 mm	M067			
2 terminals 6.3 mm	M060			

## Ordering examples:

B43268A5157M062 } large-size capacitor, snap-in version with 3 terminals 4.5 mm and PET

insulation

insulation





## Compact - 105 °C

# Overview of available types

The capacitance and voltage ratings listed below are available in different case sizes upon request. Other voltage and capacitance ratings are also available upon request.

V <sub>R</sub> (V DC)	400	450	500
	Case dimensions	d×I (mm)	
C <sub>R</sub> (μF)			
68			22 × 35
			25.4 × 25
82			22 × 35
			25.4 × 30
100			22 × 45
			25.4 × 30
			30 × 25
120		22 × 30	22 × 45
		25.4 × 25	25.4 × 35
_			30 × 30
150	22 × 30	22 × 40	22 × 50
	25.4 × 25	25.4 × 30	25.4 × 45
		30 × 25	30 × 35
			35 × 30
180	22 × 35	22 × 45	25.4 × 45
	25.4 × 30	25.4 × 35	30 × 35
		30 × 30	35 × 30
220	22 × 40	22 × 50	30 × 40
	25.4 × 30	25.4 × 40	35 × 35
	30 × 25	$30 \times 30$ $35 \times 25$	
270	22 × 45	25.4 × 45	30 × 50
270	25.4 × 35	30 × 35	35 × 40
	30 × 30	35 × 30	33 × 40
330	25.4 × 40	25.4 × 50	35 × 45
330	30 × 35	30 × 40	35 × 45
	35 × 25	35 × 30	
390	25.4 × 50	30 × 45	35 × 50
000	30 × 35	35 × 35	00 × 00
	35 × 30	00 / 00	
	13033		



Compact - 105 °C



# Overview of available types

The capacitance and voltage ratings listed below are available in different case sizes upon request. Other voltage and capacitance ratings are also available upon request.

V <sub>R</sub> (V DC)	400	450	500
	Case dimensions d × I (mm	n)	
C <sub>R</sub> (μF)			
470	30 × 40	35 × 40	
	35 × 35		
560	30 × 50	35 × 45	
	35 × 40		
680	35 × 45		
820	35 × 50		





## Compact - 105 °C

# Technical data and ordering codes

$\overline{C_{R}}$	Case	ESR <sub>typ</sub>	ESR <sub>typ</sub>	Z <sub>max</sub>	I <sub>AC,max</sub>	I <sub>AC,max</sub>	I <sub>AC,R</sub>	Ordering code
100 Hz	dimensions	120 Hz	360 Hz	10 kHz	120 Hz	120 Hz	120 Hz	(composition see
20 °C	d×I	20 °C	60 °C	20 °C	60 °C	85 °C	105 °C	below)
μF	mm	mΩ	$m\Omega$	$m\Omega$	Α	Α	Α	
$V_R = 400$	V DC							
150	22 × 30	450	140	670	2.31	1.72	0.85	B43268A9157M06#
150	$25.4 \times 25$	470	150	700	2.17	1.63	0.80	B43268B9157M06#
180	22 × 35	380	110	560	2.66	1.99	0.98	B43268A9187M06#
180	$25.4 \times 30$	390	120	570	2.49	1.87	0.92	B43268B9187M06#
220	22 × 40	310	90	460	3.14	2.35	1.15	B43268A9227M06#
220	$25.4 \times 30$	320	110	480	2.91	2.17	1.07	B43268B9227M06#
220	30 × 25	310	95	460	2.97	2.23	1.10	B43268C9227M06#
270	22 × 45	250	75	380	3.73	2.78	1.36	B43268A9277M06#
270	$25.4 \times 35$	260	85	390	3.41	2.55	1.25	B43268B9277M06#
270	30 × 30	250	75	370	3.41	2.56	1.27	B43268C9277M06#
330	$25.4 \times 40$	220	70	320	4.01	2.99	1.47	B43268B9337M06#
330	30 × 35	210	60	310	3.98	2.99	1.48	B43268C9337M06#
330	35 × 25	220	75	330	3.87	2.89	1.42	B43268D9337M06#
390	$25.4 \times 50$	180	60	270	4.62	3.46	1.70	B43268A9397M06#
390	30 × 35	180	55	260	4.67	3.49	1.71	B43268B9397M06#
390	35 × 30	180	60	270	4.30	3.23	1.69	B43268C9397M06#
470	30 × 40	150	45	220	5.44	4.06	2.12	B43268A9477M06#
470	35 × 35	150	50	220	4.94	3.71	1.95	B43268B9477M06#
560	30 × 50	120	36	180	6.17	4.63	2.42	B43268A9567M06#
560	35 × 40	120	40	190	5.66	4.25	2.23	B43268B9567M06#
680	35 × 45	100	34	160	6.63	4.98	2.61	B43268A9687M06#
820	35 × 50	85	28	130	7.76	5.81	3.04	B43268A9827M06#

## Composition of ordering code


# = Terminal style

0 = snap-in 2 terminals (6.3 mm)

2 = snap-in 3 terminals (4.5 mm)

7 = snap-in 2 terminals (4.5 mm)







# Technical data and ordering codes

$\overline{C_R}$	Case	ESR <sub>typ</sub>	ESR <sub>typ</sub>	Z <sub>max</sub>	I <sub>AC,max</sub>	I <sub>AC,max</sub>	I <sub>AC,R</sub>	Ordering code
100 Hz	dimensions	120 Hz	360 Hz	10 kHz	120 Hz	120 Hz	120 Hz	(composition see
20 °C	d×I	20 °C	60 °C	20 °C	60 °C	85 °C	105 °C	below)
μF	mm	mΩ	mΩ	$m\Omega$	Α	Α	Α	
$V_R = 450$	V DC							
120	22 × 30	530	160	780	2.10	1.57	0.77	B43268A5127M06#
120	$25.4 \times 25$	540	170	800	1.99	1.49	0.73	B43268B5127M06#
150	22 × 40	420	120	620	2.50	1.88	0.93	B43268A5157M06#
150	$25.4 \times 30$	430	130	640	2.35	1.76	0.87	B43268B5157M06#
150	30 × 25	420	120	620	2.33	1.76	0.87	B43268C5157M06#
180	22 × 45	350	100	520	2.91	2.18	1.07	B43268A5187M06#
180	$25.4 \times 35$	360	110	530	2.71	2.03	1.00	B43268B5187M06#
180	30 × 30	350	100	510	2.64	1.99	0.99	B43268C5187M06#
220	22 × 50	290	85	430	3.44	2.58	1.27	B43268A5227M06#
220	$25.4 \times 40$	290	90	440	3.18	2.38	1.18	B43268B5227M06#
220	30 × 30	290	85	430	3.15	2.37	1.17	B43268C5227M06#
220	35 × 25	290	90	440	3.03	2.28	1.13	B43268D5227M06#
270	$25.4 \times 45$	240	75	360	3.75	2.81	1.38	B43268A5277M06#
270	30 × 35	230	70	350	3.68	2.76	1.37	B43268B5277M06#
270	35 × 30	240	70	350	3.48	2.63	1.39	B43268C5277M06#
330	$25.4 \times 50$	200	65	300	4.43	3.31	1.63	B43268A5337M06#
330	30 × 40	190	55	290	4.34	3.26	1.71	B43268B5337M06#
330	35 × 30	200	65	300	4.13	3.10	1.62	B43268C5337M06#
390	30 × 45	160	50	240	4.99	3.74	1.96	B43268A5397M06#
390	35 × 35	170	55	250	4.66	3.50	1.84	B43268B5397M06#
470	35 × 40	140	45	210	5.40	4.05	2.13	B43268A5477M06#
560	35 × 45	120	38	180	6.23	4.67	2.45	B43268A5567M06#

## Composition of ordering code

# = Terminal style

0 = snap-in 2 terminals (6.3 mm)

2 = snap-in 3 terminals (4.5 mm)

7 = snap-in 2 terminals (4.5 mm)





## Compact - 105 °C

# Technical data and ordering codes

$\overline{C_{R}}$	Case	ESR <sub>typ</sub>	ESR <sub>typ</sub>	Z <sub>max</sub>	I <sub>AC,max</sub>	I <sub>AC,max</sub>	I <sub>AC,R</sub>	Ordering code
100 Hz	dimensions	120 Hz	360 Hz	10 kHz	120 Hz	120 Hz	120 Hz	(composition see
20 °C	d×I	20 °C	60 °C	20 °C	60 °C	85 °C	105 °C	below)
μF	mm	mΩ	mΩ	$m\Omega$	Α	Α	Α	·
$V_R = 500$	V DC							
68	22 × 35	980	270	1430	1.68	1.25	0.59	B43268A6686M06#
68	$25.4 \times 25$	990	290	1460	1.69	1.25	0.59	B43268B6686M06#
82	22 × 35	810	230	1190	1.90	1.42	0.66	B43268A6826M06#
82	$25.4 \times 30$	820	240	1200	1.92	1.43	0.67	B43268B6826M06#
100	22 × 45	660	190	980	2.22	1.66	0.78	B43268A6107M06#
100	$25.4 \times 30$	680	200	1000	2.17	1.61	0.75	B43268B6107M06#
100	30 × 25	670	190	980	1.88	1.41	0.67	B43268C6107M06#
120	22 × 45	560	160	820	2.52	1.88	0.88	B43268A6127M06#
120	$25.4 \times 35$	560	170	830	2.47	1.84	0.86	B43268B6127M06#
120	30 × 30	560	160	820	2.10	1.59	0.76	B43268C6127M06#
150	22 × 50	450	130	660	2.98	2.22	1.04	B43268A6157M06#
150	$25.4 \times 45$	450	130	660	2.93	2.18	1.02	B43268B6157M06#
150	30 × 35	440	130	650	2.48	1.88	0.89	B43268C6157M06#
150	35 × 30	430	130	640	2.46	1.86	0.93	B43268D6157M06#
180	$25.4 \times 45$	370	110	540	3.35	2.49	1.16	B43268A6187M06#
180	30 × 35	360	100	530	3.00	2.25	1.06	B43268B6187M06#
180	35 × 30	360	110	540	2.87	2.16	1.08	B43268C6187M06#
220	30 × 40	300	85	430	3.53	2.65	1.31	B43268A6227M06#
220	35 × 35	300	90	440	3.31	2.50	1.25	B43268B6227M06#
270	30 × 50	240	70	350	4.11	3.09	1.54	B43268A6277M06#
270	35 × 40	240	70	360	3.88	2.92	1.46	B43268B6277M06#
330	35 × 45	200	60	300	4.56	3.43	1.71	B43268A6337M06#
390	35 × 50	170	50	250	5.23	3.93	1.95	B43268A6397M06#

#### Composition of ordering code

# = Terminal style


0 = snap-in 2 terminals (6.3 mm)

2 = snap-in 3 terminals (4.5 mm)

7 = snap-in 2 terminals (4.5 mm)

Other voltage and capacitance ratings are also available upon request.







#### Useful life1)

For useful life calculations, please use our web-based "AlCap Useful Life Calculation Tool", which can be found on the Internet under the following link:


www.tdk-electronics.tdk.com/alcap

The AlCap Useful Life Calculation Tool provides calculations of useful life as well as additional data for selected capacitor types under operating conditions defined by the user.

In addition, it is possible to calculate useful life expectancies based on temperatures measured by the user in the application.


#### Frequency characteristics of ESR

Typical behavior



#### Impedance Z versus frequency f

Typical behavior at 20 °C



<sup>1)</sup> Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.





Compact - 105 °C

#### **Cautions and warnings**

#### **Personal safety**

The electrolytes used have been optimized both with a view to the intended application and with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC). Furthermore, some of the high-voltage electrolytes used are self-extinguishing.

As far as possible, we do not use any dangerous chemicals or compounds to produce operating electrolytes, although in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no alternative materials are currently known. We do, however, restrict the amount of dangerous materials used in our products to an absolute minimum.

Materials and chemicals used in our aluminum electrolytic capacitors are continuously adapted in compliance with the TDK Electronics Corporate Environmental Policy and the latest EU regulations and guidelines such as RoHS, REACH/SVHC, GADSL, and ELV.

MDS (Material Data Sheets) are available on our website for all types listed in the data book. MDS for customer specific capacitors are available upon request.

MSDS (Material Safety Data Sheets) are available for our electrolytes upon request.

Nevertheless, the following rules should be observed when handling aluminum electrolytic capacitors: No electrolyte should come into contact with eyes or skin. If electrolyte does come into contact with the skin, wash the affected areas immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment. Avoid inhaling electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.



Compact - 105 °C



# **Product safety**

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of chapter "General technical information".

Topic	Safety information	Reference chapter "General technical information"
Polarity	Make sure that polar capacitors are connected with the right polarity.	1 "Basic construction of aluminum electrolytic capacitors"
Reverse voltage	Voltages of opposite polarity should be prevented by connecting a diode.	3.1.6 "Reverse voltage"
Mounting position of screw-terminal capacitors	Screw terminal capacitors must not be mounted with terminals facing down unless otherwise specified.	11.1. "Mounting positions of capacitors with screw terminals"
Robustness of terminals	The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2.5 Nm M6: 4.0 Nm	11.3 "Mounting torques"
Mounting of single-ended capacitors	The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires.  Avoid any compressive, tensile or flexural stress.  Do not move the capacitor after soldering to PC board.  Do not pick up the PC board by the soldered capacitor.  Do not insert the capacitor on the PC board with a hole space different to the lead space specified.	11.4 "Mounting considerations for single-ended capacitors"
Soldering	Do not exceed the specified time or temperature limits during soldering.	11.5 "Soldering"
Soldering, cleaning agents	Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.	11.6 "Cleaning agents"
Upper category temperature	Do not exceed the upper category temperature.	7.2 "Maximum permissible operating temperature"
Passive flammability	Avoid external energy, e.g. fire.	8.1 "Passive flammability"





#### Compact - 105 °C


Topic	Safety information	Reference chapter "General technical information"
Active flammability	Avoid overload of the capacitors.	8.2 "Active flammability"
Maintenance	Make periodic inspections of the capacitors.  Before the inspection, make sure that the power supply is turned off and carefully discharge the capacitors.  Do not apply excessive mechanical stress to the capacitor terminals when mounting.	10 "Maintenance"
Storage	Do not store capacitors at high temperatures or high humidity. Capacitors should be stored at +5 to +35 °C and a relative humidity of ≤ 75%.	7.3 "Shelf life and storage conditions"
		Reference chapter "Capacitors with screw terminals"
Breakdown strength of insulating sleeves	Do not damage the insulating sleeve, especially when ring clips are used for mounting.	"Screw terminals — accessories"

#### Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.

Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.







# Symbols and terms

Symbol	English	German
С	Capacitance	Kapazität
$C_R$	Rated capacitance	Nennkapazität
$C_{S}$	Series capacitance	Serienkapazität
$C_{S,T}$	Series capacitance at temperature T	Serienkapazität bei Temperatur T
$C_{f}$	Capacitance at frequency f	Kapazität bei Frequenz f
d	Case diameter, nominal dimension	Gehäusedurchmesser, Nennmaß
$d_{\text{max}}$	Maximum case diameter	Maximaler Gehäusedurchmesser
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatzserienwiderstand
ESR <sub>f</sub>	Equivalent series resistance at frequency f	Ersatzserienwiderstand bei Frequenz f
ESR <sub>T</sub>	Equivalent series resistance at temperature T	Ersatzserienwiderstand bei Temperatur T
f	Frequency	Frequenz
1	Current	Strom
I <sub>AC</sub>	Alternating current (ripple current)	Wechselstrom
$I_{AC,RMS}$	Root-mean-square value of alternating current	Wechselstrom, Effektivwert
$I_{AC,f}$	Ripple current at frequency f	Wechselstrom bei Frequenz f
$I_{AC,max}$	Maximum permissible ripple current	Maximal zulässiger Wechselstrom
$I_{AC,R}$	Rated ripple current	Nennwechselstrom
l <sub>leak</sub>	Leakage current	Reststrom
I <sub>leak,op</sub>	Operating leakage current	Betriebsreststrom
I	Case length, nominal dimension	Gehäuselänge, Nennmaß
I <sub>max</sub>	Maximum case length (without terminals and mounting stud)	Maximale Gehäuselänge (ohne Anschlüsse und Gewindebolzen)
R	Resistance	Widerstand
$R_{ins}$	Insulation resistance	Isolationswiderstand
$R_{symm}$	Balancing resistance	Symmetrierwiderstand
Т	Temperature	Temperatur
$\DeltaT$	Temperature difference	Temperaturdifferenz
$T_A$	Ambient temperature	Umgebungstemperatur
$T_C$	Case temperature	Gehäusetemperatur
$T_B$	Capacitor base temperature	Temperatur des Gehäusebodens
t	Time	Zeit
$\Delta t$	Period	Zeitraum
$t_{b}$	Service life (operating hours)	Brauchbarkeitsdauer (Betriebszeit)





# $\textbf{Compact} - \textbf{105}~^{\circ}\textbf{C}$

Symbol	English	German
V	Voltage	Spannung
$V_{F}$	Forming voltage	Formierspannung
$V_{op}$	Operating voltage	Betriebsspannung
$V_R$	Rated voltage, DC voltage	Nennspannung, Gleichspannung
$V_S$	Surge voltage	Spitzenspannung
$X_{C}$	Capacitive reactance	Kapazitiver Blindwiderstand
$X_L$	Inductive reactance	Induktiver Blindwiderstand
Z	Impedance	Scheinwiderstand
$Z_T$	Impedance at temperature T	Scheinwiderstand bei Temperatur T
$tan \ \delta$	Dissipation factor	Verlustfaktor
λ	Failure rate	Ausfallrate
$\epsilon_{0}$	Absolute permittivity	Elektrische Feldkonstante
$\epsilon_{r}$	Relative permittivity	Dielektrizitätszahl
ω	Angular velocity; $2 \cdot \pi \cdot f$	Kreisfrequenz; $2 \cdot \pi \cdot f$

## Note

All dimensions are given in mm.



## **Important notes**

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.



#### Important notes

- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10