

# **Aluminum electrolytic capacitors**

Large-size capacitors

Series/Type: B43649

Date: August 2022

© TDK Electronics AG 2022. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.

# Ultra compact - 105 °C

#### B43649

#### Long-life grade capacitors

#### **Applications**

Onboard chargers

#### **Features**

- Extremely high CV product, ultra compact
- High reliability
- High ripple current capability
- RoHS-compatible
- Qualification based on the AEC-Q200 standard

#### Construction

- Charge/discharge-proof, polar
- Aluminum case covered with PET sleeve without bottom disc
- Snap-in solder pins
- Minus pole marking on PET sleeve
- Minus pole not insulated from case
- Overload protection by pressure relief device on the base

#### **Terminals**

- Standard version with 3 terminals protection against polarity reversal: length 4.5 mm
- Version with 2 terminals with 2 different lengths available: 6.3 and 4.5 mm
- Vibration-resistant version with 2 terminals: length 4.5 mm





| Large-size capacitors  | B43649 |
|------------------------|--------|
| Ultra compact – 105 °C |        |

# Specifications and characteristics in brief


| Rated voltage V <sub>R</sub>               | 450 500 V DC  |   |   |                     |  |  |  |
|--|---|---|---|---------------------|--|--|--|
| Surge voltage V <sub>S</sub>               | 1.10 · V <sub>R</sub>   |   |   |                     |  |  |  |
| Rated capacitance C <sub>R</sub>           | 100 820 μF  |   |   |                     |  |  |  |
| Capacitance tolerance                      | ±20% ≙ M  |   |   |                     |  |  |  |
| Dissipation factor tan $\delta$            | ≤ 0.20  |   |   |                     |  |  |  |
| (20 °C, 120 Hz)                            |   |   |   |                     |  |  |  |
| Leakage current I <sub>leak</sub>          | /C <sub>E</sub>   | V <sub>P</sub> \0.7                       |   |                     |  |  |  |
| (5 min, 20 °C)                             | $I_{leak} \le 0.3 \ \mu A \cdot \left(\frac{C_R}{\mu F}\right)$ | + 4 μA                                    |   |                     |  |  |  |
| Self-inductance ESL                        | Approx. 20 nH   |   |   |                     |  |  |  |
| Useful life <sup>1)</sup>                  |   | Requirements:                             |   |                     |  |  |  |
| 105 °C; V <sub>R</sub> ; I <sub>AC,R</sub> | > 3000 h  |   | ≤ 20% of initial va                           |                     |  |  |  |
|  |   |   | ≤ 2 times initial s                           |                     |  |  |  |
|  |   | I <sub>leak</sub>                         | ≤ initial specified                           | limit               |  |  |  |
| Voltage endurance test                     |   | Post test requirem                        | nents:  |                     |  |  |  |
| 105 °C; V <sub>R</sub>                     | 2000 h  |   | ≤ 10% of initial va                           |                     |  |  |  |
|  |   |   | ≤ 1.3 times initial                           | •                   |  |  |  |
|  |   | I <sub>leak</sub>                         | ≤ initial specified                           | limit               |  |  |  |
| Vibration resistance test                  | To IEC 60068-2-   | 6:2007, test Fc:                          |   |                     |  |  |  |
|  | , , ,   | 10Hz 2 kHz, dis                           |   | ude max.            |  |  |  |
|  | ,   | eration max. 5 <i>g</i> , du              |   |                     |  |  |  |
|  | · •   | ed by its body whicl                      | h is rigidly clampe                           | ed to the work sur- |  |  |  |
|  | face  |   |   |                     |  |  |  |
| Characteristics at low                     | Max. impedance  | $V_{R}$                                   | 450 V   | ≥ 475 V             |  |  |  |
| temperature                                | ratio at 100 Hz   | Z <sub>-25 °C</sub> / Z <sub>20 °C</sub>  | <sub>C</sub> 5                                | 5                   |  |  |  |
|  |   | Z <sub>-40 °C</sub> / Z <sub>20 °C</sub>  | C 14  | 11                  |  |  |  |
|  |   |   | <u>,                                     </u> |                     |  |  |  |
| IFO elimentia antonomo                     | T- IFO 00000 4  |   |   |                     |  |  |  |
| IEC climatic category                      | To IEC 60068-1:   | CL 10E °C/E6 days                         | down boot toot)                               |                     |  |  |  |
|  | ,   | C/+105 °C/56 days<br>an be operated in th | . ,   | nge of _40 °C to    |  |  |  |
|  |   | mpedance at –40 °                         | •   | •                   |  |  |  |
| Sectional specification                    | IEC 60384-4:201   | •   | cact be taller!                               | conoraciadon.       |  |  |  |
| Reference standard                         |   |   |   |                     |  |  |  |
| Reference standard                         | AEC-Q200 REV D <sup>2)</sup>                                    |   |   |                     |  |  |  |

<sup>1)</sup> Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.
2) Refer to chapter "General technical information, 2.3 AEC-Q200 standard" for further details.




# Ultra compact - 105 °C

# Dimensional drawings Large-size capacitor, snap-in version with PET sleeve



Large-size capacitors, snap-in terminals, length (6.3±1) mm. Also available in a shorter version with a length of (4.5–1) mm. Pressure relief device on the base.

| Dimensions (mm) |      | Approx.    | Packing units |
|-----------------|------|------------|---------------|
| d +1            | I ±2 | weight (g) | (pcs.)        |
| 22              | 25   | 9          | 160           |
| 22              | 30   | 12         | 160           |
| 22              | 35   | 15         | 160           |
| 22              | 40   | 18         | 160           |
| 22              | 45   | 20         | 160           |
| 22              | 50   | 24         | 160           |
| 25              | 25   | 13         | 130           |
| 25              | 30   | 17         | 130           |
| 25              | 35   | 19         | 130           |
| 25              | 40   | 22         | 130           |
| 25              | 45   | 25         | 130           |
| 25              | 50   | 29         | 130           |
| 25              | 55   | 32         | 130           |



Large-size capacitors, snap-in version with 3 terminals length (4.5–1) mm.


Pressure relief device on the base.

| Dimen                                    | sions (mm)                               | Approx.                        | Packing units            |
|--|--|--------------------------------|--------------------------|
| d +1                                     | I ±2                                     | weight (g)                     | (pcs.)                   |
| 30                                       | 25                                       | 17                             | 80                       |
| 30                                       | 30                                       | 23                             | 80                       |
| 30                                       | 35                                       | 29                             | 80                       |
| 30                                       | 40                                       | 36                             | 80                       |
| 30                                       | 45                                       | 41                             | 80                       |
| 30                                       | 50                                       | 46                             | 80                       |
| 30                                       | 55                                       | 53                             | 80                       |
| 30                                       | 60                                       | 58                             | 60                       |
|  |  |                                |                          |
| Dimen                                    | sions (mm)                               | Approx.                        | Packing units            |
| Dimen<br>d +1                            | sions (mm)<br>I +2.5/–2.0                | Approx.<br>weight (g)          | Packing units (pcs.)     |
|  | . ,                                      | · · ·                          |                          |
| d +1                                     | I +2.5/–2.0                              | weight (g)                     | (pcs.)                   |
| d +1<br>35                               | I +2.5/–2.0<br>25                        | weight (g)                     | (pcs.)                   |
| d +1<br>35<br>35                         | 1 +2.5/–2.0<br>25<br>30                  | weight (g) 22 29               | (pcs.)<br>60<br>60       |
| d +1<br>35<br>35<br>35                   | 1 +2.5/-2.0<br>25<br>30<br>35            | weight (g) 22 29 36            | (pcs.)<br>60<br>60       |
| d +1<br>35<br>35<br>35<br>35             | 1+2.5/-2.0<br>25<br>30<br>35<br>40       | weight (g)  22 29 36 41        | (pcs.) 60 60 60 60       |
| d +1<br>35<br>35<br>35<br>35<br>35<br>35 | 1+2.5/-2.0<br>25<br>30<br>35<br>40<br>45 | weight (g)  22  29  36  41  56 | (pcs.) 60 60 60 60 60 60 |



# Ultra compact - 105 °C

## Large-size capacitor, vibration-resistant terminal version with PET sleeve



|       |             | Т          | Г             |
|-------|-------------|------------|---------------|
| Dimen | sions (mm)  | Approx.    | Packing units |
| d +1  | I ±2        | weight (g) | (pcs.)        |
| 30    | 25          | 17         | 80            |
| 30    | 30          | 23         | 80            |
| 30    | 35          | 29         | 80            |
| 30    | 40          | 36         | 80            |
| 30    | 45          | 41         | 80            |
| 30    | 50          | 46         | 80            |
| 30    | 55          | 53         | 80            |
| 30    | 60          | 58         | 60            |
| Dimen | sions (mm)  | Approx.    | Packing units |
| d +1  | I +2.5/-2.0 | weight (g) | (pcs.)        |
| 35    | 25          | 22         | 60            |
| 35    | 30          | 29         | 60            |
| 35    | 35          | 36         | 60            |
| 35    | 40          | 41         | 60            |
| 35    | 45          | 56         | 60            |
| 35    | 50          | 70         | 60            |
| 35    | 55          | 81         | 60            |
| 35    | 60          | 90         | 36            |

Large-size capacitors, vibration-resistant terminals, length (4.5±1) mm.
Pressure relief device on the base.

## Ultra compact - 105 °C

#### Packing example of large-size capacitors



For ecological reasons the packing is cardboard.

#### Ordering codes for terminal styles

| Large-size capacitors                  |  |
|--|--|
| Terminal version                       | Identification in 3 <sup>rd</sup> block of ordering code |
| 3 terminals 4.5 mm                     | M052   |
| 2 terminals 4.5 mm                     | M057   |
| 2 terminals 6.3 mm                     | M050   |
| 2 vibration-resistant terminals 4.5 mm | M058   |

Ordering examples:

B43649A5157M052} large-size capacitor, snap-in version with 3 terminals 4.5 mm and

PET sleeve

B43649A5157M057} large-size capacitor, snap-in version with 2 terminals 4.5 mm and

PET sleeve



Ultra compact - 105 °C

B43649

#### Overview of available types

The capacitance and voltage ratings listed below are available in different case sizes upon request. Other voltage and capacitance ratings are also available upon request.

| V <sub>R</sub> (V DC) | 450             | 475        | 500     |
|-----------------------|-----------------|------------|---------|
|                       | Case dimensions | d x I (mm) |         |
| C <sub>R</sub> (µF)   |                 |            |         |
| 100                   | 22 x 25         |            | 25 x 25 |
| 120                   | 22 x 30         | 25 x 25    | 25 x 30 |
| 150                   | 22 x 30         | 25 x 30    | 25 x 35 |
|                       | 25 x 25         |            | 30 x 25 |
| 180                   | 22 x 35         | 25 x 35    | 25 x 40 |
|                       | 25 x 30         | 30 x 25    | 30 x 30 |
| 220                   | 22 x 45         | 25 x 40    | 25 x 45 |
|                       | 25 x 35         | 30 x 30    | 30 x 35 |
|                       | 30 x 25         | 35 x 25    | 35 x 25 |
| 270                   | 22 x 50         | 25 x 50    | 25 x 55 |
|                       | 25 x 40         | 30 x 35    | 30 x 40 |
|                       | 30 x 30         | 35 x 30    | 35 x 30 |
| 330                   | 25 x 45         | 25 x 55    | 30 x 45 |
|                       | 30 x 35         | 30 x 40    | 35 x 35 |
|                       | 35 x 25         | 35 x 30    |         |
| 390                   | 25 x 55         | 30 x 45    | 30 x 50 |
|                       | 30 x 40         | 35 x 35    | 35 x 40 |
|                       | 35 x 30         |            |         |
| 470                   | 30 x 45         | 30 x 55    | 30 x 60 |
|                       | 35 x 35         | 35 x 40    | 35 x 45 |
| 560                   | 30 x 50         | 30 x 60    | 35 x 55 |
|                       | 35 x 40         | 35 x 45    |         |
| 680                   | 35 x 45         | 35 x 55    | 35 x 60 |
| 820                   | 35 x 50         | 35 x 60    |         |



Ultra compact - 105 °C

B43649

#### Technical data and ordering codes

|                          |                           |                              |                              | _                          |                               |                               |                             | T =                            |  |
|--------------------------|---------------------------|------------------------------|------------------------------|----------------------------|-------------------------------|-------------------------------|-----------------------------|--------------------------------|--|
| C <sub>R</sub><br>100 Hz | Case dimensions           | ESR <sub>typ</sub><br>120 Hz | ESR <sub>typ</sub><br>360 Hz | Z <sub>max</sub><br>10 kHz | I <sub>AC,max</sub><br>120 Hz | I <sub>AC,max</sub><br>120 Hz | I <sub>AC,R</sub><br>120 Hz | Ordering code (composition see |  |
| 20 °C                    | d x I                     | 20 °C                        | 60 °C                        | 20 °C                      | 60 °C                         | 85 °C                         | 105 °C                      | below)                         |  |
| μF                       | mm                        | mΩ                           | mΩ                           | mΩ                         | A                             | A                             | Α                           | bolow)                         |  |
| $V_{R} = 450$            | V <sub>R</sub> = 450 V DC |                              |                              |                            |                               |                               |                             |                                |  |
| 100                      | 22 x 25                   | 1010                         | 250                          | 1610                       | 1.60                          | 1.20                          | 0.70                        | B43649A5107M05#                |  |
| 120                      | 22 x 30                   | 840                          | 210                          | 1340                       | 1.85                          | 1.39                          | 0.81                        | B43649A5127M05#                |  |
| 150                      | 22 x 30                   | 680                          | 170                          | 1080                       | 2.22                          | 1.66                          | 0.96                        | B43649A5157M05#                |  |
| 150                      | 25 x 25                   | 690                          | 180                          | 1090                       | 2.11                          | 1.58                          | 0.91                        | B43649B5157M05#                |  |
| 180                      | 22 x 35                   | 570                          | 140                          | 900                        | 2.58                          | 1.93                          | 1.12                        | B43649A5187M05#                |  |
| 180                      | 25 x 30                   | 570                          | 150                          | 910                        | 2.43                          | 1.82                          | 1.06                        | B43649B5187M05#                |  |
| 220                      | 22 x 45                   | 460                          | 110                          | 730                        | 3.07                          | 2.30                          | 1.33                        | B43649A5227M05#                |  |
| 220                      | 25 x 35                   | 470                          | 120                          | 740                        | 2.86                          | 2.15                          | 1.25                        | B43649B5227M05#                |  |
| 220                      | 30 x 25                   | 480                          | 140                          | 770                        | 2.64                          | 1.98                          | 1.15                        | B43649C5227M05#                |  |
| 270                      | 22 x 50                   | 380                          | 95                           | 600                        | 3.66                          | 2.74                          | 1.59                        | B43649A5277M05#                |  |
| 270                      | 25 x 40                   | 380                          | 100                          | 610                        | 3.39                          | 2.54                          | 1.47                        | B43649B5277M05#                |  |
| 270                      | 30 x 30                   | 390                          | 110                          | 630                        | 3.10                          | 2.32                          | 1.35                        | B43649C5277M05#                |  |
| 330                      | 25 x 45                   | 310                          | 80                           | 500                        | 4.02                          | 3.00                          | 1.74                        | B43649A5337M05#                |  |
| 330                      | 30 x 35                   | 320                          | 90                           | 510                        | 3.64                          | 2.73                          | 1.58                        | B43649B5337M05#                |  |
| 330                      | 35 x 25                   | 340                          | 120                          | 560                        | 3.26                          | 2.44                          | 1.41                        | B43649C5337M05#                |  |
| 390                      | 25 x 55                   | 260                          | 70                           | 420                        | 4.66                          | 3.49                          | 2.02                        | B43649A5397M05#                |  |
| 390                      | 30 x 40                   | 270                          | 75                           | 430                        | 4.12                          | 3.07                          | 1.72                        | B43649B5397M05#                |  |
| 390                      | 35 x 30                   | 290                          | 90                           | 460                        | 3.72                          | 2.77                          | 1.55                        | B43649C5397M05#                |  |
| 470                      | 30 x 45                   | 230                          | 65                           | 360                        | 4.79                          | 3.56                          | 1.99                        | B43649A5477M05#                |  |
| 470                      | 35 x 35                   | 240                          | 75                           | 380                        | 4.32                          | 3.21                          | 1.80                        | B43649B5477M05#                |  |
| 560                      | 30 x 50                   | 190                          | 55                           | 310                        | 5.53                          | 4.11                          | 2.29                        | B43649A5567M05#                |  |
| 560                      | 35 x 40                   | 200                          | 65                           | 320                        | 4.95                          | 3.68                          | 2.06                        | B43649B5567M05#                |  |
| 680                      | 35 x 45                   | 170                          | 55                           | 270                        | 5.74                          | 4.26                          | 2.38                        | B43649A5687M05#                |  |
| 820                      | 35 x 50                   | 140                          | 50                           | 230                        | 6.62                          | 4.91                          | 2.74                        | B43649A5827M05#                |  |

#### Composition of ordering code

<sup>#=</sup>Terminal style

<sup>0 =</sup> snap-in 2 terminals (6.3 mm)

<sup>2 =</sup> snap-in 3 terminals (4.5 m)

<sup>7 =</sup> snap-in 2 terminals (4.5 mm)

<sup>8 = 2</sup> vibration-resistant terminals (4.5 mm) - available in diameter 30 and 35 mm

B43649

#### Ultra compact - 105 °C

#### Technical data and ordering codes

|              |            |                    | 1           |                  |              | 1            | 1          |                  |
|--------------|------------|--------------------|-------------|------------------|--------------|--------------|------------|------------------|
| $C_{R}$      | Case       | ESR <sub>typ</sub> | $ESR_{typ}$ | Z <sub>max</sub> | $I_{AC,max}$ | $I_{AC,max}$ | $I_{AC,R}$ | Ordering code    |
| 100 Hz       | dimensions | 120 Hz             | 360 Hz      | 10 kHz           | 120 Hz       | 120 Hz       | 120 Hz     | (composition see |
| 20 °C        | dxl        | 20 °C              | 60 °C       | 20 °C            | 60 °C        | 85 °C        | 105 °C     | below)           |
| μF           | mm         | mΩ                 | mΩ          | mΩ               | Α            | Α            | Α          |                  |
| $V_{R} = 47$ | 5 V DC     |                    |             |                  |              |              |            |                  |
| 120          | 25 x 25    | 680                | 190         | 1020             | 1.95         | 1.47         | 0.74       | B43649A0127M05#  |
| 150          | 25 x 30    | 540                | 150         | 820              | 2.32         | 1.75         | 0.88       | B43649A0157M05#  |
| 180          | 25 x 35    | 450                | 130         | 680              | 2.69         | 2.03         | 1.02       | B43649A0187M05#  |
| 180          | 30 x 25    | 460                | 140         | 710              | 2.49         | 1.88         | 0.95       | B43649B0187M05#  |
| 220          | 25 x 40    | 370                | 110         | 560              | 3.18         | 2.40         | 1.21       | B43649A0227M05#  |
| 220          | 30 x 30    | 380                | 120         | 580              | 2.92         | 2.20         | 1.11       | B43649B0227M05#  |
| 220          | 35 x 25    | 390                | 130         | 600              | 2.77         | 2.09         | 1.06       | B43649C0227M05#  |
| 270          | 25 x 50    | 300                | 85          | 460              | 3.80         | 2.87         | 1.45       | B43649A0277M05#  |
| 270          | 30 x 35    | 310                | 95          | 470              | 3.43         | 2.59         | 1.30       | B43649B0277M05#  |
| 270          | 35 x 30    | 320                | 100         | 480              | 3.24         | 2.45         | 1.17       | B43649C0277M05#  |
| 330          | 25 x 55    | 250                | 70          | 380              | 4.50         | 3.39         | 1.71       | B43649A0337M05#  |
| 330          | 30 x 40    | 250                | 80          | 390              | 4.02         | 3.04         | 1.44       | B43649B0337M05#  |
| 330          | 35 x 30    | 270                | 95          | 410              | 3.66         | 2.76         | 1.31       | B43649C0337M05#  |
| 390          | 30 x 45    | 220                | 65          | 330              | 4.61         | 3.48         | 1.65       | B43649A0397M05#  |
| 390          | 35 x 35    | 230                | 80          | 350              | 4.19         | 3.16         | 1.50       | B43649B0397M05#  |
| 470          | 30 x 55    | 180                | 55          | 270              | 5.43         | 4.10         | 1.95       | B43649A0477M05#  |
| 470          | 35 x 40    | 190                | 65          | 290              | 4.84         | 3.65         | 1.73       | B43649B0477M05#  |
| 560          | 30 x 60    | 150                | 50          | 230              | 6.28         | 4.73         | 2.25       | B43649A0567M05#  |
| 560          | 35 x 45    | 160                | 55          | 250              | 5.55         | 4.18         | 1.99       | B43649B0567M05#  |
| 680          | 35 x 55    | 130                | 45          | 200              | 6.57         | 4.96         | 2.36       | B43649A0687M05#  |
| 820          | 35 x 60    | 110                | 40          | 170              | 7.59         | 5.72         | 2.71       | B43649A0827M05#  |

#### Composition of ordering code

<sup># =</sup> Terminal style

<sup>0 =</sup> snap-in 2 terminals (6.3 mm)

<sup>2 =</sup> snap-in 3 terminals (4.5 m)

<sup>7 =</sup> snap-in 2 terminals (4.5 mm)

<sup>8 = 2</sup> vibration-resistant terminals (4.5 mm) - available in diameter 30 and 35 mm



Ultra compact - 105 °C

B43649

#### Technical data and ordering codes

|                          | Case       | ESD                          | ECD                          | 7                          | ı                             |                               |                             | Ordering code                  |
|--------------------------|------------|------------------------------|------------------------------|----------------------------|-------------------------------|-------------------------------|-----------------------------|--------------------------------|
| C <sub>R</sub><br>100 Hz | dimensions | ESR <sub>typ</sub><br>120 Hz | ESR <sub>typ</sub><br>360 Hz | Z <sub>max</sub><br>10 kHz | I <sub>AC,max</sub><br>120 Hz | I <sub>AC,max</sub><br>120 Hz | I <sub>AC,R</sub><br>120 Hz | Ordering code (composition see |
| 20 °C                    | d x l      | 20 °C                        | 60 °C                        | 20 °C                      | 60 °C                         | 85 °C                         | 105 °C                      | below)                         |
| μF                       |            | mΩ                           | mΩ                           | mΩ                         |                               | A                             |                             | Delow)                         |
| <u> </u>                 | mm         | 11177                        | 11177                        | 11177                      | Α                             | А                             | Α                           |                                |
| $V_{R} = 500$            | O V DC     | 1                            | 1                            | ,                          | ,                             | ,                             | 1                           |                                |
| 100                      | 25 x 25    | 770                          | 220                          | 1150                       | 1.79                          | 1.35                          | 0.68                        | B43649A6107M05#                |
| 120                      | 25 x 30    | 640                          | 180                          | 960                        | 2.07                          | 1.56                          | 0.79                        | B43649A6127M05#                |
| 150                      | 25 x 35    | 510                          | 140                          | 770                        | 2.48                          | 1.87                          | 0.94                        | B43649A6157M05#                |
| 150                      | 30 x 25    | 520                          | 160                          | 790                        | 2.32                          | 1.75                          | 0.88                        | B43649B6157M05#                |
| 180                      | 25 x 40    | 430                          | 120                          | 640                        | 2.88                          | 2.17                          | 1.09                        | B43649A6187M05#                |
| 180                      | 30 x 30    | 430                          | 130                          | 650                        | 2.67                          | 2.01                          | 1.01                        | B43649B6187M05#                |
| 220                      | 25 x 45    | 350                          | 100                          | 530                        | 3.41                          | 2.57                          | 1.29                        | B43649A6227M05#                |
| 220                      | 30 x 35    | 350                          | 110                          | 540                        | 3.12                          | 2.36                          | 1.19                        | B43649B6227M05#                |
| 220                      | 35 x 25    | 380                          | 130                          | 570                        | 2.90                          | 2.18                          | 1.10                        | B43649C6227M05#                |
| 270                      | 25 x 55    | 280                          | 80                           | 430                        | 4.08                          | 3.08                          | 1.55                        | B43649A6277M05#                |
| 270                      | 30 x 40    | 290                          | 90                           | 440                        | 3.68                          | 2.77                          | 1.32                        | B43649B6277M05#                |
| 270                      | 35 x 30    | 300                          | 100                          | 460                        | 3.40                          | 2.56                          | 1.22                        | B43649C6277M05#                |
| 330                      | 30 x 45    | 240                          | 75                           | 360                        | 4.32                          | 3.26                          | 1.55                        | B43649A6337M05#                |
| 330                      | 35 x 35    | 250                          | 85                           | 380                        | 3.97                          | 2.99                          | 1.42                        | B43649B6337M05#                |
| 390                      | 30 x 50    | 200                          | 65                           | 310                        | 4.96                          | 3.74                          | 1.77                        | B43649A6397M05#                |
| 390                      | 35 x 40    | 210                          | 70                           | 320                        | 4.53                          | 3.41                          | 1.62                        | B43649B6397M05#                |
| 470                      | 30 x 60    | 170                          | 50                           | 260                        | 5.85                          | 4.41                          | 2.09                        | B43649A6477M05#                |
| 470                      | 35 x 45    | 180                          | 60                           | 270                        | 5.23                          | 3.94                          | 1.87                        | B43649B6477M05#                |
| 560                      | 35 x 55    | 150                          | 50                           | 220                        | 6.10                          | 4.61                          | 2.19                        | B43649A6567M05#                |
| 680                      | 35 x 60    | 120                          | 45                           | 190                        | 7.10                          | 5.35                          | 2.54                        | B43649A6687M05#                |

#### Composition of ordering code

Other voltage and capacitance ratings are also available upon request.

#### Remark:

For useful life calculations, please use our web-based "AlCap Useful Life Calculation Tool", which can be found on the Internet under the following link:

www.tdk-electronics.tdk.com/alcap

The "AlCap Useful Life Calculation Tool" provides calculations of useful life as well as additional data for selected capacitor types under operating conditions defined by the user.

In addition, it is possible to calculate useful life expectancies based on temperatures measured by the user in the application.

<sup># =</sup> Terminal style

<sup>0 =</sup> snap-in 2 terminals (6.3 mm)

<sup>2 =</sup> snap-in 3 terminals (4.5 m)

<sup>7 =</sup> snap-in 2 terminals (4.5 mm)

<sup>8 = 2</sup> vibration-resistant terminals (4.5 mm) - available in diameter 30 and 35 mm



B43649

Ultra compact - 105 °C

#### Cautions and warnings

#### Personal safety

The electrolytes used have been optimized both with a view to the intended application and with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC). Furthermore, some of the high-voltage electrolytes used are self-extinguishing.

As far as possible, we do not use any dangerous chemicals or compounds to produce operating electrolytes, although in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no alternative materials are currently known. We do, however, restrict the amount of dangerous materials used in our products to an absolute minimum.

Materials and chemicals used in our aluminum electrolytic capacitors are continuously adapted in compliance with the TDK Electronics Corporate Environmental Policy and the latest EU regulations and guidelines such as RoHS, REACH/SVHC, GADSL, and ELV.

MDS (Material Data Sheets) are available on our website for all types listed in the data book. MDS for customer specific capacitors are available upon request.

MSDS (Material Safety Data Sheets) are available for our electrolytes upon request.

Nevertheless, the following rules should be observed when handling aluminum electrolytic capacitors: No electrolyte should come into contact with eyes or skin. If electrolyte does come into contact with the skin, wash the affected areas immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment. Avoid inhaling electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.



| Large-size capacitors  | B43649 |
|------------------------|--------|
| Ultra compact – 105 °C |        |

## **Product safety**

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of seperate file chapter "General technical information".

| Topic   | Safety information   | Reference chapter "General technical information"                         |
|---|--|---|
| Polarity  | Make sure that polar capacitors are connected with the right polarity.   | 1 "Basic construction of aluminum electrolytic capacitors"                |
| Reverse voltage   | Voltages of opposite polarity should be prevented by connecting a diode.   | 3.1.6 "Reverse voltage"   |
| Mounting position of capacitors with screw or multi-pin terminals | Multi-pin capacitors with pressure relief vent on the can base must not be mounted with terminals facing up unless otherwise specified.  | 11.1 "Mounting positions of capacitors with screw or multi-pin terminals" |
| Robustness of terminals   | The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2.5 Nm M6: 4.0 Nm   | 11.2 "Mounting torques"   |
| Mounting of single-ended capacitors                               | The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires.  Avoid any compressive, tensile or flexural stress. Do not move the capacitor after soldering to PC board.  Do not pick up the PC board by the soldered capacitor.  Do not insert the capacitor on the PC board with a hole space different to the lead space specified. | 11.3 "Mounting considerations for single-ended capacitors"                |
| Soldering   | Do not exceed the specified time or temperature limits during soldering.   | 11.5<br>"Soldering"   |
| Soldering,<br>cleaning agents                                     | Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.  | 11.6 "Cleaning agents"  |
| Upper category temperature  | Do not exceed the upper category temperature.  | 7.2 "Maximum permissible operating temperature"                           |
| Passive flammability  | Avoid external energy, e.g. fire.  | 8.1 "Passive flammability"  |



| Large-size capacitors  | B43649 |
|------------------------|--------|
| Ultra compact – 105 °C |        |

| Topic  | Safety information   | Reference chapter "General technical information"   |
|--|--|---|
| Active flammability                            | Avoid overload of the capacitors.  | 8.2 "Active flammability"                           |
| Maintenance                                    | Make periodic inspections of the capacitors. Before the inspection, make sure that the power supply is turned off and carefully discharge the capacitors. Do not apply excessive mechanical stress to the capacitor terminals when mounting. | 10<br>"Maintenance"                                 |
| Storage  | Do not store capacitors at high temperatures or high humidity. Capacitors should be stored at +5 to +35 $^{\circ}$ C and a relative humidity of $\leq$ 75%.  | 7.3 "Shelf life and storage conditions"             |
|  |  | Reference chapter "Capacitors with screw terminals" |
| Breakdown<br>strength of<br>insulating sleeves | Do not damage the insulating sleeve, especially when ring clips are used for mounting.   | "Screw terminals – accessories"                     |

#### Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.

Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.



# Large-size capacitors B43649 Ultra compact – 105 °C

# Symbols and terms

| Symbol              | English                                       | German                                  |  |
|---------------------|---|---|--|
| С                   | Capacitance                                   | Kapazität                               |  |
| $C_R$               | Rated capacitance                             | Nennkapazität                           |  |
| $C_S$               | Series capacitance                            | Serienkapazität                         |  |
| $C_{S,T}$           | Series capacitance at temperature T           | Serienkapazität bei Temperatur T        |  |
| $C_f$               | Capacitance at frequency f                    | Kapazität bei Frequenz f                |  |
| d                   | Case diameter, nominal dimension              | Gehäusedurchmesser, Nennmaß             |  |
| $d_{max}$           | Maximum case diameter                         | Maximaler Gehäusedurchmesser            |  |
| ESL                 | Self-inductance                               | Eigeninduktivität                       |  |
| ESR                 | Equivalent series resistance                  | Ersatzserienwiderstand                  |  |
| $ESR_f$             | Equivalent series resistance at frequency f   | Ersatzserienwiderstand bei Frequenz f   |  |
| ESR <sub>T</sub>    | Equivalent series resistance at temperature T | Ersatzserienwiderstand bei Temperatur T |  |
| f                   | Frequency                                     | Frequenz                                |  |
| 1                   | Current                                       | Strom                                   |  |
| $I_{AC}$            | Alternating current (ripple current)          | Wechselstrom                            |  |
| I <sub>AC,RMS</sub> | Root-mean-square value of alternating current | Wechselstrom, Effektivwert              |  |
| $I_{AC,f}$          | Ripple current at frequency f                 | Wechselstrom bei Frequenz f             |  |
| $I_{AC,max}$        | Maximum permissible ripple current            | Maximal zulässiger Wechselstrom         |  |
| I <sub>AC,R</sub>   | Rated ripple current                          | Nennwechselstrom                        |  |
| I <sub>leak</sub>   | Leakage current                               | Reststrom                               |  |
| $I_{leak,op}$       | Operating leakage current                     | Betriebsreststrom                       |  |
| 1                   | Case length, nominal dimension                | Gehäuselänge, Nennmaß                   |  |
| I <sub>max</sub>    | Maximum case length                           | Maximale Gehäuselänge                   |  |
|                     | (without terminals and mounting stud)         | (ohne Anschlüsse und Gewindebolzen)     |  |
| R                   | Resistance                                    | Widerstand                              |  |
| $R_{ins}$           | Insulation resistance                         | Isolationswiderstand                    |  |
| $R_{symm}$          | Balancing resistance                          | Symmetrierwiderstand                    |  |
| T                   | Temperature                                   | Temperatur                              |  |
| $\DeltaT$           | Temperature difference                        | Temperaturdifferenz                     |  |
| $T_A$               | Ambient temperature                           | Umgebungstemperatur                     |  |
| $T_B$               | Capacitor base temperature                    | Temperatur des Gehäusebodens            |  |
| $T_C$               | Case temperature                              | Gehäusetemperatur                       |  |
| t                   | Time  | Zeit                                    |  |
| Δt                  | Period  | Zeitraum                                |  |
| $t_b$               | Service life (operating hours)                | Brauchbarkeitsdauer (Betriebszeit)      |  |
| V                   | Voltage                                       | Spannung                                |  |
| $V_{F}$             | Forming voltage                               | Formierspannung                         |  |
| $V_{op}$            | Operating voltage                             | Betriebsspannung                        |  |
| $V_R$               | Rated voltage, DC voltage                     | Nennspannung, Gleichspannung            |  |
| $V_S$               | Surge voltage                                 | Spitzenspannung                         |  |
| X <sub>C</sub>      | Capacitive reactance                          | Kapazitiver Blindwiderstand             |  |



| Large-size capacitors  | B43649 |
|------------------------|--------|
| Ultra compact – 105 °C |        |

| Symbol         | English                                  | German                               |
|----------------|--|--------------------------------------|
| $X_L$          | Inductive reactance                      | Induktiver Blindwiderstand           |
| Z              | Impedance                                | Scheinwiderstand                     |
| $Z_{T}$        | Impedance at temperature T               | Scheinwiderstand bei Temperatur T    |
| tan $\delta$   | Dissipation factor                       | Verlustfaktor                        |
| λ              | Failure rate                             | Ausfallrate                          |
| $\epsilon_0$   | Absolute permittivity                    | Elektrische Feldkonstante            |
| $\epsilon_{r}$ | Relative permittivity                    | Dielektrizitätszahl                  |
| ω              | Angular frequency; $2 \cdot \pi \cdot f$ | Kreisfrequenz; $2 \cdot \pi \cdot f$ |

#### Note:

All dimensions are given in mm.



#### Important notes

The following applies to all products named in this publication:

- Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- The warnings, cautions and product-specific notes must be observed.
- In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.



#### Important notes

- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, InsuGate, LeaXield, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap, XieldCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2022-07