

RM 5, RM 5 LP Core and accessories

Series/Type: B65805, B65806, B65822, B65539, B65518

Date: October 2022

[©] TDK Electronics AG 2022. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



Core and accessories

\ _p \	Individual parts	Part no.	Page
	- Adjusting screw	B65518 B65539 B65806	9
	- Core	B65805	3
	- Clamps	B65806	6
	- Coil former	B65806	5
	- Core	B65805	3
	- Threaded sleeve (glued-in)		
	- Insulating washer	B65806	6
FRM0005-2 Example of an assembly set			
Also available:	SMD coil formers	B65822	7, 8
	Clamps	B65806	7, 8
	RM 5 low profile:		
	Core	B65805P	10



Core B65805

■ To IEC 63093-4

 Core without center hole for transformer applications


■ Delivery mode: sets

Magnetic characteristics (per set)

	with center hole	without center hole	
ΣΙ/Α	1.0	0.93	mm ⁻¹
l _e	20.8	22.1	mm
l _e A _e A _{min}	20.8	23.8	mm ²
A_{min}		18	mm ²
V _e	433	526	mm ³

Approx. weight (per set)

m	2.9	3.0	g



Gapped (A_L values/air gaps examples)

Material	A _L value	s approx. mm	μ_{e}	Ordering code ¹⁾ -C with center hole -N with threaded sleeve
K1	25 ±3%	1.0	19.9	B65805+0025A001
	40 ±3%	0.40	31.8	B65805+0040A001
M33	63 ±3%	0.4	50.2	B65805+0063A033
	100 ±3%	0.2	79.6	B65805+0100A033
N48	160 ±3%	0.12	127	B65805+0160A048
	250 ±3%	0.06	199	B65805+0250A048
	315 ±3%	0.03	251	B65805+0315A048

¹⁾ Replace the + by the code letter "C" or "N" for the required version.



RM 5 Core B65805

Ungapped

Material	A _L value	μ_{e}	P _V	Ordering code -C with center hole
	nH		W/set	-J without center hole
PC200	800 +30/–20%	590	< 0.15 (50 mT, 1000 kHz, 100 °C)	B65805J0000R608
			< 0.20 (30 mT, 2000 kHz, 100 °C)	
N48	1800 +30/–20%	1430		B65805C0000R048
N45	2600 +30/–20%	1920		B65805J0000R045
N30	3500 +30/–20%	2590		B65805J0000R030
T38	6700 +40/–30%	4950		B65805J0000Y038
N49	1300 +30/–20%	960	< 0.06 (50 mT, 500 kHz, 100 °C)	B65805J0000R049
N87	2000 +30/–20%	1480	< 0.32 (200 mT, 100 kHz, 100 °C)	B65805J0000R087
N97	2000 +30/–20%	1480	< 0.24 (200 mT, 100 kHz, 100 °C)	B65805J0000R097
N95	2450 +30/–20%	1800	< 0.20 (200 mT, 100 kHz, 100 °C)	B65805J0000R095
			< 0.22 (200 mT, 100 kHz, 25 °C)	
N41	2600 +30/–20%	1920	< 0.10 (200 mT, 25 kHz, 100 °C)	B65805J0000R041

Other A_L values/air gaps and materials available on request — see Processing remarks on page 11.



Accessories B65806

Coil former

Material: GFR thermosetting plastic (UL 94 V-0, insulation class to IEC 60085:

F

max. operating temperature 155 °C), color code black

SUMIKON PM 9630 [E41429 (M)], SUMITOMO BAKELITE CO LTD


Solderability: to IEC 60068-2-20, test Ta, method 1 (aging 3): 235 °C, 2 s

Resistance to soldering heat: to IEC 60068-2-20, test Tb, method 1B: 350 °C, 3.5 s

Winding: see Processing notes, 2.1

For matching clamps and insulating washers see page 6.

Sections	A _N mm ²	I _N mm	A_R value $\mu\Omega$	Pins	Ordering code
1	9.5	25	90	4 5 6 8	B65806N1104D001 B65806N1105D001 B65806N1106D001 B65806N1108D001
2	8.7	25	94	6	B65806N1106D002





Accessories B65806

Clamp

- With ground terminal, made of stainless spring steel (tinned), 0.3 mm thick
- Solderability to IEC 60068-2-20, test Ta, method 1 (aging 3): 235 °C, 2 s


Insulating washer for double-clad PCBs


■ Made of polycarbonate (UL 94 V-0, insulation class to IEC 60085: E 120 °C), 0.25 mm thick Makrofol FR7-2 [E168120 (M)], COVESTRO AG

	Ordering code
Clamp (ordering code per piece, 2 are required)	B65806B2203X000
Insulating washer (bulk)	B65806D2005X000


Clamp

Insulating washer





Clamping forces for RM 5



 F_{min} : Extension of clamp from a to $a_2 = X_{min}$ F_{max} : Extension of clamp from a to $a_1 = X_{max}$

Clamp opening a (mm)	8.3 +0.15	
Core nose Z _{max} (mm)	0.15	
Height of core pair X (mm	n)X _{min} X _{max}	8.75 9.25
Clamping force F (N)	F _{min} F _{max}	5 40



Accessories B65822, B65806



SMD coil former with gullwing terminals

Material: GFR liquid crystal polymer (UL 94 V-0, insulation class to IEC 60085:

F ≙ max. operating temperature 155 °C), color code black Laperos E 130i [E106764 (M)], POLYPLASTICS CO LTD

Vectra E 130i [E83005 (M)], CELANESE INTERNATIONAL CORP.

Solderability: to IEC 60068-2-58, test Td, method 6 (Group 3): 245 °C, 3 s

Resistance to soldering heat: to IEC 60068-2-58, test Td, method 6 (Group 3): 255 °C, 10 s

permissible soldering temperature for wire-wrap connection on coil former: 400 °C, 1 s


Winding: see Processing notes, 2.1

Clamp

■ Without ground terminal, made of stainless spring steel, 0.335 mm thick

Sections	A _N mm ²	I _N mm	A _R value $\mu\Omega$	Terminals	Ordering code
			•		
1	11.1	25	77	8	B65822F1008T001
2	10.2	25	85	8	B65822F1008T002
Clamp(ordering code per piece, 2 are required)					B65806J2204X000

Coil former Clamp





Accessories B65822, B65806



SMD coil former with J terminals

Material: GFR liquid crystal polymer (UL 94 V-0, insulation class to IEC 60085:

F ≙ max. operating temperature 155 °C), color code black Laperos E 130i [E106764 (M)], POLYPLASTICS CO LTD

Vectra E 130i [E83005 (M)], CELANESE INTERNATIONAL CORP.

Solderability: to IEC 60068-2-58, test Td, method 6 (Group 3): 245 °C, 3 s

Resistance to soldering heat: to IEC 60068-2-58, test Td, method 6 (Group 3): 255 °C, 10 s

permissible soldering temperature for wire-wrap connection on coil former: 400 °C, 1 s

Winding: see Processing notes, 2.1

9.8±0.1

7.1±0.1

ø5.95-0.15


Clamp


■ Without ground terminal, made of stainless spring steel, 0.335 mm thick


Sections	A _N mm ²	I _N mm	A _R value μΩ	Terminals	Ordering code
1	11.1	25	73	8	B65822J1008T001
Clamp(orderin	B65806J2204X000				

Coil former Clamp

15-0.1










Accessories


B65539, B65806, B65518


Adjusting screw

■ Tube core with thread and core brake made of GFR polyterephthalate Pocan B3235® [E245249 (M)], LANXESS AG

Figure	Tube core			Ordering code
	$\emptyset \times \text{length (mm)}$	Material	Color code	
а	1.81 × 2.0	K1	yellow	B65539C1003X001
а	1.81 × 2.7	N22	red	B65539C1002X022
b	1.81 × 3.4	N22	green	B65806C3001X022
С	1.81 × 2.0	K1	blue	B65518C3000X001









FRM0347-V

RM 5 »Low Profile«

Core B65805P

■ To IEC 63093-4

■ For compact transformers

■ Without center hole

■ Delivery mode: sets

Magnetic characteristics (per set)


 $\Sigma I/A = 0.71 \text{ mm}^{-1}$

 $I_e = 17.5 \text{ mm}$

 $A_e = 24.5 \text{ mm}^2$

 $A_{min} = 18 \text{ mm}^2$ $V_e = 430 \text{ mm}^3$

Approx. weight 2.6 g/set



Ungapped

Material	A _L value	μ_{e}	P _V	Ordering code
	nH		W/set	
T38	7700 +40/–30%	4380		B65805P0000Y038
N49	1700 +30/–20%	970	< 0.09 (50 mT, 500 kHz, 100 °C)	B65805P0000R049
N92	1900 +30/–20%	1080	< 0.29 (200 mT, 100 kHz, 100 °C)	B65805P0000R092
N87	2400 +30/–20%	1360	< 0.26 (200 mT, 100 kHz, 100 °C)	B65805P0000R087

Other A_L values/air gaps and materials available on request — see Processing remarks on page 11.



Cautions and warnings

Mechanical stress and mounting

Ferrite cores have to meet mechanical requirements during assembling and for a growing number of applications. Since ferrites are ceramic materials one has to be aware of the special behavior under mechanical load.

As valid for any ceramic material, ferrite cores are brittle and sensitive to any shock, fast temperature changing or tensile load. Especially high cooling rates under ultrasonic cleaning and high static or cyclic loads can cause cracks or failure of the ferrite cores.

For detailed information see data book, chapter "General - Definitions, 8.1".

Effects of core combination on A_I value

Stresses in the core affect not only the mechanical but also the magnetic properties. It is apparent that the initial permeability is dependent on the stress state of the core. The higher the stresses are in the core, the lower is the value for the initial permeability. Thus the embedding medium should have the greatest possible elasticity.

For detailed information see data book, chapter "General - Definitions, 8.1".

Heating up

Ferrites can run hot during operation at higher flux densities and higher frequencies.

NiZn-materials

The magnetic properties of NiZn-materials can change irreversible in high magnetic fields.

Ferrite Accessories

Our ferrite accessories have been designed and evaluated only in combination with our ferrite cores. We explicitly point out that our ferrite accessories or our ferrite cores may not be compatible with those of other manufacturers. Any such combination requires prior testing by the customer and will be at the customer's own risk.

We assume no warranty or reliability for the combination of our ferrite accessories with cores and other accessories from any other manufacturer.

Processing remarks

The start of the winding process should be soft. Else the flanges may be destroyed.

- Too strong winding forces may blast the flanges or squeeze the tube that the cores can not be mounted any more.
- Too long soldering time at high temperature (>300 °C) may effect coplanarity or pin arrangement.
- Not following the processing notes for soldering of the J-leg terminals may cause solderability
 problems at the transformer because of pollution with Sn oxyde of the tin bath or burned insulation of the wire. For detailed information see chapter "Processing notes", section 2.2.
- The dimensions of the hole arrangement have fixed values and should be understood as a recommendation for drilling the printed circuit board. For dimensioning the pins, the group of holes can only be seen under certain conditions, as they fit into the given hole arrangement. To avoid problems when mounting the transformer, the manufacturing tolerances for positioning the customers' drilling process must be considered by increasing the hole diameter.



Cautions and warnings

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.



Symbols and terms

Symbol	Meaning	Unit
A	Cross section of coil	mm ²
A_{e}	Effective magnetic cross section	mm ²
A_L	Inductance factor; $A_L = L/N^2$	nH
A_{L1}^{-}	Minimum inductance at defined high saturation (≙ μ _a)	nH
A_{min}	Minimum core cross section	mm ²
A _N	Winding cross section	mm ²
A_R	Resistance factor; $A_R = R_{Cu}/N^2$	$\mu\Omega = 10^{-6} \Omega$
В	RMS value of magnetic flux density	Vs/m ² , mT
ΔΒ	Flux density deviation	Vs/m ² , mT
Ê	Peak value of magnetic flux density	Vs/m ² , mT
Δ B	Peak value of flux density deviation	Vs/m ² , mT
B_{DC}	DC magnetic flux density	Vs/m ² , mT
B _R	Remanent flux density	Vs/m ² , mT
B_S	Saturation magnetization	Vs/m ² , mT
C_0	Winding capacitance	F = As/V
CDF	Core distortion factor	mm ^{-4.5}
DF	Relative disaccommodation coefficient DF = d/μ_i	
d	Disaccommodation coefficient	
E_a	Activation energy	J
f	Frequency	s−1, Hz
f _{cutoff}	Cut-off frequency	s⁻¹, Hz
f _{max}	Upper frequency limit	s−1, Hz
f _{min}	Lower frequency limit	s ^{−1} , Hz
f_r	Resonance frequency	s⁻¹, Hz
f_{Cu}	Copper filling factor	
g	Air gap	mm
Н	RMS value of magnetic field strength	A/m
Ĥ	Peak value of magnetic field strength	A/m
H_{DC}	DC field strength	A/m
H_c	Coercive field strength	A/m
h	Hysteresis coefficient of material	10 ^{−6} cm/A
h/μ_i^2	Relative hysteresis coefficient	10 ^{−6} cm/A
1	RMS value of current	Α
I_{DC}	Direct current	Α
Î	Peak value of current	Α
J	Polarization	Vs/m ²
k	Boltzmann constant	J/K
k_3	Third harmonic distortion	
k _{3c}	Circuit third harmonic distortion	
L	Inductance	H = Vs/A



Symbols and terms


Symbol	Meaning	Unit
ΔL/L	Relative inductance change	Н
L_0	Inductance of coil without core	Н
L _H	Main inductance	Н
L_p	Parallel inductance	Н
L _{rev}	Reversible inductance	Н
L_s	Series inductance	Н
l _e	Effective magnetic path length	mm
I_N	Average length of turn	mm
N	Number of turns	
P_{Cu}	Copper (winding) losses	W
P _{trans}	Transferrable power	W
P_V	Relative core losses	mW/g
PF	Performance factor	
Q	Quality factor (Q = ω L/R _s = 1/tan δ _L)	
R	Resistance	Ω
R_{Cu}	Copper (winding) resistance (f = 0)	Ω
R_h	Hysteresis loss resistance of a core	Ω
ΔR_h	R _h change	Ω
R_i	Internal resistance	Ω
R_p	Parallel loss resistance of a core	Ω
R_s	Series loss resistance of a core	Ω
R_{th}	Thermal resistance	K/W
R_V	Effective loss resistance of a core	Ω
S	Total air gap	mm
T	Temperature	°C
ΔT	Temperature difference	K
T_{C}	Curie temperature	°C
t	Time	s
t_{v}	Pulse duty factor	
$tan \ \delta$	Loss factor	
$\text{tan } \delta_{\text{L}}$	Loss factor of coil	
$tan \; \delta_r$	(Residual) loss factor at $H \rightarrow 0$	
$tan \; \delta_{\text{e}}$	Relative loss factor	
$tan \; \delta_h$	Hysteresis loss factor	
tan δ/μ_i	Relative loss factor of material at $H \rightarrow 0$	
U	RMS value of voltage	V
Û	Peak value of voltage	V
V_e	Effective magnetic volume	mm ³
Z	Complex impedance	Ω
Z_n	Normalized impedance $ Z _n = Z /N^2 \times \epsilon (I_e/A_e)$	Ω/mm



Symbols and terms

Symbol	Meaning	Unit
α	Temperature coefficient (TK)	1/K
α_{F}	Relative temperature coefficient of material	1/K
α_{e}	Temperature coefficient of effective permeability	1/K
r	Relative permittivity	
Þ	Magnetic flux	Vs
1	Efficiency of a transformer	
Ів	Hysteresis material constant	mT-1
li	Hysteresis core constant	$A^{-1}H^{-1/2}$
'S	Magnetostriction at saturation magnetization	
,	Relative complex permeability	
0	Magnetic field constant	Vs/Am
а	Relative amplitude permeability	
арр	Relative apparent permeability	
е	Relative effective permeability	
i	Relative initial permeability	
p '	Relative real (inductive) component of $\overline{\mu}$ (for parallel components)	
p"	Relative imaginary (loss) component of $\overline{\mu}$ (for parallel components)	
r	Relative permeability	
rev	Relative reversible permeability	
s'	Relative real (inductive) component of $\overline{\mu}$ (for series components)	
s"	Relative imaginary (loss) component of $\overline{\mu}$ (for series components)	
tot	Relative total permeability	
	derived from the static magnetization curve	
	Resistivity	Ω m $^{-1}$
I/A	Magnetic form factor	mm ⁻¹
Cu	DC time constant $\tau_{Cu} = L/R_{Cu} = A_L/A_R$	s
)	Angular frequency; ω = 2 Π f	s ⁻¹

All dimensions are given in mm.





Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.



- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, InsuGate, LeaXield, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap, XieldCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2022-07